

G611E17WKA

gorenje

Freestanding all gas cooker



HomeMade shape



SilverMatte



High Efficiency Burners

Energy class: **A**

Colour: **White**

Control panel material: **Varnished metal**

Door material: **Glass**

Oven volume: gross/net: **56 / 57 l**

SuperSize baking area

HomeMADE® modelled on traditional wood-fired bread oven

Knob shape: **Ergonomic knobs**

Electric ignition of gas burners

Gas hob

Burner frames number: **2**

1 auxiliary burner + 1 large burner + 2 standard burners Left front: Ø 6.9 cm, 1.9 kW, Right front: Ø 9.4 cm, 3 kW, Left behind: Ø 6.9 cm, 1.9 kW, Right behind: Ø 4.6 cm, 1 kW

Type of pan support: **Enameled**

Gas oven - 57 l

Heating:



Illumination

Deep enamelled pan

Wire shelf

Wire oven guides

Double glazed oven door with one heat deflector (CompactDoor)

AquaClean

Energy consumption: **1.69 kWh (conventional)**

Energy consumption gas oven: **6.08 MJ**

Gas type: **G20/20 natural gas**

Enclosed nozzles: **Gas nozzles G30/30 liquid gas**

Dimensions of the product (WxHxD): **60 x 90 x 60 cm**

Dimensions of packed product (WxHxD): **67.6 x 95 x 71.5 cm**

Net weight: **45 kg**

Code: **497814**

EAN code: **3838942050114**



<http://www.gorenje.co.uk/product/497814>