



PRO-SERIES HD

720P



Professional Security System

8 Channel Digital Video Recorder & 4 Cameras

8CH

8 CHANNEL VIEWING

HD

LIVE VIEW & RECORDING

1TB

30 DAYS RECORDING+



DAY/NIGHT VISION



WEATHER PROOF



EASY BACKUP

HDMI

CONNECT TO TV/MONITOR

DIY

EASY INSTALLATION

Be protected & see every detail in HD

- A state of the art & expandable surveillance system with video technology equivalent to 720p HD resolution
- Set & forget by recording continuously from 8 channels for 30 days+ onto a 1TB hard drive, even longer with motion detection
- Seeing is believing with 4 x 720p HD Cameras(1 Megapixel)
- Expand by adding 4 Swann PRO-AXXX cameras of your choice for full 8 channel monitoring^
- Save time & have peace of mind by easily locating incident video, then transfer to external storage via USB or network
- View live or playback video in high definition on your HDTV, LCD screen or monitor via HDMI connection or VGA port
- Connect in minutes using SwannLink 'Peer-to-Peer' easy network connection software
- Surveillance in the palm of your hand with live viewing on 3G/4G-enabled Smartphone & tablets including, iPhone, iPad, Android devices and more* using the free SwannView Link app

SWDVK-844004

For more information on this product visit www.swann.com



Professional HD Security System

DVR8-4400™ 8 Channel 720p Digital Video Recorder + 4 x 720p HD Cameras

What's in the box

All installation accessories included

- DVR8-4400™ with Hard Drive
- PRO-A850™ 720p Cameras x 4
- BNC Cables 60ft / 18m x 4
- Ethernet Cable
- HDMI Cable
- Power Adapter & Splitter
- Mouse
- Mounting Screws & Plugs
- Quick Start Guide
- Theft Deterrent Stickers



Specifications

DVR8-4400™ Digital Video Recorder

Video

Inputs	8 Channels
Outputs	VGA, HDMI
Display Resolution	Up to 1080p

Audio

Audio Input	1 RCA
Audio Output	1 RCA

Recording

Compression Format	H.264
Recording Modes	Manual / Motion / Schedule
Recording Resolution	Up to 720p
Multi Tasking	Recording / Playback / Network Simultaneously
Frame Rate	Up to real-time 30fps / 25fps

Hard Drive

HDD Included	1TB
Hard Drive Capacity	Up to 3TB SATA HDD

Connection

Network Connection	SwannLink 'Peer-to-Peer'
Network Interface	RJ45 Port x 1
USB Interface	USB 2.0 x 2

Software

Computer Operating Systems	Windows, Mac OS
Internet Viewing	SwannView Link
Handheld Device Supported	iOS, Android, 3G / 4G Smartphones & Tablets

General

Operating Power	DC 12V
Dimensions (WxDxH)	8.5" x 8.9" x 2.0" / 215 x 225 x 50mm

PRO-A850™ Camera

Video

Video Quality	720p
Viewing Angle	62°

Night Vision

Night Vision Distance	Up to 100ft / 30m
IR cut Filter	Yes
General	Indoor or outdoor, IP67 rated
Indoor / Outdoor	DC 12V
Operating Power	-4° F ~ 122° F / -20° C ~ 50° C
Operating Temperature	Aluminum
Body Construction	2.6" x 7.1" x 2.6" / 66 x 180 x 66mm
Dimensions - Camera	0.8lbs / 363g

Code

Swann Code SWDVK-844004

^ 720P recording only possible with PRO-AXXX cameras

+ 30 days recording achieved using lower settings, default settings give 4 days recording


* Monitor, tablet and mobile phones not included. Not all handsets supported

Note: Trademarks are properties of their respective owners

Now with

SwannLink™

LINK & SEE YOUR WORLD IN MINUTES!



Free Download
SwannView Link App



COMPATIBLE WITH



Our Promise

Swann stands by its promise of Lifetime Support to make advanced security easy to use, install and maintain. Everything is in the pack but if you need it Swann's help desk is available **24 hours a day, 7 days a week** for the life of the product.

Installation is easy

Do-it-Yourself

Installing this Swann product is simple. For instructions, tips and videos see the operating instructions in this pack or visit www.swann.com

Professional Installation

Need extra help? We have an installer in your region! For more visit www.swann.com

For more information on this product visit

www.swann.com