

# AVerCharge S40i

## 40 Device Intelligent Charging Cart



### Load with Ease

S40i's two easy-access sliding shelves hold up to 40 laptops, Chromebooks, netbooks, iPads, and Android/Windows tablets (devices up to 14" screens).



### We've got your back

With AVer, you not only get a superior solution, but you are backed by dedicated technical and customer support teams, plus America's best cart warranty: 10-year mechanical and 5-year electrical warranties.



### Easy Cable Management

S40i provides individual AC adapter compartments and cable clips to prevent any cable mess. Device slots are also individually numbered to keep cable routing and devices organized.



### Safe, Secure, Durable

With three-point steel locking mechanisms built into its cabinet doors, S40i provides a safe haven for your devices when they are being charged or stored.



### Intelligent Charging System

S40i monitors all 40 devices in groups of 10 and determines the best charging sequence: all device groups at once, or each group individually. No programming required – it's automatic, safe, and efficient!



### Dependable, Versatile, Maneuverable

The charging cart's large capacity, steel construction, and smooth-rolling, 5" medical-grade locking swivel castors provide a rugged, yet easily maneuverable storage cart that can double as a teaching platform!



# Specifications

<b>Device Capacity</b>	40 (20 devices * 2 sliding shelves)	<b>Cart Dimension</b>	W = 97cm (38.19") D = 62cm (24.41") H = 103cm (40.43")
<b>Slot Size</b>	W = 2.8cm (1.1") D = 36.4cm (14.33") H = 25.0cm (9.84")	<b>Package Dimension</b>	W = 103cm (40.55") D = 72cm (28.35") H = 123.5cm (48.62")
<b>Supported Devices</b>	Chromebooks, iPads, Android, Windows Tablets, Netbooks (up to 14" screen, supports most tablet covers with total width up to 1.1")	<b>LED Indicator</b>	Power LED: Green Status LED (x4): Solid Blue: Regular Charging, Flashing Blue: Quick Charge
<b>Charging Type</b>	Intelligent, self-monitoring, zone-based charging system; no programming required	<b>Power Specification</b>	<p><b>AC IN:</b> 100-120V ~ 50/60Hz, 12A 220-240V ~ 50/60Hz, 8A</p> <p><b>PWR Strip 40-Port Total</b> 100-120V ~ 50/60Hz, 8A 220-240V ~ 50/60Hz, 6A</p> <p><b>Outlet 4-Port Total</b> 100-120V ~ 50/60Hz, 4A 220-240V ~ 50/60Hz, 2A</p>
<b>Cable Management</b>	Numbered device slots with cable clips; individual AC adapter compartments	<b>Security</b>	Front and rear doors: 3 point mechanism with lock hole
<b>External Power Outlets</b>	4	<b>Cooling/Ventilation</b>	Ventilation slots along front/back panels
<b>Push Cart Handles</b>	Two: integrated, top/side mount	<b>Casters</b>	5" medical-grade casters (x4) 2 are lockable

# Specifications

<b>Color</b>	Exterior: Black doors, side panels White trim, auxiliary power panel  Interior: Black doors, side panels Silver: Steel rod dividers AC adapter slots	<b>Certification</b>	UL certified
<b>Gross Weight</b>	116kg (255.8lbs)	<b>Net Weight</b>	87kg (191.8lbs)
<b>Warranty</b>	10 years cart and tray 5 years electrical components	<b>Accessories with Shipment</b>	User manual, warranty card, power cord, cable clips



Aver Information Inc. Americas  
[averusa.com](http://averusa.com)  
 668 Mission Court,  
 Fremont, CA 94539  
 T 408.263.3828  
 F 408.263.8132  
 toll free 1.877.528.7824