




e2470Swhe

59.9cm (23.6") LCD MONITOR



General Features:

Line:	Value
Panel type:	WLED / TN
Panel Size:	23.6" / 59.9 cm
Aspect Ratio:	16:9
Brightness:	250 cd/m ²
Contrast Ratio Dynamic:	20M:1
Contrast Ratio Typical:	1000:1 (CR)
Pixel / Dot / Pitch:	0.276 (H) mm x 0.276 (V) mm
Display Area:	531.36 (H) x 298.89 (V)
Viewing Angle:	170(H)/160(V) (CR≥10)
Response Time:	5 ms
Color:	Black

Scanning Frequency:

Scanning Frequency:	H: 30-83 KHz / V: 55-75 Hz
Pixel Frequency:	148.5MHz

Resolution:

Maximum Resolution:	1920x1080@60Hz
Recommend Resolution:	1920x1080@60Hz
Colors:	16,7M
HDCP compatible:	Yes

Connectors:

Analogue Input: D-Sub	1x
Digital Input: DVI-D	No
HDMI:	2x
USB:	No
MHL:	No
DisplayPort:	No
Daisychain:	No

Power:

Power Source:	110 - 240 V AC, 50 / 60 Hz
Power Consumption:	On: 26W, Standby: <0.5W, Off: 0.5W

Other Features:

Plug & Play:	Yes
User Control:	Button
Speaker:	No
Wallmount:	100 x 100 mm
Height adjustment:	No
Pivot:	No
Swivel:	No
Tilt:	-5/+15

Regulations:	CE Energy Star 6.0 EuP EPEAT Gold GOST NRTL RoHS TUV-GS TUV-Bauert TCO 6.0
--------------	---

Specific Features:

e-Saver
Eco Mode
i-Menu
Kensington Security Lock
Screen+

Accessories:

Power cable
D-Sub cable
HDMI cable
Product CD-ROM
Warranty Card on CD-ROM

Dimensions:

Product with stand (WxHxD):	551.4 x 396.9 x 78.2 mm
Packaging (WxHxD):	620 x 127 x 435 mm
Weight:	3.58 kg wo/packaging // 5.21 kg w/packaging
Warranty:	3 Years
EAN:	4038986144193