

PLA 3D Filament 3mm 1kg Reel – Green (55263)

Reorder Number 55263
Pack Size 1 ea

Manufactured to very tight tolerances and from the highest quality materials, Verbatim PLA 3D Printing Filament does not require a heated print bed and is less prone to warping than other filament materials. Designed for compatibility with most commercially available printers, Verbatim PLA filament can be cut, filed or glued post printing, but PLA filament should not be used with acetone. With diameter tolerances of 0.05mm, Verbatim PLA 3D Filaments ensure consistent feeding and stable prints, every time. Verbatim 3D Filaments feature a custom spool designed for strength and balance for uniform feeding. Filaments are packaged in a vacuum-sealed bag, including desiccant, to promote longevity and prevent the introduction of moisture. Verbatim PLA 3D Printing Filaments are backed by a 1-year limited warranty.



- Manufactured to very tight tolerances (+0.05mm diameter) using the highest quality materials to ensure consistent feeding and stable prints
- Custom spool, designed for strength and uniform feeding – ensures top quality prints every time.
- Filaments packaged in vacuum-sealed bag, with desiccant to prevent introduction of dust and moisture.
- PLA (Polylactic Acid) filament for use with 3D printers – degradable bioplastic derived from plants.
- Easier to print – less prone to warping than other filament materials.
- Can be cut, filed or glued post printing – do not use with acetone.
- Compatible with most commercially available non-cartridge based 3D printers.
- For best performance, an extrusion temperature between 200-220°C.
- Heated build platform not required.
- Environmentally friendly – guaranteed not to contain heavy metals, phthalates; BPA Free.
- 1-Year Limited Warranty

Specifications

Diameter Tolerance	3 ± 0.05 mm	Spool depth (In)	2.83 In (7.20 cm)
Process Temperature	200 to 220° C	Hub diameter (In)	4.02 In (10.20 cm)
Net Weight (lbs)	2.20 lbs (1.00 kg)	Hub hole diameter (In)	2.01 In (5.10 cm)
Gross Weight (lbs)	3.00 lbs (1.36 kg)	Heated platform required	No
Spool diameter (In)	7.87 In (20.00 cm)	Recommended storage temperature	-20 to 50° C

Product Information			
L x H x W (In)	7.87 x 2.83 x 7.87 (19.99 x 7.19 x 19.99 in cm)	Weight (lbs)	3.00 lbs (1.36 kg)
Packaging Information			
L x H x W (In)	8.16 x 8.16 x 3.19 (20.73 x 20.73 x 8.1 in cm)	Weight (lbs)	3.31 lbs (1.5 kg)
UPC#	023942552635	Unit Quantity	1 ea
Pallet Quantity	180 (1 ea)	Cartons Per Layer	20
Layers Per Pallet	3		
Master Case Information			
L x H x W (In)	8.81 x 10.81 x 8.81 (22.38 x 27.46 x 22.38 in cm)	Weight (lbs)	10.71 lbs (4.86 kg)
UPC#	50023942552630	Quantity	3 (1 ea)
Shipping Information			
Available Ship Date	In Stock	Country of Origin	JP
Tariff Code	3916.90.3000	Warranty	1-Year Limited Warranty
Minimum Order Qty	3 (1 ea)		

Keywords

55263,#55263,Verbatim PLA Filament 3.00mm - Green, PLA Filament, 3mm PLA Filament, Green PLA Filament, 3D Filament, Green 3D Filament, 3mm 3D Filament, 3D Printing, 3D Printing Supplies, 3D Printing Filament, 3D Printing Filaments