

Dual VGA with Audio over Cat5/Cat6 Extender, Box-Style Receiver, 1440x900 60 Hz, Up to 300 ft. (90 m), TAA

MODEL NUMBER: **B132-200A-SR**



Extends a VGA and audio signal to two sets of monitors and speakers up to 300-ft. from the source

Features

- Features dual VGA and audio ports for the connection of two sets of monitors and speakers
- Works with a B13 or B13 Transmitter Unit to extend a VGA video and audio signal up to 300-ft. from the source
- Extends a 1440 x 900 video and audio signal up to 150-ft, or a 1024 x 768 video and audio signal up to 300-ft.
- 24AWG, Solid Wire Cat5e/6 cable (such as Tripp Lite's N20 Cat6 cables) is required to achieve maximum distance and resolution
- Features a built-in equalization control to adjust the video image
- All operating systems supported
- Plug and play; no software or drivers required
- HDCP and EDID compliant
- Ideal for digital signage installations for retail, schools, churches, etc.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332185570
Product Type	Receiver

Highlights

- Features dual VGA and audio ports for the connection of two sets of monitors and speakers
- Works with a B132-002A-2 or B132-004A-2 Transmitter Unit to extend a VGA video and audio signal up to 300-ft. from the source
- Extends a 1440 x 900 video and audio signal up to 150-ft, or a 1024 x 768 video and audio signal up to 300-ft.
- Plug and play, no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Package Includes

- B132-200A-SR
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 4.5 ft.)
- Screwdriver for EQ adjustment
- Owner's Manual

AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 4.5 ft.
Technology	VGA/SVGA; Stereo Audio; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	1440x900 @ 60Hz
Max 720P Range (ft)	150
Max 1280 x 720 (720p) Range (ft)	150
Receiver/Transceiver Video Output	VGA
Receiver - Number of Video Outputs	2
Signal Range (ft)	300ft @ 1024 x 768 (60Hz) 150ft @ 1440 x 900 (60Hz)
Signal Range (m)	91.4m @ 1024 x 768 (60Hz) 45.7m @ 1440 x 900 (60Hz)
Recommended Cabling	Solid Wire Cat6 Cables (Tripp Lite's N202-Series)
AUDIO	
Audio Output	3.5mm
Audio Specification	Stereo Audio
POWER	
Power Source	Unit (Included)
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P
External Power Supply Input Specs (V / Hz / A)	100-240V / 50-60Hz / 0.5A
External Power Supply Output Specs (V / A)	5V/2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.38
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; PSE; TUV; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red (Power) RJ45: Green (Connection), Orange (Data Transmission)
PHYSICAL	
Color	Black
Included Mounting Accessories	Wallmount
Number of Displays	2

Form Factor/Mounting Options	Box; Wall-mount
Shipping Dimensions (hwd / cm)	5.59 x 15.75 x 18.29
Shipping Dimensions (hwd / in.)	2.20 x 6.20 x 7.20
Shipping Weight (kg)	0.50
Shipping Weight (lbs.)	1.10
Unit Dimensions (hwd / cm)	2.7 x 11.5 x 6.24
Unit Dimensions (hwd / in.)	1.06 x 4.53 x 2.46
Unit Packaging Type	Box
Unit Weight (kg)	0.23
Unit Weight (lbs.)	0.5
Housing	Metal
ENVIRONMENTAL	
Operating Temperature Range	32 to 122 F (0 to 50 C)
Storage Temperature Range	-4 to 158 (-20 to 70 C)
Relative Humidity	10% to 90% RH, Non-Condensing
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	300
Max 480P Range (ft)	300
Max 1440 x 900 Range (ft)	150
Max 480i Range (ft)	300
Max 640 x 480 Range (ft)	300
Max 800 x 600 Range (ft)	300
EDID Compatible	Yes
USB Extension Support	No
CONNECTIONS	
Ports	2
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	(2) HD15 (FEMALE)
FEATURES & SPECIFICATIONS	
Driver Required	No
Built-In Equalizer	Yes
STANDARDS & COMPLIANCE	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Certifications	Tested to FCC, RoHS, REACH
Approvals	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>