



CYBERMED H6

20" All-in-One Medical Grade PC



Display	<ul style="list-style-type: none"> 20-inch 16:9 widescreen (1920x1080) IP64 splash-proof & dustproof front bezel 	Webcam	<ul style="list-style-type: none"> 1.3 Megapixel Camera (Front-Facing)
CPU Support	<ul style="list-style-type: none"> 3rd generation Intel Core i3 & i5 processors 	Wall Mount	<ul style="list-style-type: none"> Supports 75mm & 100mm VESA mounting holes
I/O Ports	<ul style="list-style-type: none"> 2x USB 3.0 ports, 4x USB 2.0 ports 1x RS232, option to expand to 3 COM ports DVI-I Monitor Out Port HDMI Full 1080p 	Bios	<ul style="list-style-type: none"> AMI Flash BIOS supports ACPI, API, DMI, Plug & Play, and security password. Supports booting from HDD, PXE, LAN, CD-ROM, and ANY USB device. Has BIOS System POST and BIOS setup password protection.
Chipset	<ul style="list-style-type: none"> Intel H61 Express chipset (Sandy Bridge) 	Expansion Slots	<ul style="list-style-type: none"> Two Mini PCI-e (1x Full-Size and 1x Half-Size)
Memory	<ul style="list-style-type: none"> 2 x DDR3 204-pin SO-DIMM sockets, populated up to 8GB Max. Supports PC3-10600 1333MHz SO-DIMM 	HDD Support	<ul style="list-style-type: none"> 2x 6Gbps Serial ATA III ports 1x 3Gbps Serial ATA II port for optional Optical Drive
Operating System	<ul style="list-style-type: none"> Windows 8, Windows 7, XP, Linux 	Weight	<ul style="list-style-type: none"> 17 lbs
Video & Graphics	<ul style="list-style-type: none"> Intel HD Graphics 	Dimensions	<ul style="list-style-type: none"> 19.3" x 14.2" x 3.1" (L, W, D)
Networking	<ul style="list-style-type: none"> Dual Gigabit (Gbe) Fast Ethernet, Realtek RTL 8111E 	Colors	<ul style="list-style-type: none"> White with Antimicrobial Germ Protection
Audio	<ul style="list-style-type: none"> Realtek ALC892 High Definition Audio, Dolby Digital 5.1 surround sound, 10 channels of enhanced sound quality, multiple audio streams and jack re-tasking 	Power Supply	<ul style="list-style-type: none"> Medical Grade 180Watt AC Adapter. Input: universal 100 ~ 240V AC, 50-60Hz. Supports Output range: DC12V/19V. 5.0A/9.5A Adapters for Energy Star 5.0/UL
Environment	<ul style="list-style-type: none"> Ambient Temperature: 0°C ~ 50°C (operating) 	Relative Humidity	<ul style="list-style-type: none"> 10% ~ 90% (non-condensing)
Touch Screen	<ul style="list-style-type: none"> 5-Wire Resistive Technology supports up to 10 million touches 	Certifications	<ul style="list-style-type: none"> EN60601-1 medically certified, UL60950 electrical safety, FCC class B, CE, Energy Star 5.2, RoHs, WEEE
Wireless	<ul style="list-style-type: none"> Intel Centrino dual band a/g/n + Bluetooth 	Swivel Base	<ul style="list-style-type: none"> Optional desktop stand with Antimicrobial Germ protection with rotation function Left/Right plus tilt function Up/Down
Security Lock	<ul style="list-style-type: none"> Security lock slot located on the back of the system case 		