




Dimensions (unit : mm)




Summary

The VMAX960H is an advanced H.264 Stand Alone digital video recorder that records 480fps, Real-Time at 960H, D1, 2CIF, and CIF. All the great features, such as Panoramic Search, Single Channel Search in Playback, Single Touch Backup and Event management, can be controlled with the front panel, included USB mouse, or IR remote control. And with our special Image Enhancer, you can add the convenience of controlling cameras installed up to 6,000ft from the DVR, without losing clarity or quality. The DVR is available with basic storage from 1 to 16 terabytes.

Features

- Advanced H.264 Stand Alone DVR
- Multiplex - Live, Playback, Recording, Backup, Network, Configuration
- Record 30 Frames per Second on Every Channel
- One Touch Video Backup, Reverse Playback, & Emergency Recording
- Simple & Free DDNS Support
- Mirroring (RAID 0,1,10)
- Web-Based Client with Multi-User Access
- Scheduled Network Backup
- 8/16 Channels Looping Output
- S.M.A.R.T HDD Health Check with Email Notifications
- HDD Calculation and Auto Recording Configuration
- 16 Audio Input, 2 Audio Output
- 16 Sensor Input, 4 Relay Output
- Email & Text Event Notifications
- Watermark Verification (Digital Signature Verification)
- Help Menu on Major Functions
- Auto & Manual Firmware Upgrade Available
- USB Mouse, IR Remote Control, GUI
- Central Management Software, Up to 128CH
- Mobile Application for iPhone, iPad, iPod, Android Smart Phones and Tablets, and Kindle Fire
- MAC Compatible Remote Software

Available Models



Specifications

VIDEO		
Video Input	8/16 Channels	
Video Live	Framerate	1~30fps
	Resolution	960H, D1, 2CIF, CIF
Video Output	HDMI, Composite, VGA, SPOT	
Loop Output	8/16 Channels Looping Output	
Audio	8/16 Input	
	Output	2 Output
	Audio Codec	ADPCM
Alarm	Sensor Input	8/16 Input
	Alarm Out	4 Output
Operating System	Embedded Linux	
Serial	1xRS232, 2xRS485 for PTZ Camera & Controller, 2xUSB 2.0	
User Interface	Menu Display	Graphical User Interface (GUI)
	Control Methods	IR Remote Control, USB Mouse, Front Panel Buttons
Screen Display Mode	16CH: 1,4,9,16, Single Channel Playback, Sequence	
Screen Resolution	1080p, 720p, 1280X1024, 1024X768, 720X480 (NTSC), 720X576 (PAL)	
Performance		
Recording	Compression	H.264
	Recording Mode	Schedule, Event, Time-Lapse, Panic, Continuous, Pre & Post Event, Motion, Recording Configuration per Channel
	Pre Recording	0~10 Seconds
	Post Recording	10~10 Seconds
	Recording Rate	16CH: 480/ 400 fps (NTSC/ PAL) @ All Resolutions 8CH: 240/ 200 fps (NTSC/PAL) @ All Resolutions
	Recording Resolutions	Full 960H Real-Time Recording, 30fps @ All Resolutions
Playback	Playback Rate	16CH: 480/ 400 fps (NTSC/ PAL) @ All Resolutions 8CH: 240/ 200 fps (NTSC/PAL) @ All Resolutions
	Playback Resolution	Full 960H Real-Time Playback, 30fps @ All Resolutions
	Fast Forward Functions	x1/16, x1/8, x1/4, x1/2, x1, x2, x4, x8, x16, x32,
	Rewind Functions	First Data, Last Data, Frame-by-Frmee
	Search Modes	Date & Time, Record Table, Calendar, Event Preview, Bookmark, Play from Search, System & Event Logs
Storage	HDD Interface	Up to 4 HDD
	Program Memory	Built-in Flash (512Mb)
	Max. Internal HDDs	Up to 16TB (4HDD x 4TB)
	External Storage	USB Flash Drive, USB HDD, DVD
	CD/ DVD RW	Yes
	HDD Interface Type	SATA-II, SATA-III
	HDD Health Check	Temperature, S.M.A.R.T. with E-mail Notifications
Features	FaceStamp	Employee Management and Fraud Prevention
	Image Enhancer	Amplify signal up to 3,000ft (Cat5), 6,000ft (RG-59)
	Camera Color Control	Brightness, Contrast, Saturation, Hue
	Digital Zoom	Yes (Live & Playback)
	Software Upgrade	USB Flash Drive, Network Upgrade, FTP Remote Upgrade
	3G Mobile	Mobile App for Apple & Android Smart Phones & Tablets
	Covert Channel	Yes (Live & Playback)
Network		
Streaming	Network Connection	Ethernet (1 x Gigabyte 10/100/1000 Mbps)
	Transmission Speed Live	480/400 fps @ D1 (NTSC/ PAL)
	Protocols	Static, DDNS, DHCP
Access	Web Viewer	Live, Playback, & Config. up to 10 multiple connections
	Client Monitoring Software	ACS (Client S/W), MAC (Apple S/W), Pivot (CMS S/W)
General		
	Operating Temperature/ Humidity	5 ~ 40°C (41 ~ 104°F)
	Operating Humidity	Less than 80% (Non-Condensing)
Electrical	Power Requirement	12V 9A D/C
	Power Consumption	108W
	Dimensions	18.89 X 3.46 X 17.57 in (430 X 88 X 446.5mm)
	Weight	13.84lb (6.28kg)

*Specification is subject to change without prior notice.