

Wireless AC600 Dual-Band USB Mini Adapter

GWU635



- 802.11ac Wireless Dual-Band USB Mini Adapter
- Supports speeds of up to 433Mbps on 5GHz and 150Mbps on 2.4GHz networks
- Supports WEP, WPA, WPA2, TKIP, and AES encryption
- Push-button Wi-Fi Protected Setup™ (WPS) simplifies secure connections to existing Wi-Fi networks
- Works with 802.11a/b/g/n routers and access points
- Convenient LED status indicator

Wi-Fi USB Mini Adapter with Wireless 802.11ac

The capabilities of legacy Wi-Fi are being surpassed because of the requirements of HD video streaming, large file downloads and intense online gaming. With IOGEAR's Wireless AC600 Dual-Band USB Mini adapter you can now enjoy the power of next-generation Wi-Fi technology. Using the latest 802.11ac wireless standard, experience data rates of up to 433Mbps on 5GHz with compatible 802.11ac routers.

Dual-Band 5GHz / 2.4GHz

As more technology products entering the market with Wi-Fi capabilities, your Wi-Fi network is becoming more congested. With the Wireless AC600 Dual-Band USB Mini Adapter, you can enjoy greater bandwidth and less network interference.

- 5GHz band provides 433Mbps which means faster downloads, seamless HD streaming, and robust online gaming.
- 2.4GHz provides up to 150Mbps great for internet surfing, social networking and email.

Wi-Fi Protected Setup™ (WPS) Support

Enjoy the simplicity of connecting to your network with the push of a button. IOGEAR's Wireless Dual-Band Wi-Fi Adapter supports Wi-Fi Protected Setup (WPS), giving you the capability of conveniently connecting to your network with all your personal security presets.



Wireless AC600 Dual-Band USB Mini Adapter

How does it work?

Connect the GWU635 Wi-Fi Adapter to a USB port on your computer

Connect to your wireless 802.11ac* router

Enjoy faster downloads, seamless HD streaming, and robust online gaming!



Dual-Band
Wireless AC Router

Downloads, HD videos,
gaming, and more



GWU635

*For optimal performance

Product Requirements

- Operating System
- Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1
- Hardware
- USB 2.0+ Port

Package Contents

- 1 x GWU635 Wireless AC600 Dual-Band USB Mini Adapter
- 1 x Driver Installation CD
- 1 x Quick Start Guide
- 1 x Warranty Card

Wireless AC600 Dual-Band USB Mini Adapter

Specifications

Function	GWU635	Dimensions	GWU635
Frequency Band	2.412~2.484GHz 4915 ~ 5850MHz	Unit Dimensions	
Standards	IEEE 802.11ac, IEEE802.11a/b/g/n	Height	1.125" (2.86cm)
Data Rate	5GHz: Up to 433Mbps(dynamic); 2.4GHz: Up to 150Mbps (dynamic)	Depth	0.375" (0.95cm)
Management	Windows based Utility	Length	0.625" (1.59cm)
Security	64/128-bit WEP, AES, TKIP, WPA, WPA2, 802.1x, WPA-PSK, WPA2-PSK, MAC, WDS	Inner Pack	
Interface	USB 2.0+	Width	6.75" (17.15cm)
Antenna Type	1T1R	Height	4.5" (11.43cm)
Transmission Power	<20dBm (EIRP)	Depth	7.375" (18.73cm)
Sensitivity	Range: -90dBm ~ -65dBm	Inner Pack Qty.	6
Modulation	DBPSK, DQPSK, CCK, OFDM, 16-QAM, 64-QAM	Unit Package Dimensions	
LEDs		Width	3.75" (9.53cm)
Link	Green	Height	6.75" (17.145cm)
Environment		Depth	1" (2.54cm)
Operation Temperature	0℃~40℃ (32°F~104°F)	Master Carton	
Storage Temperature	-40℃~70℃ (-40°F~158°F)	Width	8.5" (21.59cm)
Humidity	Relative Humidity (Operational) 10%~90% non-condensing; Relative Humidity (Storage) 5%~90% non-condensing	Height	8" (20.32cm)
Operating Range	100-300m, depending on surrounding environment	Depth	10.375" (26.35cm)
USB Specification	USB 2.0	Master Carton Qty.	12
		Weight	
		Master Carton Wt.	2.70 lb (1.22 kg)
		Inner Pack Wt.	1.00 lb (0.46 kg)
		Unit Pack Wt.	0.10 lb (0.06 kg)