

Outdoor iSecurity Camera with Built-in 8GB Memory

Introducing the new **IPcam-SDII**; a new and improved internet protocol camera from SecurityMan to fit your security needs. This weatherproof camera is an ideal camera that allows you to monitor your home or business with HD video resolution and enhance night vision up to 60ft. Its wireless capability allows you to connect to the internet and view your camera using your mobile device from anywhere in the world. The camera comes with an 8GB SD Card memory already built-in. Whether it is viewing from a remote location or local area, this camera is essential to your security needs.



Wi-Fi

1

Download the Free App



2

Connect the Camera
& Scan the QR Code



3



Detect & Monitor



Or QUAD Screen

Features:

- Plug&Play / QR Code Setup
- Built-in 8GB memory for 5hr of video recording (upgradeable to 32GB for 20hr of recording)
- HD 1280 x 720 at 30fps clear video quality
- Infrared LED lights enables night vision coverage up to 60 feet
- Enhanced IR cutter for better outdoor color image
- Advanced H.264 video compression for smoother video streaming and smaller file size
- 2-in-1 Design: Wired Ethernet or Wireless Wi-Fi
- Supports private recording options (motion detection, manual, or schedule recording) to built-in memory or remote PC
- Email and phone alarm alerts
- Remote monitoring from Smartphone, Tablet, MAC, or PC
- Point-to-point service for easy remote access without network knowledge or configuration
- Free CMS software for remote access/control, record/playback, and monitor up to 64 IP cameras
- Supports up to 10 login users at the same time

Package Contents:

- IPCam-SDII main unit
- Power adapter
- Ethernet cable
- Mounting Bracket
- Mounting screws
- QSG (quick start guide)
- CD (PC software and manual)

Key Specifications:

Camera	Image Sensor	1/4" Megapixel CMOS, Color
	Video Standard	NTSC
	Lens	8mm
	Minimum Illumination	0.1 Lux (IR OFF), 0 LUX (IR ON)
	Frame Rate	30fps (NTSC)
	Resolution	1280 x 720
	IR Cut Filter	Yes (For better outdoor color image)
	Night Vision	Up to 60 feet
	Dimension (L x D)	4.5" x 3.0" (camera only)
	G.W/N.W	3.0lbs/1.5lbs (camera/bracket/antenna/visor)
Recording/ Playback	Video Compression	H.264 high profile / Snapshot: JPEG, BMP
	Recording Mode	Motion detection, manual, and schedule
	Indoor/outdoor usage	Both
	Operating temperature	14° -122° Fahrenheit
	Humidity	95% Relative Humidity
	Power	Input: 100-240VAC, Output: 12VDC, 2.0A
	Storage	Internal 8GB built-in. Optional upgrade up to 32GB SD card
	Backup	Remote back up to PC
	Playback	Playback via SD Card; Playback via remote devices/CMS
Alarm	Motion Detection	Video Motion Detection
	Alarm Actions	Email photo, record video/photo to FTP, record video/photo to SD
Network	Network Interface	10/100 Base Ethernet (for wired network connection)
	Wireless Network	Wi-Fi 802.11 b/g/n
	IP Mode	Dynamic IP address; static IP address
	Online Users	Up to 10 users
	Mobile Surveillance	iPhone, Android
	Internet Viewing	Supports browsers: Internet Explorer, Firefox, & Safari
	Remote Access	Yes
Software	CMS Software	Computer software used to setup recording, remote monitoring, remote access and control, search and playback, and up to 64 multiple cameras surveillance
	User Levels For CMS	Administrator, Normal, & Guest (viewing only)
	Camera Naming	Customize each camera's name
	Video Adjustment	Brightness, contrast, & saturation
	Video Bit Rate	1024 Kbps - 4096 Kbps
	Password Protection	Yes
CPU & System	Operating System	Embedded Linux OS
	Micro Processor	32Bit RISC embedded processor
	System Requirement	Microsoft Windows XP, Vista, 7, & 8