



C2783FQ

16.7M colors	DCR	D	e	e-saver	hairline texture	HDMI	i-menu
LED	MHL	narrow bezel	windows 8				

MODEL: C2783FQ DATA SHEET

GENERAL FEATURES

panel type:	
screen size:	27"
viewable image size:	27"
aspect ratio:	21:9
brightness:	300 cd/m2
contrast ratio (DCR):	50,000,000:1
pixel pitch (H x V):	0.233 x 0.233 mm
display area (H x V):	597.88 x 336.31 mm
viewing angle:	horizontal ° x vertical 178° (CR >= 10)
response time:	5 ms
color:	black

SCANNING FREQUENCY

scanning frequency:	horizontal: Hz vertical: 50~75 Hz
---------------------	--------------------------------------

RESOLUTION

max resolution:	1920 x 1080 @ 60 Hz
recommended resolution:	1920 x 1080 @ 60 Hz
color resolution:	16.7 million

POWER

power source:	110~240VAC
power consumption:	ON: <18 W STANDBY: <0.5 W

OTHER FEATURES

user control:	
plug and play:	NA
speakers:	
web cam:	no
headphone out:	NA
wall mount:	NA
height adjustable:	NA
tilt:	-3° ~ 21°

SIGNAL INPUT

analog D-sub 15 pin:	1 x VGA
DVI-D 24-pin:	1 x DVI-D
HDMI:	0 x HDMI
HDMI w/MHL:	1 x HDMI w/MHL
USB 2.0:	0 x USB 2.0
USB 3.0:	0 x USB 3.0
display port (in):	1 x DP (in)
display port (out):	0 x DP (out)
support MHL:	NA

REGULATIONS

CE, FCC, RoHS Compliant, cTUVus

SOFTWARE

i-Menu / e_Saver /

IN THE BOX

VGA Cable, Power Cord, User Manual, Warranty Card, Driver, AOC Software, Audio Cable

LOADING QUANTITY

20' container loading w/ pallet:210
40' STD container loading w/ 450
pallet:

DIMENSIONS

product with stand (WxHxD):
631.1mm x 461mm x 175.2mm
24.8" x 18.15" x 6.9"

packaging (WxHxD):
754mm x 225mm x 582mm
29.68" x 8.86" x 22.91"

weight (NET):	5.83 kg 12.85 lbs
weight (GROSS)	8.6 kg 18.95 lbs
warranty:	3 years
UPC code:	685417703685