



# CC8370-HV

## Anti-Ligature Fisheye Network Camera



3MP · WDR Pro · 3DNR · 180° Panoramic View · IK10 ·  
IP66 · SNV · Anti-Ligature · Anti-Grip


VIVOTEK's CC8370-HV is a vandal-proof fisheye network camera offering up to 30 fps at 3-Megapixel resolution. With its unique anti-grip design and inconspicuous appearance, the CC8370-HV plays a life secure guard role in unique security environments. Without ligature edges, it will effectively eliminate self-harm and suicide happen, ideal for detention house, holding cells, psychiatric ward, mental hospital, and correctional institution. Featuring 180° horizontal panoramic views with adjustable 25° tilt angle, the camera allows users amazing flexibility of viewing angles and options. The camera's weather-proof compact size also makes it an ideal choice for indoor and outdoor scenario such as boutique, convenience store, bank, school, parking lot and street.

The CC8370-HV can view at a wide angle of 180 degrees, providing complete video security with no dead angles. Featuring WDR Pro, the camera captures both the dark and bright areas of an image and combines the differences to create a highly realistic representation of the original scene. Further, with added SNV technology, high-quality full-color surveillance video becomes possible even under low-light conditions. These combined features enable the camera to provide video quality remarkably close to the capabilities of the human eye. When installing the unit, the unique mounting design facilitates easy installation on a wall or desktop in order to capture faces at eye level. Further increasing the level of surveillance, a built-in microphone which records sound within a 5 meter radius.


The CC8370-HV also supports the industry-standard H.264 compression technology, drastically reducing file sizes and conserving valuable network bandwidth. Together with the ST7501 multi-lingual 32-channel recording software, users can simply and quickly set up an easy-to-use IP surveillance system.

### Key Features


- 3-Megapixel CMOS Sensor
- 30fps @ 2048x1536
- Anti-Ligature Design
- Weather-proof IP66-rated and Vandal-proof IK10-rated Housing
- 180° Horizontal Panoramic View
- ±25° Tilt Lens
- WDR Pro (100dB) to Provide Extreme Visibility in High Light Contrast Scenes
- Video Rotation
- Built-in Microphone
- SNV (Supreme Night Visibility)
- 3D Noise Reduction for Low-light Conditions
- Real-time H.264 and MJPEG Compression (Dual Codec)
- Built-in IEEE 802.3af Compliant PoE
- Built-in MicroSD/SDHC/SDXC card slot



The World's First Adjustable Tilt Angle Fisheye Network Camera



Holding Cell



Prison





Psychiatric Ward



Retail Store

## Technical Specifications

Model	CC8370-HV	Interface	10Base-T/100BaseTX Ethernet (RJ-45) *It is highly recommended to use standard Cat. 5e & Cat. 6 cables which are compliant with the 3P/ETL standard.
<b>System Information</b>		ONVIF	Supported, specification available at <a href="http://www.onvif.org">www.onvif.org</a>
CPU	Multimedia SoC (System-on-Chip)	<b>Intelligent Video</b>	
Flash	128 MB	Video Motion Detection	Five-window video motion detection
RAM	256 MB	<b>Alarm and Event</b>	
<b>Camera Features</b>		Alarm Triggers	Video motion detection, manual trigger, periodical trigger, system boot, recording notification, camera tampering detection, audio detection
Image Sensor	1/3 Progressive CMOS	Alarm Events	Event notification using HTTP, SMTP, FTP, NAS server and SD Card File upload via HTTP, SMTP, FTP, NAS server and SD card
Maximum Resolution	2048x1536	<b>General</b>	
Lens Type	Fixed-focal	Connectors	RJ-45 for Network/PoE connection
Focal Length	1.6 mm	LED Indicator	System power and status indicator
Aperture	F2.0	Power Input	IEEE 802.3af PoE Class 1
Field of View	180° (horizontal) 130° (vertical) 180° (diagonal)	Power Consumption	PoE Max. 4.9 W
Shutter Time	1/5 sec. to 1/32,000 sec.	Dimensions	115 (D) x 65 (W) x 59 (H) mm
WDR Technology	WDR Pro	Weight	Net: 331g
Minimum Illumination	0.05 Lux @ F2.0 (Color)	Casing	IP66, IK10
Pan/tilt/zoom Functionalities	ePTZ: 4x digital zoom IE plug-in	Safety Certifications	CE, LVD, FCC Class B, VCCI, C-Tick, UL
On-board Storage	MicroSD/SDHC/SDXC card slot	Operating Temperature	Starting Temperature: -10°C ~ 50°C (14°F~ 122°F) Working Temperature: -20°C ~ 50°C (-4°F~ 122°F)
<b>Video</b>		Warranty	24 months
Compression	H.264 & MJPEG	<b>System Requirements</b>	
Maximum Frame Rate	30fps @ 2048x1536	Operating System	Microsoft Windows 8/7/Vista/XP/2000
Maximum Streams	3 simultaneous streams	Web Browser	Mozilla Firefox 7~10 (streaming only) Internet Explorer 7/8/9/10
S/N Ratio	58.8 dB	Other Players	VLC: 1.1.11 or above Quicktime: 7 or above
Dynamic Range	100 dB	<b>Included Accessories</b>	
Video Streaming	Adjustable resolution, quality and bitrate	Others	Quick installation guide, warranty card, mounting bracket, screw pack
Image Settings	Adjustable image size, quality and bit rate; Time stamp, text overlay, flip & mirror & rotate; Configurable brightness, contrast, saturation, sharpness, white balance, exposure control, gain, backlight compensation, privacy masks; Scheduled profile settings	<b>Dimensions</b>	
<b>Audio</b>		 	
Audio Capability	Audio input		
Compression	G.711, G.726		
Interface	Buit-in Microphone		
Effective Range	5 meters		
<b>Network</b>			
Users	Live viewing for up to 10 clients		
Protocols	IPv4, IPv6, TCP/IP, HTTP, HTTPS, UPnP, RTSP/RTP/RTCP, IGMP, SMTP, FTP, DHCP, NTP, DNS, DDNS, PPPoE, CoS, QoS, SNMP, 802.1X, UDP, ICMP, ARP, SSL, TLS		

All specifications are subject to change without notice. Copyright © VIVOTEK INC. All rights reserved.

Ver. 14



**VIVOTEK INC.**

6F, No.192, Lien-Cheng Rd., Chung-Ho,  
New Taipei City, 235, Taiwan, R.O.C.  
T: +886-2-82455282 F: +886-2-82455532  
E: [sales@vivotek.com](mailto:sales@vivotek.com)

**VIVOTEK USA**

2050 Ringwood Avenue,  
San Jose, CA 95131  
T: 408-773-8686 F: 408-773-8298  
E: [salesusa@vivotek.com](mailto:salesusa@vivotek.com)

**VIVOTEK Europe**

Randstad 22-133, 1316BW Almere,  
The Netherlands  
T: +31(0)36-5298-434  
E: [saleseurope@vivotek.com](mailto:saleseurope@vivotek.com)

**VIVOTEK India**

602, Best sky Tower, Plot No. F-5,  
Netaji Subhash Place, Pitam Pura, Delhi-110 034  
T: +91-11-45137465  
E: [salesindia@vivotek.com](mailto:salesindia@vivotek.com)