

# LG FULL HD SIGNAGE MONITOR SE3KB SERIES 65SE3KB



## FEATURES:

- 65" IPS Panel with Slim Design
- Wi-Fi Compatible and SNMP Support
- USB Cloning
- Ideal for Offices, Restaurants and Retail
- Native Resolution : 1920 x 1080 (Full HD)
- Aspect Ratio : 16:9
- Brightness : 400cd/m<sup>2</sup>
- Contrast Ratio : 1,300:1
- Orientation: Portrait and Landscape
- Viewing Angle (H x V) : 178° x 178°



\*LED LCD Monitors combine LCD screen with LED back light technology

[www.lg.com.au](http://www.lg.com.au)

# Technical Data

## 65SE3KB



<b>PANEL</b>	
Screen Size	65" (164cm)
Panel Technology	IPS
Aspect Ratio	16 : 9
Native Resolution	1920 x 1080 (Full HD)
Brightness	400cd/m <sup>2</sup>
Contrast Ratio	1,300 : 1 (Native)
Dynamic CR	500,000 : 1
Operating Hours	18 Hours / Day
Viewing Angle (H x V)	178° x 178°
Orientation	Portrait and Landscape
Surface Treatment	Hard coating(3H), Anti-glare treatment (Haze 1%)
<b>CONNECTIVITY</b>	
Input (Rear)	HDMI(1), DVI-D(1), Support HDCP
Digital	
Analogue	RGB (1)
Audio	Yes (1)
External Control	RS232C (1), IR receiver (1)
USB	Yes (2, USB2.0)
Wi-Fi	Dongle Compatible
SD Card	-
Wired LAN	RJ45 (1)
Output (Rear)	-
Digital	Yes (1)
Audio	RS232C (1)
External Control	
<b>PHYSICAL SPECIFICATIONS</b>	
Bezel Width	11.9mm(T/R/L), 18mm(B)
Monitor Dimension (W x H x D)	1457mm x 838mm x 56.5mm
Dimension with optional stand (W x H x D)	1457mm x 898mm x 294mm
Carton Dimensions (W x H x D)	1561mm x 951mm x 170mm
Weight (head)	27.9kg
Weight(head+stand)	32.9kg
Packed Weight	33.8kg
VESA™ Standard Mount Interface	300 x 300 mm
<b>SPECIAL FEATURES</b>	
Additional	Temperature Sensor, Auto Config/Phase, SNMP Support, Input Label, Contents Scheduling, DPM Select, Holiday Schedule, Smart Energy Saving, File Play with USB, USB Cloning, Built-in Speakers (10W x 2), PM Mode, Tile Mode, Lock Mode
<b>ENVIRONMENT CONDITIONS</b>	
Operation Temperature	0 °C to 40 °C
Operation Humidity	10 % to 80 %
<b>POWER</b>	
Power Supply	100-240V~, 50/60Hz
DPM	0.7W
Typical / Smart Energy Saving on	95W/70W
Power Off	0.5W
Power Type	Built-In-Power
<b>STANDARD (CERTIFICATION)</b>	
Safety	UL/cUL/CB/TUV/KC
EMC	FCC Class "A"/CE/KCC, C-tick
ErP/US EPA	Yes / Yes (Energy Star 6.0)
<b>MEDIA PLAYER COMPATIBILITY</b>	
External Media player Attachable	Yes (MP500/MP700)
<b>SOFTWARE COMPATIBILITY</b>	
SuperSign-w lite / SuperSign-c	Yes / Yes (Via Software Download)
<b>ACCESSORIES</b>	
Included	Remote Controller (including 2ea battery), QSG, Power Cable, RGB Cable, Regulation Book, Phono to RS232C Gender, IR Receiver
Optional	Stand (ST-652T), Wall bracket (LSW350B), VESA Adapter (AM-B330S), Media Player, Wi-Fi Dongle Kit (AN-WF500)
Warranty	3 Years (Parts & Labour)

Disclaimer: All product specifications correct at time of printing. Specifications may change without prior notice.

[www.lg.com.au](http://www.lg.com.au)

