



## Features and Specification

- Wireless 2.0 channel speakers with rechargeable battery
- Pressure-driven liquid visual effects and multi-LED lighting effects
- Left and right speakers deliver big sound from 40 mm full-range drivers
- Connects via Bluetooth® or 3.5mm AUX audio cable
- Accessories included: USB cable, AUX cable
- Power: Rechargeable battery (800 mAh), USB charge (DC 5V)

### SPECIFICATIONS

- **Output Power (RMS):** 6W total (2 x 3W)
- **Frequency Response:** 100-18,000 Hz
- **Removable Media Support:** --
- **Media Formats:** --
- **Radio Tuner:** --
- **Wireless Source:** Bluetooth® 2.1 +EDR
- **Input:** 3.5mm AUX audio
- **Power Source:** Rechargeable battery (800 mAh), USB charge (DC 5V)
- **Battery Life\*:** 2 hours
- **Accessories Included:** 3.5mm AUX cable, USB charge cable
- **Package Type:** Gift box

\* Estimated time; battery life will vary depending on use conditions.

## Product Details

<b>Model</b>	NAS-3058
<b>Barcode</b>	Black 840005009369
<b>Unit</b>	
Dimensions (in)	3.25 x 3.25 x 8.85 [L x W x H]
Weight (lbs)	1.05
<b>Giftbox/Clamshell</b>	
Dimensions(in)	7.1 x 4.0 x 9.45 [L x W x H]
Weight(lbs)	1.47
<b>Master Carton</b>	
Dimensions (in)	14.9 x 9.0 x 10.5 [L x W x H]
Weight (lbs)	7.24
# Of Units/per	N/A
<b>Inner Carton</b>	
Dimensions (in)	N/A x N/A x N/A [L x W x H]
Weight (lbs)	N/A
# of Units Per Inner Carton Color1	4 Black
<b>Loading Qty/Container</b>	
20	4,917
40	10,780
40HQ	12,293
<b>Number of units/standard pallet</b>	N/A

Product URL: <http://www.naxa.com/nas-3058.html>

Feature, specifications, measurements and weight may be subject to change without prior notice