

ZuM™ Monaural and Binaural USB Headsets

Single Ear Monaural and Dual Ear Binaural USB, LYNC Headsets



Monaural Headset



Binaural Headset

Comfort and Durability

Call center tested, for durability. The hexagon-shape enhanced structural design gives maximum strength against bending and physical damage. Designed for extensive use, the large speaker chambers cover most ear sizes comfortably.

Both Headset Models Feature:

- Over-the-Head Monaural and Binaural versions.
- Powerful 40mm speakers for top quality sound.
- Durable structural design that is ideal for extensive use situations.
- Large, comfortable ear pads.
- Bendable microphone arm for infinite adjustments.
- The 5 Watt speaker can generate volume up to 90dB.
- Noise canceling microphone.
- Acoustic shock protection.
- UC compatible: LYNC, Avaya, Cisco, IBM and more.

Performs well in the Harshest Conditions

Not only are they durable, they provide noise canceling for use in busy environments and padded ear covers offer comfort in situations that require many hours of use. Built-in Acoustic Shock Protection (ASP) provides a circuit-breaker-type protection against sudden loud noise from the speaker source.

	Monaural	Binaural
Part	ZUMUC1	ZUMUC2
UPC	800807320253	800807320277
MSRP	\$69.99	\$79.99

ZüM™ Monaural and Binaural USB Headsets

Single Ear Monaural and Dual Ear Binaural USB, LYNC Headsets

Package Includes



Monaural



Binaural



Controller

Specifications

FEATURES

- Over-the-Head Monaural and Binaural versions
- Powerful 40mm speakers for top quality sound
- Durable structural design
- Large, comfortable ear pads
- Bendable microphone arm for infinite adjustments
- The 5 Watt speaker can generate volume up to 90dB
- Noise canceling microphone
- Acoustic shock protection
- UC compatible: LYNC, Avaya, Cisco, IBM and more

TECHNICAL SPECIFICATIONS

- Speaker size: 1.57" (40mm) Diam
- Sensitivity: 97dB ± 3dB (SPL/100mV@1K Hz)
- Microphone Sensitivity: -61dB ± 3dB
- Impedance: 160Ω ± 20%
- Frequency Response: 200–5000Hz

PHYSICAL SPECIFICATIONS

- Dimensions: 8" x 6.67" x 2.4" (20cm x 17cm x 6cm)
- External Microphone dimension: .23" x .2" (6 x 5mm)
- Weight: 50g
- Cord Length: 5' (1.5m) normal, 9.8' (3m) extended

CONTROLS

- Volume UP/DOWN
- Microphone ON/OFF

PACKAGING

- Type: Retail Clamshell Container
- Dimensions: 7.5" x 10" x 2" (190 x 254 x 51mm)

COMPATIBILITY

