

## HDBaseT HDMI over Cat5e/6/6a Extender Kit with Power and IR Control, 4K x 2K 30 Hz UHD / 1080p 60 Hz, Up to 328 ft. (100 m)

MODEL NUMBER: BHDBT-K-PI-LR



Extends HDMI video/audio and IR control signals with Power over a single Cat5e/6/6a cable to a projector, monitor or television up to 328 ft. from the source.

### Description

The BHDBT-K-PI-LR HDBaseT HDMI over Cat5e/6/6a Extender Kit extends uncompressed HDMI audio and video and IR remote control signals up to 328.08-ft. (100 m) over a single Cat5e/6/6a cable, including an Ultra High Definition (UHD) 4096 x 2160 or 3840 x 2160 (4K x 2K) @ 30Hz signal.

In addition to HDMI and IR signals, this extender kit features built-in PoE technology, which powers the receiver over Cat5e/6/6a cable, eliminating the need for an external power source. The two-way IR remote control feature (@ 39 KHz) lets you control your Blu-ray player or other HDMI source using its remote when at the remote monitor or control your remote monitor using its remote when at the Blu-ray player. Locking HDMI ports (ideal for use with Tripp Lite's P569-006-LOCK high-speed HDMI cables with locking connectors) on both the transmitter and receiver prevent cables from coming loose or undone, ensuring an intact signal.

The plug-and-play BHDBT-K-PI-LR supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio, as well as 3D video, EDID and HDCP. Attach the transmitter and receiver units to a wall, rack or pole with the included mounting hardware.

### Features

#### Extends HDMI Video/Audio and IR Control Signals with Power Over a Single Cat5e/6/6a Cable

- Ideal for digital signage, classrooms, retail locations, conference rooms and trade show booths
- Extends an Ultra High Definition (UHD) 4096 x 2160 or 3840 x 2160 (4K x 2K) @ 30Hz signal up to 328.08-ft. (100 m)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio

### Highlights

- Ideal for digital signs, classrooms and trade show booths
- Extends both a 4096 x 2160 and 3840 x 2160 (4K x 2K) @ 30Hz signal up to 328.08-ft. (100 m)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD
- Built-in PoE technology powers receiver over Cat5e/6/6a cable
- Plug and play—no software or drivers to install

### Package Includes

- Transmitter unit
- Receiver unit
- IR-IN cable, 5-ft. (1.52 m)
- IR-OUT cable, 6-ft. (1.83 m)
- External Power Supply with C14 inlet (Input: 100-240V, 50/60 Hz, 1.5A; Output: 48V, 1A), 4.5 ft. (1.37 m)
- C13 to NEMA 5-15P power cord, 6-ft. (1.83 m)
- Mounting hardware
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

- Supports 3D video, EDID and HDCP
- Reduces cable clutter and installation costs
- Built-in PoE technology powers receiver over Cat5e/6/6a cable, eliminating need for external power source

#### Controls IR Devices

- 2-way 39 KHz IR remote control functionality lets you control your Blu-ray player with its remote while standing at the remote monitor (and vice versa)

#### Locking HDMI Ports on Transmitter and Receiver

- Prevent cables from coming loose or disconnected, ensuring an intact signal
- Ideal for use with Tripp Lite's P569-006-LOCK high-speed HDMI cables with locking connectors

#### Easy to Set Up and Use

- Plug and play with no software or drivers to download and install
- Includes mounting hardware for attaching each unit to a wall, rack or pole

#### TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332186942
Product Type	Extender Kit
AC Adapter	Input: 100-240V, 50/60Hz, 1.5A; Output: 48V, 1A, 4.5 ft.
Technology	HDBaseT; HDMI; IR; Cat5/5e; Cat6; POC
VIDEO	
Max Supported Video Resolution	3840x2160 (4K @ 30Hz)
Max 720P Range (ft)	328
Max 1080P Range (ft)	328
Max 1280 x 720 (720p) Range (ft)	328
Max 1920 x 1080 (1080p) Range (ft)	328
Max 1920 x 1200 Range (ft)	328
Max 2560 x 1600 Range (ft)	328
Max 3840 x 2160 (4K@30Hz) Range (ft)	328



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Transmitter Video Input	HDMI
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Signal Range (ft)	328
Signal Range (m)	100
Recommended Cabling	HDMI
Max Supported Color Depth	36-bit Deep Color
3D Video Supported	Yes
<b>AUDIO</b>	
Audio Input	HDMI
Audio Output	HDMI
Audio Specification	7.1 Channel Surround Sound, DTS-HD and Dolby TrueHD
<b>POWER</b>	
Power Source	Transmitter end only (Included)
Power Source Type	AC Adapter with detachable power cord
AC Plug Type	NEMA 5-15P
External Power Supply Input Specs (V / Hz / A)	100-240V / 50-60Hz / 2.0A
External Power Supply Output Specs (V / A)	48V/1.04A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.4
External Power Supply Certifications	UL; cUL; PSE; FCC; CE; TUV; LPS; RoHS; WEEE
Power Over Cable (PoC) Support	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	RJ45 INPUT/OUTPUT (GREEN / POWER, ORANGE / LINK) ACTIVITY (FLASHING ORANGE WHEN TX/RX POWERED AND CONNECTED) HDMI LINK (GREEN WHEN SIGNAL IS BEING SENT FROM SOURCE TO DISPLAY) POWER (GREEN)
<b>PHYSICAL</b>	
Color	Black
Included Mounting Accessories	Wallmount
Number of Displays	1
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket <a href="http://www.tripplite.com/din-rail-mounting-bracket-for-digital-signage-version-2-B110-DIN-02">B110-DIN-02</a>



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Form Factor/Mounting Options	Box; Wall-mount
Receiver Unit Dimensions (hwd / in.)	3.97 x 5.04 x 1.17
Receiver Unit Weight (lbs.)	1.7
Shipping Dimensions (hwd / cm)	21.41 x 15.01 x 8.10
Shipping Dimensions (hwd / in.)	8.43 x 5.91 x 3.19
Shipping Weight (kg)	1.34
Shipping Weight (lbs.)	2.95
Transmitter Unit Dimensions (hwd / in.)	3.97 x 5.04 x 1.17
Transmitter Unit Weight (lbs.)	1.7
Unit Dimensions (hwd / in.)	3.97 x 5.04 x 1.17
Unit Packaging Type	Box
Unit Weight (kg)	0.77
Unit Weight (lbs.)	1.7
Housing	Metal
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104 F (0 to 40)
Storage Temperature Range	5 TO 122F (-15 TO 50 C)
Relative Humidity	0% TO 85% RH, Non-Condensing
Operating Humidity Range	0% TO 85% RH, Non-Condensing
Storage Humidity Range	0% TO 85% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Max 1024 x 768 Range (ft)	328
Max 480P Range (ft)	328
Max 1440 x 900 Range (ft)	328
Max 1080i Range (ft)	328
Max 1920 x 1440 Range (ft)	328
Max 4K UHD Range (ft)	328
Max 480i Range (ft)	328
Max 640 x 480 Range (ft)	328
Max 800 x 600 Range (ft)	328
Max 1600 x 1200 Range (ft)	328
Max 2048 x 1536 Range (ft)	328
EDID Compatible	Yes



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

IR Remote Extension Support	Yes
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
<b>CONNECTIONS</b>	
Ports	1
Side A - Connector 1	HDMI (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	1.4
Driver Required	No
Built-In Equalizer	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>