

IZ2/UD2-Series



PROFILE

So much more than you might think! Our affordable, space- and energy-saving hardware series sets new benchmarks for entry-level devices. These compact devices offer high-level performance, including for basic multimedia applications. Four USB ports and two digital monitor connections ensure a wide range of desktop usage options, including Dualview. For additional space savings, the IZ2/UD2 can be VESA mounted on the back of the monitor.

FEATURES AND BENEFITS

► Slim Design

The perfect companion for any workplace due to the small form factor and the latest design.

► Excellent price performance

Very affordable price as Zero Client as well as Universal Desktop Thin Client.

► Dualview support

Direct connectivity for a second monitor via additional DVI port. No adapter or extra cable required.

► VESA mountable (optional)

Mountable on the back of a monitor with the optional available VESA bracket, ideal for space constrained environments.

► No moving parts, e.g. cooling fans

The absence of moving parts means the devices are almost noiseless and fail-safe with minimal heat generation.

► Free evaluation:

www.igel.com/evaluation



DEVICES

Zero Clients

IZ2 HDX
IZ2 RFX
IZ2 Horizon

Universal Desktop

UD2 LX

Free evaluation:

www.igel.com/evaluation

COLOR



black

PERIPHERAL INTERFACES



IGEL IZ2/UD2 SPECIFICATIONS

SYSTEM	
Available Operating Systems	IGEL Linux v5 (LX)
Management	IGEL Universal Management Suite included
Form Factor	Standard Desktop
Processor	Intel E3815 1.5GHz Single-Core
Chipset	Intel Bay Trail SoC
MEMORY	
RAM (DDR3L)	2 GB
Flash Memory	2 GB
GRAPHICS	
Chipset	Intel HD Graphics
Video Memory	64 – 256 MB shared memory
Ports	1 x DVI-I, 1 x DVI-D
Supported Resolutions	max. 1920 x 1200, Dualview
NETWORK	
Ethernet	10/100/1000
AUDIO	
Chipset	High Definition Audio
Ports	Front: 1 x line-out, 1 x mic-in
Speakers	1 x internal
PERIPHERAL INTERFACES	
Serial	Optional, via USB-to-Serial adapter
Parallel	Optional, via USB-to-Parallel adapter
USB 2.0	3 x back
USB 3.0	1 x front
Kensington Lock	1 x back
DIMENSIONS	
Device (D x W x H), upright	205 x 63 x 194 mm with foot, 200 x 48 x 182 mm without foot
Packaging (D x W x H), horizontal	275 x 95 x 260 mm
Weight (without foot)	0.9 kg
ENVIRONMENT	
Cooling	Fanless convection
Operating Temperature	0° to 40° C (vertical) 0° to 35° C (horizontal, with rubber feet)
Operating Humidity	10% – 80%, non-condensing
POWER	
Input	Auto sensing 100~240VAC / 50~60Hz
Power Supply	External
Power Consumption: Idle / Sleep Mode	5W / 1W
OPTIONS	
VESA Mount	For mounting on the back of a monitor
Rubber Feet	For horizontal placement of the device
USB-to-Serial Adapter	For connecting peripherals that require a serial port
USB-to-Parallel Adapter	For connecting printers that require a parallel port
Shared WorkPlace (only UD2)	It allows user-dependent configuration based on setting profiles

All IGEL clients come with a standard two-year warranty (starting from the date of delivery). Take advantage of our free online registration and, by doing so, automatically extend the hardware warranty period for your IGEL thin clients, as per our original end-customer warranty agreement. By completing this one-time registration, you will also obtain extended warranty periods for all future IGEL devices. This offer of warranty extension does not apply to optional accessories. IGEL is a registered trademark of IGEL Technology GmbH. All hardware and software names are registered trademarks of the respective manufacturers. Errors and omissions excepted.
©2015/2016 IGEL Technology | 85-US-10-5 | WEEE-Reg.-Nr. DE 79295479

IGEL Technology America, LLC | info@igelamerica.com | www.igel.com/us

GERMANY Augsburg Bremen Mainz	AUSTRALIA Sydney	AUSTRIA Vienna	BELGIUM Leuven	CHINA Hong Kong Beijing Shanghai Guangzhou	FRANCE Paris	THE NETHERLANDS Utrecht	SINGAPORE Singapore	SWEDEN Sundsvall	SWITZERLAND Zurich	UNITED KINGDOM Reading	UNITED STATES Cincinnati New York
--	---------------------	-------------------	-------------------	--	-----------------	----------------------------	------------------------	---------------------	-----------------------	---------------------------	---

info@igel.com
www.igel.com

