



IK-WF51R

5MP Vandal Resistant
Panoramic IP Camera

Vandal-resistance with Panoramic Views and IR LEDs

The Toshiba IK-WF51R is a 5MP panoramic vandal-resistant dome IP camera with integrated IR LEDs. Surround viewing and up to 15fps in full resolution empower the IK-WF51R to cover large surveillance areas with a single camera. IR LEDs and an asthetically pleasing yet rugged form factor make it suitable for any indoor or outdoor application. ONVIF compliance and PoE/PoE+ ensure compatibility with Toshiba and 3rd party systems.

- 5MP resolution
- Digital WDR and True Day/Night
- Full surround panoramic view
- Integrated IR LEDs
- Ceiling, wall & desktop mount
- IP66 and IK10 ratings
- MicroSD card for edge recording
- ONVIF compliant for maximum compatibility
- PoE (802.3af) and PoE+ (802.3at)
- On board Dewarping



Onvif

Camera

Image sensor	1/2.5 inch CMOS 5MP
Effective pixels	2560 x 1920 (4:3)
Lens	Fisheye f=1.5mm, F=2.8
Lens type	Fixed focal M12
Angle of view	175° horizontal 175° vertical
Min. Illumination	0.6 lux / F2.8 (50 IRE, Gain 100%, 1/30 sec), 0 lux w/IR on
IR illuminators	IR LED, 10m x 10m area at 3m range (see Diagram A)

Network

Protocols	IPv4, IPv6, TCP/IP, HTTP, HTTPS, UPnP, RTSP/RTP/RTCP, IGMP, SMTP, FTP, DHCP, NTP, DNS, DDNS, PPPoE, CoS, QoS, SNMP, and 802.1X
ONVIF	Profile-S (test tool v14.12)
Maximum user access	10 clients
Security	Multi level ID/Password, IP address filtering, HTTPS, 802.1x port-based authentication
Basic Authorization	Yes (Windows standard)
Bandwidth control	QoS, CoS
Camera set-up program	Installation Wizard
Plug-In	Active X
Alarm recording	FTP, email, MicroSD card, HTTP

General


Dimensions	2.0 inch (H) x 6.3 inch (Diameter) (51mm x 160mm)
Weight	1.75 lbs (794g)
Power requirements	802.3af PoE, 802.3at PoE+, 12V DC ± 10 %
Power consumption	22W
Operation temperature	PoE: 14°F to 122°F (-10°C to 50°C) PoE+/12V DC: -22°F to 122°F (-30°C to 50°C)
Operation humidity	~ 90%
Approvals	FCC/B (verification), IC(ICES-003), UL(60950), cUL
Vandal resistance	IK10
Environmental	IP66, EN50155 Railway standard
Warranty	2 years

System Requirements

Web browser support	Internet Explorer® Ver. 8.0 or later
Supported OS	Windows® XP, Vista® Business, Windows 7 professional

Accessories

Included	Quick start guide, CD-ROM, alignment sticker, screw and anchor kit, desiccant, screw driver, power I/O cable, mounting bracket
-----------------	--



Interface

Ethernet connectors	10 Base-T/100 Base-TX, RJ45 connector
Digital In/Out	1 in/1 out
SD card slot	MicroSD/SDHC/SDXC 64GB max

¹: Varies in accordance with the object, image quality, network environment and performance of the personal computer used.

²: The sound may not be clear depending on the conditions of the lines.

Camera Modes

The IK-WF51R panoramic camera can display full surround video in multiple modes such as: original surround, full panoramic, 4 regions of interest, or combinations of original surrounds or panoramic plus regions of interest. With electronic PTZ controls, the panoramic camera can cover a large surveillance area with a single device.



Original surround



Four Regions of Interest
(no GUI)



Four Regions of Interest
(with GUI)



Panoramic
(no GUI)



Panoramic
(with GUI)

IK-WF51R

5MP Vandal-Resistant Panoramic IP Dome

TOSHIBA

Leading Innovation >>>

Included Accessories

- Quick start guide
- Screw and anchor kit
- CD-ROM
- Cable tie
- Alignment sticker

Optional Accessories

Accessory Type	Part Number	Description	Photo
Corner Mount	JK-CMA12	Corner mount adapter. Requires use with JK-PHO14 and JK-WM12	
Pendant Mount	JK-PHO14	Pendant mount adapter	
Pole Mount	JK-PMA12	Pole mount adapter. Requires use with JK-PHO14 and JK-WM12	
Pendant Head	JK-PMH12	Pendant head adapter. Requires use with JK-PHO14	
Pendant Pipe	JK-PMP12	Pendant pipe. Requires use with JK-PMH12	
Wall Mount	JK-WM12	Wall mount. Requires use with JK-PHO14	