

PT Dome Network Camera, 2-Megapixel, Outdoor, PoE 802.3af, Day & Night, IR LEDs, WDR

Key Features

- 2-Megapixel (1920 x 1080) high-definition resolution
 - Support unique features for auto-tracking function of moving objects
 - Built-in infrared LEDs for night viewing up to 10m
 - Removable IR-cut filter for day and night surveillance
 - Vandal-proof IK08-rated housing
 - Supports 2 video streams simultaneously
 - Compression: H.264/MPEG-4/MJPEG
 - Built-in Micro SD/SDHC card slot for local storage
 - Dual power support: 12VDC/PoE (IEEE 802.3af)
 - Free video surveillance and CMS (Central Management System) software with 64-channel license
-

Specifications

System Specifications

Standards & Protocols:

IEEE 802.3 10-BASE-T, Ethernet

IEEE 802.3u 100-BASE-TX, Fast Ethernet

TCP/IP, HTTP, SMTP, FTP, DDNS, UPnP, NTP, PPPoE, DNS, DHCP, RTSP, Samba

Image Sensor:

2-Megapixel 1/2.7" Progressive Scan CMOS

Connectors and Cabling:

1 x RJ-45 10/100 Mbps PoE port

1 x DC Power Jack

1 x line out

1 x line in

1 x Power terminal block

I/O terminal block (1 DI/1 DO)

Modularity:

1 x MicroSDHC card slot

**Button:**

Reset Button

Indicator:

Power, Link

Lens:

Board lens, Fixed-focal, f=4.0 mm, F2.0

IR Cut Filter:

Removable infrared-cut filter for day & night function

IR LED:

19 IR LEDs for illumination up to 10m

Shutter Time:

Indoor : 1/30 ~ 1/120 sec

Outdoor : 1/30 ~ 1/1,000,000 sec

Angle of View:

62°

Pan/Tilt/Zoom:

Pan range: 200°

Tilt range: 70°

Auto pan mode

Auto patrol mode

Video Compression:

H.264 / MPEG4 / MJPEG

Resolution:

2M (1920x1080)

Video Format:

MPEG4

Audio Compression:

AMR / AAC

Power:

Power Consumption: 8W

Power Input: DC12V 1.5A / AC24V / 802.3af PoE

Features

General:

Backup: MicroSDHC card slot for local storage

IPv6: IPv4/IPv6 network operation

DNS: Easy Internet monitoring

Security:

Alarm: Motion detection

Notification: FTP, SMTP, Samba

Access Control: Multi-level user access with password protection

IP address filtering

HTTPS encrypted data transmission

Video:

Image Setting:

- Adjustable image size, quality and bit rate

- Configurable brightness, sharpness, contrast, saturation, white balance and exposure

- AGC/AWB/AEC

- Wide Dynamic Range (WDR)

- 3D Noise Reduction (3DNR)

- Flip & Mirror

- Time Stamp

Streaming: Up to 2 video streams

Audio:

Streaming: 2-way audio

Input/Output: Line-in/audio

Performance**Number of Clients:**

16

Data Transfer Rate:

10/100Mbps

Storage Capacity:

SD/MicroSD memory card of up to 64GB

Frame Rate:

30 fps at 1920 x 1080; 30 fps at 1280 x 720; 30 fps at 640 x 480; 15 fps at 320 x 240

Minimum illumination:

Color: 1.0 lux at F2.0

B/W: 0 lux (IR LED on)

Environment**Temperature (°C):**

Operating: 0°C ~ 40°C

Humidity (Non-condensing):

Operating: 10% ~ 80%

Physical Specifications**Dimensions (W x D x H mm):**

63 x 63 x 92 mm

Weight (g):

500 g

Enclosure:

Weather proof IP66-rated housing

Vandal Resistant IK08-rated

Others**Approval and Compliance:**

CE, FCC, Onvif

Deployment:

Desktop/Ceiling Mount

Operation Systems:

Microsoft Windows 8/7/Vista/XP

Viewing Systems:

Browser: Internet Explorer 6.x or above, Firefox, Chrome, Safari

Cell phone: 3GPP player

Real Player: 10.5 or above

Quick Time 6.5 or above

Order Information

FCS-4102



Package Contents

FCS-4102

Power Adapter

Screw Kit

Quick Installation Guide

Resource CD (User Manual, Utility, QIG)

No liability or responsibility for any errors or omissions in the content.
Specifications are subject to change without notice.
All mentioned brand names are registered trademarks and property of their owners.
Copyright © Digital Data Communications GmbH, Germany. All Rights Reserved.