

# IN1100 Series

Light, Bright, Ultra-Portable Projectors  
with 1080p HD and PC-less Display

Part #s: IN1116, IN1118HD

**InFocus**

*Collaboration That Works*

The IN1100 Series of mobile projectors deliver bright, clear images no matter where you are, from nearly any device.

Leave your laptop behind and use the IN1100's built-in 4GB memory or a USB drive to present files. You can view presentations, documents and videos the way they were meant to be viewed, in true 1080p high definition.

The IN1100 Series projectors are the brightest products on the market, lumens per pound. Whether you're in a bright room or cramped for space, the IN1100 Series offers a mobile projector you can count on to perform every time.



## Why choose the IN1100 Series?

- IN1118HD is the only full 1080p HD product on the market at this ultra-portable size
- Compact and light weight for easy travel
- 2400 lumens for bright images in any lighting
- Connect via HDMI and VGA with ease
- Durable, road-tested design that's built to last
- PC-less display from USB drive or 4GB of memory

## Built for the Road

The projector has a recessed lens to keep it safe from impact. Plus its smooth exterior leaves nothing to snag or break off when taking it in and out of a bag.

## Display from No Device at All

Project images, audio and video directly from the projector's on-board 4GB of memory or from a USB thumb drive. Just load it and go.

## Carry Easily and Connect Quickly

At only 3.5 lbs. it's easy to pack and carry and connects with your notebook or tablet via HDMI or USB in seconds to present full HD quality video.



# Specifications\*\*

	IN1116	IN1118HD
Resolution	WXGA (1280 x 800)	1080p (1920 x 1080)
Brightness (lumens)		Eco: 1920, Normal: 2400
Illumination Technology		UHP Lamp 170W
Display Technology		DLP
Contrast Ratio	14000:1	15000:1
Aspect Ratio	16:10 (Standard) / 4:3 and 16:9 (Compatible)	16:9 (Standard) / 4:3 and 16:10 (Compatible)
Projection Lens (f-stop)		F2.59 - 2.91
Zoom Ratio		1.3:1
Throw Distance		1.0m - 10.0m
Throw Ratio	1.18 - 1.54	1.15 - 1.5
Image width		30 - 300 inches
Vertical/Offset		15%
Auto Keystone		Yes, ± 40°
Input Connections	HDMI 1.4a (including audio), VGA, composite, S-video, 3.5mm audio in	
Output Connections	3.5mm audio out	
Basic PC Compatibility	VGA (640x480), wVGA (854x480), SVGA (800x600), wSVGA (1024x600), XGA (1024x768), wXGA (1280x800), wXGA+ (1440x900), SXGA (1280x1024), wSXGA+ (1680x1050), UXGA (1600x1200), wUXGA (1920x1200)	
Video Compatibility	Standard: NTSC, NTSC 4.43, PAL/M/N, SECAM SD: 480i, 480p, 576i   HD: 720p, 1080i, 1080p	
Internal Memory	4 GB	
PC-Less Compatibility	Compatible with USB HID mouse and keyboard, USB Type A x2, USB Type Micro-B	Compatible with USB HID mouse and keyboard, USB Type A x2, USB Type Micro-B
Document Reader	Supports pdf, doc, docx, xls, xlsx, ppt, pptx, Notes	
Video Player	Supports avi, mkv, mpg, mpeg, mov, mp4, 3gp, rm, rmvb	
Photo Reader	Supports jpg, jpeg, bmp, png	
Music Player	Supports mp3, wma, wav, aac	
H-Sync Range	15K-91K Hz	
V-Sync Range	24-120 Hz	
Lamp Power (Eco/Normal)	150w / 170w	
Lamp Life (Eco/Normal)	10000 / 6000 hours	
Power Consumption (Standby/Eco/Normal)	<0.5 / 180 / 220w	
Noise (Eco/Normal)	27 / 30dBa	
Power Supply Range	90V-264V at 50-60 Hz	
Operating Conditions	32 to 95°F at 0 to 10K ft / 0 to 35° at 0 to 3,048 m (Up to 104°F / 40°C below 7.5K ft / 2,286 m)	
Storage Temperature	-4 to 140° F / -20 to 60° C	
Operating Humidity	10 - 85% RH Without Condensation	
Interface Languages	English, French, German, Spanish, Italian, Norwegian, Dutch, S. Chinese, T. Chinese, Korean, Swedish, Russian, Finnish, Polish, Turkish, Danish, Arabic, Indonesian, Persian, Portuguese, Vietnamese, Czech, Romanian, Hungarian	
Documentation Languages	English, French, German, Spanish, Italian, Norwegian, Dutch, S. Chinese, Korean, Portuguese, Swedish, Russian, Arabic, Indonesian	
Speaker	1x - 2w	
Dimensions (W x D x H)	8.8 x 7.3 x 3.1 in. / 222.4 x 185 x 79.2 mm	
Weight	3.5 lbs / 1.59 kg	
Standard Accessories	Power cord, remote control, carry case, VGA cable, 3.5mm AV cable, documentation	
Warranty	1 year (product), 6 months (lamp), 90 days (accessories)	

\*\*Product specifications, terms, and offerings are subject to change at any time without notice.



## Accessories

- Replacement Lamp (SP-LAMP-095)
- Presenter 2 RF Remote with USB Receiver (HW-PRESENTER-2)
- Portable 16:9 Projector Screens (SC-PUW-73, SC-PUW-90)