


CADENCE

Xenith

XS 682



6 x 8 in



TS PARAMETERS

FMS: 92.4 Hz	BL: 3.8
QMS: 2.50	SPL: 90 dB
QES: 1.70	VAS: 18.4 l
QTS: 1.01	RE: 3.6 Ohm
RES: 4.0 Ohm	RP: 3.8 Ohm
RMS: 2.7 kg/s	LP: 4.8 mH
CMS: 0.26 mm/N	CP: 1346.5 μ F
MMS: 11.6 gr	LE: 0.1 mH
NREF: 0.82 %	

4 Ohm

275 Watts

Xenith Power

SPECIFICATIONS

Application: 2 - Way Speaker

Basket Type: Open Steel Basket

Cone: Black Plated Acrylic w/ Piano Finish

Tweeter: Extended Frequency Dome Tweeter

Surround Style: Butyl Rubber


Structure Weight: 30 oz.

Impedance: 4 Ohm

RMS / Peak Watts: 50 / 150

Frequency Response: 60Hz - 20KHz

SPL @ 1w/1m: 90dB



Cadence Acoustics

6519 Highway 9 North • Howell, NJ 07731
800.477.2328 • 732.370.5400 • fax: 732.370.5553 • www.cadencesound.com

