

ICIP-D3000-AIR

3 MP Indoor/Outdoor, Mini Orbital IR Network Dome Camera



This Indoor-Outdoor 3MP IR dome camera has a high resolution, 3 Megapixel Progressive Scan Aptina CMOS sensor capable of outputting a crisp and clear image. The optics on this camera include a fixed 3.6mm lens, providing a rather wide field of vision. Built in IR LED illumination is effective up to 60' at 0 light. The ICIP D3000 AIR is IP-66 rated. This camera supports PoE, is fully accessible via the entire ICR software suite, and is also compatible with third party ONVIF equipment.

Features

- 3.6mm fixed lens
- Max 20fps@3M (2052×1536)
- DWDR, Day/Night (ICR), 3DNR
- IP66, PoE
- Max. IR LEDs Length 60'

ICIP-D3000-AIR

Specifications

Model	ICIP-D3000-AIR
Camera	
Image Sensor	1/3" 3Megapixel progressive scan CMOS
Effective Pixels	2048(H)×1536(V)
Scanning system	Progressive
Electronic Shutter Speed	Auto/Manual, 1/3(4)~1/10000s
Min. Illumination	0.1lux/F1.8(color)
S/N Ratio	More than 50db
Camera Features	
Max. IR LEDs Length	60'
Day/Night	Auto(Electronic)/Color/B/W
Backlight Compensation	BLC / HLC / DWDR
White Balance	Auto / Manual
Gain Control	Auto / Manual
Noise Reduction	3D
Privacy Masking	Up to 4 areas
Lens	
Focal Length	2.8mm
Max Aperture	F2.0
Focus Control	Manual
Angle of View	H: 90°
Lens Type	Fixed lens
Mount Type	Board-in Type
Video	
Compression	H.264/MJPEG
Resolution	3M(2048×1536) / 1080P(1920×1080) / 720P(1280×720) / D1(704×480) / CIF(352×240)
Frame Rate	Main Stream: 3M(1~20fps)/1080P/720P(1 ~ 25/30fps) Sub Stream: D1/CIF(1 ~ 30fps)
Bit Rate	H.264: 32K ~ 8192Kbps
Network	
Ethernet	RJ-45 (10/100Base-T)
Protocol	IPv4/IPv6, HTTP, HTTPS, SSL, TCP/IP, UDP, UPnP, ICMP, IGMP, SNMP, RTSP, RTP, SMTP, NTP, DHCP, DNS, PPPOE, DDNS, FTP, IP Filter, QoS, Bonjour
ONVIF	ONVI,PSIA,CGI
Max. User Access	20 users
Smart Phone	iPhone, iPad, Android, Windows Phone
General	
Power Supply	DC12V, PoE (802.3af)
Power Consumption	Max 4W
Working Environment	-20°C ~ 60°C, Less than 95% RH
Ingress Protection	IP66
Dimensions	Φ4.5"×3.4"

Weight	0.88lb
--------	--------

ICIP-D3000-AIR

Optional Accessories



[MNT-IPMINIDOME-WALL](#)



[MNT-JUNCTION BOX 1](#)



[MNT-PCNRIP](#)



[MNT-POLIP](#)

IC Realtime LLC

3050 N Andrews Avenue Extension
Pompano Beach, FL 33064
(866) 997-9009

www.icrealtime.com

Designs and specifications subject to change without notice. Copyright © 2015 IC Realtime, LLC. All rights reserved.