

HP LaserJet Pro M402dw



Printing performance and robust security built for how you work. This capable printer finishes jobs faster and delivers comprehensive security to guard against threats.¹ Original HP Toner cartridges with JetIntelligence give you more pages.²



Print speed: Letter: Up to 40 ppm black; First Page Out As fast as 6.4 sec

Print Resolution: Black (best) 600 x 600 dpi, Up to 4800 x 600 enhanced dpi

Print Technology Resolution: HP FastRes 1200, HP ProRes 1200, 600 dpi

Standard Connectivity: 1 Hi-Speed USB 2.0; 1 Host USB; 1 Gigabit Ethernet 10/100/1000T network; 1 Wireless 802.11b/g/n

Wireless: Yes, built-in Wi-Fi 802.11b/g/n

Standard Memory: 128 MB

Mobile Printing Capability: HP ePrint, Apple AirPrint™, Wireless direct printing, Mopria-certified, Google Cloud Print, Mobile Apps

Paper Handling: 100-sheet multipurpose input Tray 1, 250-sheet input Tray 2; 150-sheet output bin; Optional 550-sheet tray 3

Display: 2-line LCD (text and graphics)

Fast printing. Strong protection.

- Grab pages and go—without waiting around. This printer wakes up and prints faster than the competition.¹
- Breeze through multipage documents with two-sided printing that's faster than the competition.¹
- Keep printing safe from boot up to shutdown with security features that guard against complex threats.

More. Pages, Performance, and Protection.

- Get the most prints for your money—with Original HP High Yield Black Toner cartridges with JetIntelligence.²
- Count on consistent results at high speeds with precision black toner.
- Help ensure you're getting the authentic HP quality you paid for with innovative anti-fraud technology.
- Print right away with preinstalled toner cartridges. Replace them with optional high-yield cartridges.

Save energy and easily manage tasks

- Help save energy with HP Auto-On/Auto-Off Technology.³
- Print using less energy than competitors—enhanced by Original HP Toner cartridges with JetIntelligence.⁴
- Make the most of your office space, with a printer that conveniently fits right into your work style.
- Easily manage devices and settings using HP Web Jetadmin with a suite of essential management features.⁵

Stay connected with easy mobile printing options

- Easily print from a variety of smartphones and tablets—generally no setup or apps required.⁶
- Easily access, print, and share resources with Ethernet and wireless networking.⁷
- Count on wireless direct printing in the office—from mobile devices—without accessing the company network.⁸
- Help workers print with just a touch of their NFC-enabled mobile device to the printer—no network needed.⁹



Mac



¹ Based on HP internal testing of top three leading competitors' first page out from sleep mode and duplex print speed completed 8/2015. Subject to device settings. Actual results may vary. For details see hp.com/go/Ljclaims ² Based on cartridge yields for HP 80X compared with HP 26X Original HP LaserJet Toner Cartridges. For more information, see hp.com/go/learnaboutsupplies ³ HP Auto-On/Auto-Off Technology capabilities subject to printer and settings; May require a firmware upgrade. ⁴ Based on HP testing using the ENERGY STAR® program's Typical Electricity Consumption (TEC) method or as reported in energystar.gov of top three leading competitors as of 8/2015. Actual results may vary. For details see hp.com/go/Ljclaims ⁵ HP Web Jetadmin is free and available for download at hp.com/go/webjetadmin ⁶ Wireless operations are compatible with 2.4 GHz operations only. App or software and HP ePrint account registration may also be required. Some features require purchase of an optional accessory. Learn more at hp.com/go/mobileprinting ⁷ Wireless performance is dependent on physical environment and distance from access point, and may be limited during active VPN connections. ⁸ Feature is supported on the HP LaserJet Pro M402dw only. Mobile device needs to be connected directly to the WiFi network of a wireless direct-capable MFP or printer prior to printing. Depending on mobile device, an app or driver may also be required. Learn more at hp.com/go/businessmobileprinting ⁹ Feature is supported on the HP LaserJet Pro M402dw only. Requires a compatible NFC-printing-enabled mobile device. For a list of compatible NFC-printing-enabled mobile devices, see hp.com/go/nfcprinting

HP LaserJet Pro M402dw Specifications Table

Print Speed	Letter: Up to 40 ppm black; ⁴ First Page Out: As fast as 6.4 sec (ready); As fast as 9.8 sec (sleep) ¹²
Print Resolution	Black (best): 600 x 600 dpi, Up to 4800 x 600 enhanced dpi
Print Technology	Laser
Print Resolution Technologies	HP FastRes 1200, HP ProRes 1200, 600 dpi
Print Cartridges Number	1 (black)
Standard Print languages	HP PCL 5, HP PCL 6, HP postscript level 3 emulation, direct PDF (v 1.7) printing, URF, PCLM, PWF
Printer Smart Software Features	Auto-duplex printing, N-up printing, collation, HP ePrint, Apple AirPrint™, Google Cloud Print, Mopria-certified, Wireless direct printing, HP Auto Wireless Connect, NFC, Instant-on Technology, HP Auto-On/Auto-Off technology, JetIntelligence Cartridge Technology, Job Storage with PIN printing
Printer Management	Printer Administrator Resource Kit (Driver Configuration Utility, Driver Deployment Utility, Managed Printing Administrator); HP Web JetAdmin Software; HP Proxy Agent Software; HP Imaging and Printing Security Center; HP Utility (Mac); HP Device Toolbox
Standard Connectivity	1 Hi-Speed USB 2.0; 1 Host USB; 1 Gigabit Ethernet 10/100/1000T network; 1 Wireless 802.11b/g/n
Network Capabilities	Via built-in 10/100/1000 Base-TX Ethernet, Gigabit; Auto-crossover Ethernet; Authentication via 802.1X
Network Ready	Standard (built-in Ethernet, Wi-Fi)
Wireless Capability	Yes, Built-in Wi-Fi; Authentication via WEP, WPA/WPA2, WPA Enterprise; Encryption via AES or TKIP; WPS, Wi-Fi Direct
Mobile Printing Capability	HP ePrint, Apple AirPrint™, Wireless direct printing, Mopria-certified, Google Cloud Print 2.0, Mobile Apps
Memory	Standard: 128 MB; Maximum: 128 MB
Processor Speed	1200 MHz / Hard disk: None
Duty Cycle	Monthly, letter: Up to 80,000 pages ⁶
Recommended Monthly Page Volume	750 to 4000 ⁷
Media Types Supported	Paper (plain, EcoFICIENT, light, heavy, bond, colored, letterhead, preprinted, prepunched, recycled, rough); Envelopes; Labels; Transparencies
Media Weight Supported	Tray 1: 16 to 46.6 lb; Tray 2, Optional 550-sheet Tray 3: 16 to 32 lb
Media Sizes Supported	Tray 1: Letter, Legal, Executive, Oficio (8.5 x 13 in), A4, A5, A6, B5 (JIS), Oficio (216 x 340 mm), 16K (195 x 270 mm), 16K (184 x 260 mm), 16K (197 x 273 mm), Japanese Postcard, Double Japan Postcard Rotated, Envelope #10; Envelope Monarch, Envelope B5, Envelope C5, Envelope DL, Custom Size, A5-R, 4 x 6 in, 5 x 8 in, B6 (JIS), 10 x 15 in, statement; Tray 2 & Tray 3: Letter, Legal, Executive, Oficio (8.5 x 13 in), A4, A5, A6, B5 (JIS), Oficio (216 x 340 mm), 16K (195 x 270 mm), 16K (184 x 260 mm), 16K (197 x 273 mm), Custom Size, A5-R, 5 x 8 in, B6 (JIS), statement
Media Sizes Custom	Tray 1: 3 x 5 to 8.5 x 14 in; Tray 2, 3: 4.13 x 5.85 to 8.5 x 14 in
Paper Handling	100-sheet multipurpose Tray 1, 250-sheet input Tray 2; 150-sheet output bin; Duplex Options: Automatic (standard); Envelope Feeder: No; Standard Paper Trays: 2; Input Capacities: Up to 350 sheets (Tray 1: up to 100 sheets; Tray 2: up to 250 sheets); Output Capacities: Up to 150 sheets; Up to 10 envelopes; Up to 75 sheets
What's in the box	CSF95A HP LaserJet Pro M402dw; Preinstalled HP 26A Black LaserJet Toner Cartridge (~3100 pages); Getting Started Guide; Setup Poster; Support Flyer; Warranty Guide; Printer documentation and software on CD-ROM; Power cord; USB cable ¹
Replacement Cartridges	HP 26A Black LaserJet Toner Cartridge (~3100 pages), CF226A; HP 26X Black LaserJet Toner Cartridge (~9000 pages), CF226X ¹
Product Dimensions	W x D x H: 15 x 14.06 x 8.5 in ² ; Maximum: 15 x 25 x 9.5 in
Product Weight	18.92 lb ¹⁰
Warranty Features	One-year warranty, return to HP Authorized Service Provider
Energy Efficiency Compliance	ENERGY STAR® certified; Blue Angel; EPEAT® Silver
Control Panel	2-line backlit LCD graphic display; Buttons (OK, Menu, Cancel, Back, Wi-Fi); LED indicator lights (Attention, Ready, Wi-Fi)
Display Description	2-line LCD (text and graphics)
Software Included	For Windows 7: HP Software Installer/Uninstaller, HP PCL 6 Printer Driver, HP Device Experience (DXP), HP Update, HP Device Toolbox, HP Printer Status and Alerts, HP Product Improvement Study, Reconfigure your HP Device; Warranty and Legal Guide, User Guide; For Windows 8+: HP Software Installer/Uninstaller, HP PCL-6 Printer Driver, HP Device Experience (DXP), Warranty and Legal Guide, User Guide, Reconfigure your HP Device; For Windows XP, Windows Vista and associated servers: HP Software Installer/Uninstaller, HP PCL-6 Printer Driver, Warranty and Legal Guide, User Guide; For Mac OS: Welcome Screen (Directs users to http://www.hp.com or OS App Source for LaserJet Software)
Fonts and Typefaces	84 scalable TrueType fonts

Compatible Operating Systems	Windows OS compatible with In-Box Driver: Windows XP SP3 all 32-bit editions (XP Home, XP Pro, etc), Windows Vista all 32-bit editions (Home Basic, Premium, Professional, etc), Windows 7 all 32 & 64-bit editions, Windows 8/8.1 all 32 & 64-bit editions (excluding RT OS for Tablets), Windows 10 all 32 & 64-bit editions (excluding RT OS for Tablets); Windows OS compatible with Universal Print Driver (From HP.com): Windows XP SP3 32 & 64-bit editions (XP Home, XP Pro, etc.), Windows Vista all 32 & 64-bit editions (Home Basic, Premium, Professional, etc), Windows 7 all 32 & 64-bit editions, Windows 8/8.1 all 32 & 64-bit editions (excluding RT OS for Tablets), Windows 10 all 32 & 64-bit editions (excluding RT OS for Tablets); Mac OS (HP Print Drivers available from HP.com and Apple Store): OS X 10.8 Mountain Lion, OS X 10.9 Mavericks, OS X 10.10 Yosemite; Mobile OS (In-OS drivers): iOS, Android, Windows 8/10/RT; Linux OS (In-OS HPLIP); Auto install: BOSS(3.0, 5.0), DEBIAN(6.0, 6.0.1, 6.0.2, 6.0.3, 6.0.4, 6.0.5, 6.0.6, 6.0.7, 6.0.8, 6.0.9, 6.0.10, 7.0, 7.1, 7.2, 7.3, 7.4, 7.5, 7.6), FEDORA(17, 18, 19, 20), LINUX MINT(13, 14, 15, 16, 17), SUSE LINUX(12.2, 12.3, 13.1), UBUNTU(10.04, 11.10, 12.04, 12.10, 13.04, 13.10, 14.04, 14.10); Manual install: MANDRIVA LINUX (2010.0, 2011.0), MEPIS (6.0, 6.5, 7.0, 8.0), PCLINUXOS (2006.0, 2006, 2007.0, 2007, 2008.0, 2008, 2009.0, 2009), RED HAT(8.0, 9.0), RED HAT ENTERPRISE LINUX(5.0, 6.0, 7.0), SLACKWARE LINUX(9.0, 9.1, 10.0, 10.1, 10.2, 11, 12, 12.1), GOS(8.04.1), IGOS(1.0), LIMPUS LINUX(9.4, 9.5), LINUX FROM SCRATCH(6); Other OS: UNIX ⁹
Compatible Network Operating Systems	Windows OS compatible with In-Box Driver: Windows Server 2003/2003 R2 32-bit (SP1/SP2) Standard/Enterprise (+ Cluster & Terminal Services), Windows Server 2008 32/64-bit (SP2) Standard/Enterprise (+ Cluster & Terminal Services), Windows Server 2008 R2 64-bit (SP1) Standard/Enterprise (+ Cluster & Terminal Services); Windows OS compatible with Universal Print Driver (UPD) or Product-Specific drivers from HP.com: Windows Server 2003/2003 R2 32-/64-bit (SP1/SP2) Standard/Enterprise/Datacenter (+ Cluster & Terminal Services), Windows Server 2008/2008 R2 32-/64-bit (SP1/SP2) Standard/Enterprise/Datacenter (+ Cluster & Terminal Services), Windows Server 2012/2012 R2 64-bit Standard/Foundation/Essentials/Datacenter (+ Cluster & Terminal Services); MS Windows Server 2012 R2 Terminal Services: Citrix XenApp 7.5, Citrix XenDesktop 7.0, Citrix XenDesktop 7.5; MS Windows Server 2012 Terminal Services: Citrix XenApp 7.5, Citrix XenDesktop 7.0, Citrix XenDesktop 7.5; MS Windows Server 2008 R2 SP1 Terminal Services: Citrix XenApp 6.0, Citrix XenApp 6.5, Citrix XenApp 7.5, Citrix XenDesktop 5.6, Citrix XenDesktop 7.0, Citrix XenDesktop 7.5; MS Windows Server 2008 R2 Terminal Services: Citrix XenApp 6.0, Citrix XenApp 6.5, Citrix XenDesktop 5.6; MS Windows Server 2008 Terminal Services: Citrix XenApp 5.0, Citrix XenApp 5.0 Feature Pack 2 & 3; MS Windows Server 2003 Terminal Services: Citrix Presentation Server(TM) 4.5, Citrix Presentation Server 4.0; MS Windows Server 2003 Terminal Services: Citrix Presentation Server 4.5, Citrix Presentation Server 4.0, Citrix MetaFrame® Presentation Server, 3.0, Citrix MetaFrame XP Presentation Server (Feature Release 1, 2, and 3); Novell Servers (http://www.novell.com/iprint): Novell Open Enterprise Server 11/SP1 /SP2, Novell Open Enterprise Server 2 for Linux; NetWare 6.5/SP8; Novell Clients (http://www.novell.com/iprint): Novell iPrint Client v5.4 for Vista & Win7 & Win8 (32-bit, 64-bit), Novell iPrint Client v5.4 for WinXP (32-bit, 64-bit)
Minimum System Requirements	PC: Windows 10 (32-bit/64-bit), Windows 8.1 (32-bit/64-bit), Windows 8 (32-bit/64-bit), Windows 7 (32-bit/64-bit): 1 GHz processor, 1 GB RAM (32-bit) or 2 GB RAM (64-bit), 400 MB available hard disk space, CD/DVD-ROM or Internet, USB or Network port; Windows Vista (32-bit): 1 GHz 32-bit (x86) processor, 1 GB RAM (32-bit), 400 MB available hard disk space, CD/DVD-ROM or Internet, USB or Network port; Windows XP (32-bit) SP2: Pentium 233 MHz processor, 512 MB RAM 400 MB available hard disk space, CD/DVD-ROM or Internet, USB or Network port; Windows Server 2003 (32-bit) (SP1 or greater), Windows Server 2003 R2 (32-bit), Windows Server 2008 (32-bit) (SP1 or greater): 1 GHz 32-bit (x86) processor, 1 GB RAM (32-bit), 400 MB available hard disk space, CD/DVD-ROM or Internet, USB or Network port; Windows Server 2008 (64-bit) (SP1 or greater), Windows Server 2008 R2 (64-bit), Windows Server 2008 R2 (64-bit) (SP1): 1 GHz 64-bit (x64) processor, 2 GB RAM (64-bit), 400 MB available hard disk space, CD/DVD-ROM or Internet, USB or Network port; MAC: OS X 10.8 Mountain Lion; OS X 10.9 Mavericks; OS X 10.10 Yosemite; Network port; 1 GB available hard disk space; OS compatible hardware (For OS hardware requirements see http://www.apple.com)
Power	Power Supply Type: Internal (built-in) power supply; Power Requirements: 110-volt input voltage: 110 to 127 VAC (+/- 10%), 50/60 Hz (+/- 2 Hz); 220-volt input voltage: 220 to 240 VAC (+/- 10%), 50/60 Hz (+/- 2 Hz) (Not dual voltage, power supply varies by part number with #option code identifier); Typical Electricity Consumption: 1.79 kWh/Week (Energy Star) ¹³ Power Consumption: 591 watts (Active Printing), 6.1 watts (Ready), 2.8 watts (Sleep), 0.6 watts (Auto-On/Auto-Off, via USB connectivity), 0.1 watts (Shutdown or Off) ¹⁵
Acoustics	Acoustic Power Emissions (active): 6.8 B(A); Acoustic Power Emissions (ready): Inaudible; Acoustic Pressure Emissions (active): 54 dB(A); Acoustic Pressure Emissions (ready): Inaudible ¹⁶
Operating Environment	Operating Temperature Range: 59 to 90.5°F; Recommended Operating Temperature: 63.5 to 77°F; Storage Temperature Range: -4 to 104°F; Non-Operating Humidity Range: 10 to 90% RH; Operating Humidity Range: 10 to 80% RH; Recommended Humidity Operating Range: 30 to 70% RH
Security Management	Embedded Web Server: password-protection, secure browsing via SSL/TLS; Network: enable/disable network ports and features, SNMPv1 & SNMPv2 community password change; HP ePrint: HTTPS with certificate validation, HTTP Basic Access Authentication, SASL authentication; Firewall and ACL; SNMPv3, 802.1X, Secure Boot, authentication via WEP, WPA/WPA2 Personal, WPA2 Enterprise; Encryption via AES or TKIP
Accessories	HP LaserJet 550-sheet Feeder/Tray D9P29A; HP v222w 16GB Mini USB Drive P0R81AA
HP Service and Support Options	UBTM2E - HP 3y Next Business Day LaserJet M402 Hardware Support; UBTM3E - HP 4y Next Business Day LaserJet M402 Hardware Support; UBTM4E - HP 5y Next Business Day LaserJet M402 Hardware Support; UBTM5E - HP 3y Next Business Day Exchange LaserJet M402 Service; H3110E - HP Network Install Inkjet/Personal LaserJet Service

Learn more at hp.com

¹ Declared yield value in accordance with ISO/IEC 19752. Actual yields vary considerably based on images printed and other factors. For more information, visit hp.com/go/learnaboutsupplies ² Without optional 550-sheet tray; Dimensions with optional 550-sheet tray: 15 x 14.06 x 13.58 in (381 x 357 x 345 mm) ³ Job Storage feature requires a purchase of separate USB flash drive with a minimum of 16 GB capacity. ⁴ Measured using ISO/IEC 24734, excludes first set of test documents. For more information see hp.com/go/printerclaims. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ⁵ Measured using ISO/IEC 17629, excludes first set of test documents. For more information see hp.com/go/printerclaims. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ⁶ Duty cycle is defined as the maximum number of pages per month of imaged output. This value provides a comparison of product robustness in relation to other HP LaserJet or HP Color LaserJet devices, and enables appropriate deployment of printers and MFPS to satisfy the demands of connected individuals or groups. ⁷ HP recommends that the number of printed pages per month be within the stated range for optimum device performance, based on factors including supplies replacement intervals and device life over an extended warranty period. ⁸ HP SureSupply alerts you when your print cartridge is running low and helps you purchase online or locally through HP or a participating retailer. For more information, visit hp.com/go/SureSupply; only available with Original HP supplies; Internet access required. ⁹ Not all "Compatible Operating Systems" are supported with in-box software; Full solution software available only for Windows 7 and newer; Legacy Windows Operation Systems (XP, Vista, and equivalent servers) get print drivers only; Windows RT OS for Tablets (32-bit & 64-bit) uses a simplified HP print driver built into the RT OS; UNIX Modelscripts are available on HP.com (Modelscripts are printer drivers for UNIX operating systems); Linux systems use In-OS HPLIP software; HP Software for Mac is no longer included on the CD, but can be downloaded from hp.com - the Mac driver and Mac Utility are installed for Mac operating systems. ¹⁰ With 26A cartridge. ¹² Measured using ISO/IEC 17629, excludes first set of test documents. For more information see hp.com/go/printerclaims. Exact speed varies depending on the input voltage, system configuration, software application, driver, and document complexity. ¹³ Typical Electricity Consumption (TEC) rating represents the typical electricity consumed by a product during 1 week, measured in kilowatt-hours (kWh). ¹⁵ Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. ¹⁶ Acoustic values are subject to change. For current information see hp.com/support. Configuration tested: base model, simplex printing, A4 paper at an average of 38 ppm.

© Copyright 2015 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. ENERGY STAR and the ENERGY STAR logo are registered U.S. marks. Windows is a registered trademark of Microsoft Corporation. AirPrint, iPad, iPhone, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries.

