

Lenovo YOGA 3 (11, 14 inch)

POSITIONING STATEMENT

The Lenovo 11-inch and 14-inch YOGA 3 are intelligent and powerful convertible PCs that serve as true mobile companions. The convertibles offer amazing value, performance and entertainment with four mode adaptability – *Laptop, Tablet, Stand and Tent*. Additionally, the YOGA 3 delivers powerful performance, sharp graphics and a large display for maximum productivity and entertainment.

KEY FEATURES

- 360° hinge to transform the device into a *Laptop, Tablet, Stand* or *Tent* for any use case
- Features intelligent software that automatically responds to different modes to provide an optimal user experience
- Thin and light for increased mobility
- Powerful performance with an Intel® Core™ processor
- 11- and 14-inch devices available, giving users larger screen options for enhanced productivity, gaming and media experiences
- Stereo speakers with Waves Audio certification provide captivating audio
- Up to 6.5 hours of battery life¹



DETAILED SPECIFICATION

Note: specification will vary by region.

Processor	11-inch: Intel® Core™ M processor 14-inch: Up to 5 th Generation Intel® Core™ i7 processor
Operating System	Windows 8.1 update
Display/Resolution	11-inch: FHD 1920x1080 IPS touchscreen 14-inch: FHD 1920x1080 IPS touchscreen
Video Graphics	11-inch: Integrated Intel® HD GFX 14-inch: Up to Next Generation GeForce GPU
Memory	11-inch: Up to 8GB LP-DDR3 14-inch: Up to 8GB DDR3L
Storage	11-inch: Up to 256GB SSD 14-inch: Up to 500GB SSHD or 256GB SSD
Sound	Stereo speakers with Waves Audio certification
Connectivity	2xUSB 3.0, 1XUSB 2.0, 4in1 card reader (SD,SDHC,SDXC, MMC), Audio combo jack, HDMI
Bluetooth	802.11 A/C WiFi
Camera	720p HD
Battery	Up to 6.5 hours of battery life ¹
Color Options²	11-inch: silver, white and black 14-inch: black, silver and orange
Weight	11-inch: 1.1 kg (2.65 lbs.) 14-inch: 1.6 kg (3.53 lbs.) with SSD; 1.7 kg (3.75 lbs.) with SSHD
Dimensions	11-inch: 290 x 197 x 15.8 mm (11.4 x 7.8 x .6 in.) 14-inch: 334.9 x 229.5 x 18.3 mm (13.2 x 9 x .7 in.)

¹Dependent on type of use

²Color options vary by region