


DS-2CD2T42WD-I3/I5/I8 4.0MP EXIR Bullet Network Camera



- 1/3" Progressive Scan CMOS
- Up to 4 megapixel resolution
- Full HD1080p real-time video
- 120dB Wide Dynamic Range
- 3D DNR
- EXIR high performance LEDs
- Up to 30/50/80 meters IR range
- 12V DC $\pm$ 10% & PoE(802.3af)
- IP66
- Mobile monitoring via EZVIZ or iVMS-4500



DS-2CD2T42FWD-I3/I5/I8

4.0MP EXIR Bullet Network Camera



Specification

Camera	
Image Sensor	1/3" Progressive Scan CMOS
Min. Illumination	0.01Lux @(F1.2,AGC ON), 0.014 Lux @(F1.4,AGC ON), 0 Lux with IR
Shutter Speed	1/3 s ~ 1/10,000 s
Slow Shutter	Support
Lens	(-I3: 4,6mm; -I5: 4,6,12mm; -I8: 6,12,16mm) @F1.4
Lens Mount	M12
Day & Night	IR cut filter with auto switch
WDR	120dB
Compression Standard	
Video Compression	H.264/MJPEG
H.264 Type	Main Profile
Video Bit Rate	256 Kbps – 16 Mbps
Image	
Max. Resolution	2688 × 1520
Frame Rate	50Hz: 20fps (2688×1520), 25fps(1920×1080), 25fps(1280×720) 60Hz: 20fps (2688×1520), 30fps (1920×1080), 30fps(1280×720)
Image Enhancement	BLC/3D DNR/ROI
Image Setting	Rotate Mode, Saturation, Brightness, Contrast, Sharpness adjustable by client software or web browser
Day/Night Switch	Auto/Schedule/Triggered by Alarm In
Network	
Network Storage	NAS (Support NFS,SMB/CIFS)
Alarm Trigger	Intrusion Detection, Line Crossing detection, Motion detection, Dynamic Analysis, Tampering alarm, Network disconnect, IP address conflict, Storage exception
Protocols	TCP/IP, UDP, ICMP, HTTP, HTTPS, FTP, DHCP, DNS, DDNS, RTP, RTSP, RTCP, PPPoE, NTP, UPnP, SMTP, SNMP, IGMP, 802.1X, QoS, IPv6, Bonjour
Security	Flash-prevention, dual stream, heartbeat, mirror, password protection, privacy mask, watermark, IP address filtering, Anonymous access
Standard	ONVIF (PROFILE S, PROFILE G), PSIA, CGI, ISAPI
General	
Communication Interface	1 RJ45 10M/100M Ethernet interface
Operating Conditions	-30 °C – 60 °C (-22 °F – 140 °F), Humidity 95% or less (non-condensing)
Power Supply	12V DC±10%, PoE (802.3af)
Power Consumption	I3: Max. 6W; I5: Max. 7.5W; I8: Max. 10.5W
Ingress Protection level	IP66
IR Range	I3: 30 meters; I5: 50 meters; I8: 80 meters
Dimensions	299.71 × 86.48 × 85.11(11.8" × 3.4" × 3.35")
Weight	1200g (2.65 lbs)
Order Model	
DS-2CD2T42WD-I3, DS-2CD2T42WD-I5, DS-2CD2T42WD-I8	