

## Portable Server Rack with Handles - 9U

**Product ID:** RK960CP



This 9U portable server rack lets you store your server, network and telecommunications equipment in a sturdy mobile rack that has a fixed depth of 23 inches. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

With built-in handles and four swiveling casters, this mobile rack is easy to transport around your server room, office or studio. Its increased mobility makes this cabinet the ideal solution for telecommunication racks that need to interface with different equipment around your workspace.

The server rack features heavy-gauge mounting rails to ensure a stable installation platform. This durable 4-post rack supports a static loading capacity of up to 220 lb (99.8 kg), and is compliant with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494), providing a universal design that's compatible with most rack equipment.

Save time and hassle with a rack that's easy to put together. With its easy four-step assembly process, you can set this portable rack up in minutes.

The RK960CP is backed by a 2-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Create a portable video editing and production rack that you can move around your studio to interface with different equipment

- Store this mobile rack beneath a table or bench in small offices or workspaces
- Mount equipment in technology shops and repair centers where security is required

## Features

- **MAXIMUM PORTABILITY:** With built-in handles and four swiveling casters, this mobile AV equipment rack is ideal for racks that need to interface with other equipment around your workspace
- 4AV
- **STURDY DESIGN:** The server room rack features heavy-gauge mounting rails to ensure a stable installation platform; this 4-post rack supports a static loading capacity of up to 220 lb
- 4 99kg
- **EASY INSTALLATION:** Save time with this portable equipment rack that's easy to put together; with its easy four-step assembly process, you can set this portable rack up in minutes
- 4
- **TAA COMPLIANT:** This TAA compliant 4 post open frame rack adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases
- TAA TAAGSA4
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this server rack is backed for life, including free lifetime 24/5 multi-lingual technical assistance
- StarTech.com30IT

---

### Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Enclosed Cabinet
U Height	9U
Special Features	Casters (Included)
	Easy Assembly
	U-Markings
Mounting Rail Profile	L-Shape

Mounting Hole Types      Square (For Cage Nut)

Industry Standards      EIA/ECA-310-E

---

**Performance**

Weight Capacity (Stationary)      297.7 lb [135 kg]

Weight Capacity for Racks (Rolling)      220.5 lb [100 kg]

---

**Special Notes / Requirements**

Note      Dynamic Load Capacity 100.00 kg (220.46 lbs)

Static Load capacity 135.00 kg (297.62 lbs)

---

**Physical Characteristics**

Color      Black

---

**Product Measurements**

Product Length      23.6 in [60 cm]

Product Width      20.3 in [51.5 cm]

Product Height      18.8 in [47.7 cm]

Weight of Product      53.1 lb [24.1 kg]

Maximum Mounting Depth      23.4 in [59.5 cm]

Product Height with Casters      22.1 in [56.2 cm]

---

**Packaging Information**

Flat Pack (Assembly Required)      Yes

Package Length      33.0 in [83.8 cm]

Package Width      28.7 in [73 cm]

Package Height      5.8 in [14.7 cm]

Shipping (Package) Weight      61.4 lb [27.8 kg]

---

**What's in the Box**

Included in Package	2 - Side panel with handles
	1 - Top panel
	1 - Bottom panel
	8 - Plastic corner caps
	32 - M5 (10 mm) Phillips flat-headscrew
	24 - M3 (8 mm) Phillips flat-headscrew
	2 - 2.5 in. caster
	2 - 2.5 in. brakecaster
	16 - M5 (15 mm) bracket screws
	50 - M5 (12 mm) panel screws
	50 - M5 cage nut
	1 - Cage nut tool
	1 - Phillips screwdriver
	1 - Phillips bit
	1 - Instruction manual

---

*\*Product appearance and specifications are subject to change without notice.*