

**960H**WIDESCREEN
DVD-QUALITY**650TVL**CRYSTAL
CLEAR**500GB**30 DAYS
RECORDING+**HDMI**HDTV
VIEWINGWEATHER
PROOFDAY/NIGHT
VISION**USB**EASY
BACKUP**DIY**EASY
INSTALLATION

Compact Security System

4 Channel Digital Video Recorder & 4 Cameras

Know what's happening for peace of mind day & night

- View & record from 4 cameras simultaneously during the day, night, indoors or outdoors
- Includes 4 all-weather, high resolution 650TVL cameras with powerful night vision to 66ft/20m.
- Set & forget by recording continuously from 4 cameras for 30 days* onto a massive 500GB hard drive with motion detection
- Save time & have peace of mind by easily locating incident video, then transfer to USB flash drive
- Connect to the internet in seconds with the latest SwannLink™ encrypted 'Peer-to-Peer' technology - just scan the DVR's unique QR Code
- Surveillance in the palm of your hand with live viewing on 3G/4G-enabled Smartphone & tablets including, iPhone, iPad, Android devices and more* using the free SwannView Plus app
- Fight back against crime by deterring intruders, protecting your property & knowing what's happening at all times

Compact Security System

4 Channel Digital Video Recorder & 4 x Cameras

What's in the box

All installation accessories included

- 4 Channel DVR
- 500GB Hard Drive (installed)
- Day/Night Cameras x 4
- HDMI Cable
- BNC Cables 60ft / 18m x 4
- Power Adapter & Splitter
- Mouse
- Ethernet Cable
- Mounting Screws & Plugs
- Operating Instructions
- Theft Deterrent Sticker



Specifications

4 CHANNEL DVR

Video

Inputs	4 Channels
Outputs	VGA, HDMI
Display Resolution	Up to 1080p

Audio

Input	1 x RCA
Output	1 x RCA

Recording

Compression Format	H.264
Recording Mode	Manual / Motion / Schedule
Recording Resolution	960H
Frame Rate	Up to real-time 25/30fps

Hard Drive

HDD Included	500GB
HDD Capacity	Up to 4TB SATA HDD

Connection

Network Connection	SwannLink P2P
Network Interface	RJ45 x 1
USB Interface	USB 2.0 x 2

General

Operating Power	DC 12V
Dimensions (WxDxH)	7.88" x 7.88" x 1.78" / 200 x 200 x 45mm

Software

Computer Operating System	Windows, Mac OS
Internet Viewing	SwannView Plus
Handheld Device Supported	iOS, Android, 3G/4G Smartphones & Tablets

Day/Night Camera

Video

Video Quality	650 TV Lines
Viewing Angle	55°

Night Vision

Night Vision Distance	66ft/20m
IR Cut Filter	Yes

General

Indoor / Outdoor	Both, IP66 rated
Audio Microphone	No
Operating Power	DC 12V
Operating Temperature	-4°F ~ 122°F / -20°C ~ 50°C
Body Construction	Aluminum
Dimensions (WxDxH)	2.56" x 2.56" x 5.7" / 65mm x 65mm x 145mm
Weight (incl. stand)	0.557lbs / 253g

Code

Swann Code SWDVK-4ALP14

+ 30 days recording achieved using lower settings, default settings give 6 days recording
* Monitor, tablet & mobile phones not included. Not all handset models supported
Note: Trademarks are properties of their respective owners.

Now with

SwannLink™

LINK & SEE YOUR WORLD IN MINUTES!



Free Download
SwannView Plus App



DOWNLOAD FREE APP FROM



Our Promise

Swann stands by its promise of Lifetime Support to make advanced security easy to use, install and maintain. Everything is in the pack but if you need it Swann's help desk is available **24 hours a day, 7 days a week** for the life of the product.

Installation is easy

Do-it-Yourself

Installing this Swann product is simple. For instructions, tips and videos see the operating instructions in this pack or visit www.swann.com

Professional Installation

Need extra help? We have an installer in your region! For more visit www.swann.com

For more information on this product visit www.swann.com