

# WorkForce® Pro WF-6530

Wireless | Print | Copy | Scan | Fax | Ethernet

All-in-One

Workgroup



Powered by

**PRECISIONCORE®**



## The fast, heavy-duty multifunction printer for small workgroups.

**Powered by PrecisionCore®** — the next generation of inkjet printing technology

**Print-shop quality** — print documents and graphics in high resolution with precise dot placement

**Save on ink** — up to 50 percent lower printing costs vs. color lasers<sup>1</sup>

**Fast print speeds** — 24 ISO ppm (black), 24 ISO ppm (color)<sup>†</sup>

**Hassle-free, high-yield cartridges** — print or copy up to 4000 black/color pages without changing cartridges<sup>2</sup>

**High-speed copying and scanning** — single-pass, 2-sided scanning and copying

**Versatile paper handling** — 500-sheet tray, plus 80-sheet rear tray; features auto 2-sided print, copy, scan and fax

**Wireless, Wi-Fi Direct<sup>®3</sup> and NFC<sup>4</sup>** — print from iPad<sup>®</sup>, iPhone<sup>®</sup>, tablets and smartphones<sup>5</sup>; includes remote printing and access to the cloud

**Easy navigation and control** — intuitive 4.3" color touchscreen

**Duty cycle** — up to 50,000 pages monthly<sup>6</sup>

*Designed for use exclusively with Epson cartridges\*.*



**Print**

**Printing Technology** 4-color (CMYK) drop-on-demand MicroPiezo® inkjet technology / PrecisionCore 4S printhead  
**Printer Language** Epson ESC/P®-R  
**Maximum Print Resolution** 4800 x 1200 optimized dpi  
**ISO Print Speed<sup>†</sup>** Black 24 ISO ppm / Color 24 ISO ppm  
**Two-Sided ISO Print Speed<sup>†</sup>** Black 15 ISO ppm / Color 15 ISO ppm  
**Minimum Ink Droplet Size** 3 droplet sizes, as small as 3.7 picoliters  
**Duty Cycle<sup>6</sup>** Up to 50,000 pages (Recommended monthly page volume: up to 4000 pages)

**Copy**

**ISO Copy Speed<sup>††</sup>** Black 19 ISO cpm / Color 19 ISO cpm  
**Copy Quality** Color/Black-and-White: Standard/Best  
**Copy Quantity** 1 – 999 (PC-free)  
**Maximum Copy Size** 8.5" x 14"  
**Copy Features** Auto 2-sided, Preview, Resize, Collate, Adjustable Copy Density, ID Copy

**Scan**

**Scanner Type** Color flatbed / Auto 2-sided ADF  
**Photoelectric Device** Color CIS line sensor  
**Scanned Size** 8.5" x 14"  
**Optical Resolution** 2400 dpi  
**Hardware Resolution** 1200 x 2400 dpi  
**Maximum Resolution** 9600 x 9600 dpi interpolated  
**Scanner Bit Depth** 48-bit color input / 24-bit color output  
**Scan Features** Scan to PC via Document Capture Pro, Scan to Cloud<sup>7</sup> (including email), Memory Device, Password Protected PDF

**Fax**

Black-and-white and Color  
 Modem: 33.6 Kbps – as fast as 3 sec per page  
 Memory: Up to 550 pages  
 Speed dials: 200 (max.)  
 PC-Fax

**Connectivity**

**Standard Connectivity**  
 Hi-Speed USB (compatible with USB 2.0 specification)  
 Wireless (802.11 b/g/n)<sup>3</sup>  
 Wired Ethernet (10/100/1000 Mbps)  
 Wi-Fi Direct<sup>3</sup>  
 NFC<sup>4</sup>

**Connectivity (continued)**

**Operating Systems** Windows® 10, Windows 8.x (32-bit, 64-bit), Windows 7 (32-bit, 64-bit), Windows Vista® (32-bit, 64-bit), Windows XP SP3 (32-bit), Windows XP Professional x64 Edition, Windows Server® 2012 R2<sup>8</sup>, Windows Server 2012<sup>8</sup>, Windows Server 2008 R2<sup>8</sup>, Windows Server 2008<sup>8</sup>, Windows Server 2003 R2<sup>8</sup>, Windows Server 2003<sup>8</sup>, Mac OS® X 10.5.8 – 10.10.x<sup>9</sup>

**Mobile Printing**

**Epson Connect<sup>TM</sup>** Epson Email Print, Epson iPrint™ Mobile App, Epson Remote Print  
**Other** Apple® AirPrint™, Google Cloud Print™, Fire™ OS

**Paper Handling**

**PC-free Paper Support** Plain (Letter, Legal, A4)  
 Photo (4" x 6", 5" x 7", 8" x 10", 8.5" x 11", A4)  
**Maximum Paper Size** 13" x 47.2"  
**Paper Sizes** 3.5" x 5", 4" x 6", 5" x 7", 8" x 10", 8.5" x 11", A4, A6, half letter, executive, user definable (3.5" – 47.2" in length)  
**Paper Types** Plain paper, Bright White Paper, Presentation Paper Matte, Premium Presentation Paper Matte, Premium Presentation Paper Matte Double-sided, Premium Photo Paper Glossy, Ultra Premium Photo Paper Glossy, Premium Photo Paper Semi-gloss  
**Envelope Types** No. 10; plain paper, bond paper, air mail  
**Input Paper Capacity**

500 sheets plain paper (500 sheets plain paper x 1 tray)  
 Rear feed: 80 sheets  
 10 envelopes  
 Auto Document Feeder: 50 sheets

**General**

**Display** 4.3" color touchscreen  
**Temperature**  
 Operating: 50 ° to 95 °F (10 ° to 35 °C)  
 Storage: -4 ° to 104 °F (-20 ° to 40 °C)  
**Relative Humidity**  
 Operating: 20 – 80%  
 Storage: 5 – 85% (no condensation)  
**Sound Level**  
 Power: 6.5 dB(A)  
 Pressure: 50 dB(A)

**General (continued)**

**Rated Voltage** AC 100 – 240 V Universal (Automatic)

**Rated Frequency** 50 – 60 Hz

**Rated Current** 1.2 A – 0.6 A

**Power Consumption**

Approx. 36 W ISO 24712 (Standalone copy printing)

Approx. 16 W (Standby)

Approx. 2.7 W (Sleep)

Approx. 0.5 W (Power off) ENERGY STAR® qualified

**Safety Standards** UL60950, CSA C22.2 No. 60950

EMI FCC Part 15 subpart B class B,

CAN/CSA-CE/IEC CISPR 22 class B

**Telecom Regulations** FCC Part 68 (U.S.A.), IC/CS03 (Canada)

**Country of Origin** Indonesia

**Weight and Dimensions (W x D x H)**

Printing: 20.3" x 29.8" x 21.3"

Storage: 20.3" x 20.6" x 20.2"

Weight: 68.3 lb

**What's in the Box** Epson WorkForce Pro WF-6530 multifunction printer, CD-ROM for product setup, power cord, DURABrite® Pro Ink cartridges<sup>2</sup> – Four 748 series ink cartridges: Black, Cyan, Magenta, Yellow

**Software Included<sup>10</sup>** Epson printer driver, Document Capture Pro

**Warranty** One-year limited warranty in the U.S. and Canada

**Ink**

**Ink Type** DURABrite Pro pigment ink (smudge, fade and water resistant)

**Ink Palette** Cyan, Magenta, Yellow and Black

**Ink Cartridge Configuration** Four individual ink cartridges

**Replacement Ink Cartridges<sup>2</sup>**

748 Standard-capacity Black, Cyan, Magenta, Yellow (Yield, ISO pages – Black: 2500, Color: 1500)

748XL High-capacity Black, Cyan, Magenta, Yellow (Yield, ISO pages – Black: 5500, Color: 4000)

Printer is designed for use with Epson cartridges only, not third-party cartridges or ink. [www.epson.com/cartridgereturn](http://www.epson.com/cartridgereturn)\*

**Eco Features**

Uses up to 70% less power than laser printers<sup>11</sup>

Save up to 50% of your paper supply with auto 2-sided printing

ENERGY STAR qualified

RoHS compliant

Recyclable product<sup>12</sup>

Epson America, Inc. is a SmartWay<sup>SM</sup> Transport Partner<sup>13</sup>

**Ordering Information**

WorkForce Pro WF-6530

C11CD48201

\*This product uses only genuine Epson-brand cartridges. Other brands of ink cartridges and ink supplies are not compatible and, even if described as compatible, may not function properly.

† Black and color print speeds are measured in accordance with ISO/IEC 24734. Actual print times will vary based on system configuration, software, and page complexity. For more information, visit [www.epson.com/printspeed](http://www.epson.com/printspeed) | †† Black and color copy speeds are determined in accordance with ISO/IEC 29183. Actual copy times will vary based on system configuration and page complexity. For more information, visit [www.epson.com/copyspeed](http://www.epson.com/copyspeed) | 1 Compared with best-selling, color multifunction laser printers priced at \$499 (USD) or less, as of June 2015. Calculation based on continuous printing with highest capacity individual cartridges. Actual savings will vary based on print task and use conditions. | 2 748XL Black cartridge prints about 5000 ISO pages. 748XL color cartridges print about 4000 ISO pages on average. Actual number of pages will vary. Replacement cartridge yields are based on ISO/IEC 24711 tests in Default Mode printing continuously. Cartridge yields vary considerably for reasons including images printed, print settings, temperature and humidity. Yields may be lower when printing infrequently or predominantly with one ink color. All ink colors are used for printing and printer maintenance, and all colors have to be installed for printing. For print quality, part of the ink from the included cartridges is used for printer startup and a variable amount of ink remains in the cartridges after the "replace cartridge" signal. For details, see [www.epson.com/cartridgeinfo](http://www.epson.com/cartridgeinfo) | 3 Wi-Fi CERTIFIED™; level of performance subject to the range of the router being used. Wi-Fi Direct may require printer software. | 4 NFC requires use of a device that includes NFC, and may require additional software. | 5 Most features require an Internet connection to the printer, as well as an Internet- and/or email-enabled device. For a list of Epson Connect enabled printers and compatible devices and apps, visit [www.epson.com/connect](http://www.epson.com/connect) | 6 Monthly duty cycle up to 50,000 is the highest duty a user could expect in a month, based on near-constant operation of a device of this kind. It is not recommended that the device be run at this duty. For best device performance, run the device at the recommended duty of 4000 pages per month. | 7 Requires an Internet connection, a free Epson Connect account and a destination email address or cloud storage account. For a list of supported cloud services, visit [www.epson.com/connect](http://www.epson.com/connect) | 8 Only printing and scanning are supported under Windows Server OS. | 9 Some applications and/or functions may not be supported under Mac OS® X. | 10 Internet access is required to install OS X® drivers and software. | 11 Compared to best-selling, color laser multifunction printers priced at \$399 (USD) or less as of July 2013. Actual power savings will vary by product model and usage. | 12 For convenient and reasonable recycling options, visit [www.epson.com/recycle](http://www.epson.com/recycle) | 13 SmartWay is an innovative partnership of the U.S. Environmental Protection Agency that reduces greenhouse gases and other air pollutants and improves fuel efficiency.

**Better Products for a Better Future™**  
[eco.epson.com](http://eco.epson.com)

**Epson America, Inc.**  
 3840 Kilroy Airport Way, Long Beach, CA 90806



**Epson Canada Limited**  
 185 Renfrew Drive, Markham, Ontario L3R 6G3



[www.epson.com](http://www.epson.com)  
[www.epson.ca](http://www.epson.ca)