

## 10/100Mbps Ethernet to USB 2.0 Network LPR Print Server

StarTech ID: PM1115U2



This palm-sized print server makes it easy to share a USB printer with users on your network. It's the ideal solution for home or small office networks.

### **Reliable, cost-efficient network printing**

Enjoy cost-efficient network printing for multiple users. The USB 10/100 Mbps print server lets you share one USB printer with multiple users on your network, instead of having to buy separate printers for each individual workstation.

### **Place your shared printer in a convenient location**

With web-based management, you can set up and monitor the printer server through a web browser, so you can place your printer at any convenient shared location - there's no need to put your printer next to your computer. You can send print jobs to another user in your home or office, or even to a printer in another country.

### **Easy to use and install**

Compact and lightweight, the print server is easy to install with its straightforward installation wizards and remote web-based management. You simply use a USB cable to connect the print server to your printer's USB port, then use an RJ45 networking cable to connect it to the rest of your network.

### **Supports LPR network printing and Bonjour Print Services**

The printer server supports the Line Printer Remote (LPR) protocol which enables Internet printing. It also supports Bonjour Print Services, making it easier to find and configure printers on your network.

The PM1115U2 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Applications

- Allows multiple users on an Ethernet network to share one USB printer
- Provides a reliable network printing solution for home, small office, educational and government institutions and any other environments that require printer sharing

## Features

- Share a single USB printer with multiple users over a network
- Print from any network computer, across the office or over the Internet
- Provides a reliable Ethernet connection with 10Base-T/100Base-TX auto-sensing
- Compliant with USB 2.0
- Compatible with most standard printers
- Easy to configure using Windows based setup program or web-based management
- Supports LPR network printing, Bonjour Print Services
- Full-duplex support
- Jumbo frame support
- Auto MDI-X support
- Compact housing

**Technical Specifications**

Warranty	2 Years
Color	Black
Enclosure Type	Plastic
Product Height	1 in [25 mm]
Product Length	2.2 in [55 mm]
Product Weight	2.1 oz [60 g]
Product Width	2 in [52 mm]
Chipset ID	EST2862B
Industry Standards	Compliant with IEEE 802.3 10BASE-T and IEEE 802.3u 100BASE-TX
Ports	1
Auto MDIX	Yes
Full Duplex Support	Yes
Jumbo Frame Support	9K max.
Max Distance	100 m / 330 ft
Maximum Data Transfer Rate	100 Mbps
Remote Management Ability	Yes
Supported Protocols	LPR
External Ports	1 - RJ-45 Female
External Ports	1 - USB A (4 pin) Female
OS Compatibility	Windows® 8 / RT (32/64bit), 7 (32/64) Windows Server® 2012 (32/64), XP, 2008 R2, 2003 Mac OS® 10.x (Tested up to 10.10)
<b>Note</b>	OS Compatibility refers to the included software only - the Print Server itself can be used without software on most platforms that support network printing
System and Cable Requirements	Printer with USB connection
System and Cable Requirements	USB printer cable not included
LED Indicators	1 - Power

LED Indicators	1 - Link
LED Indicators	1 - Activity
Center Tip Polarity	Positive
Input Current	0.3
Output Current	1A
Output Voltage	5 DC
Plug Type	B
Power Consumption	200mA
Power Source	AC Adapter Included
Humidity	10% ~ 90% RH
Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	-10°C to 70°C (14°F to 158°F)
Shipping (Package) Weight	9.9 oz [280 g]
Included in Package	1 - USB 2.0 network LPR print server
Included in Package	1 - universal power adapter (NA / UK / EU, AU)
Included in Package	1 - RJ45 network cable
Included in Package	1 - quick start guide
Included in Package	1 - software CD

Certifications, Reports and Compatibility

