

Q2963PQ



16.7M colors	DCR	D	e	e-saver	hairline texture	HDMI	i-menu
IPS	LED	MHL	narrow bezel	screen+	VESA mount	windows 8	

MODEL: Q2963PQ DATA SHEET

GENERAL FEATURES

panel type:	IPS
screen size:	29"
viewable image size:	29"
aspect ratio:	21:9
brightness:	300 cd/m2
contrast ratio (DCR):	50,000,000:1
pixel pitch (H x V):	0.263 x 0.263 mm
display area (H x V):	672.77 x 283.82 mm
viewing angle:	horizontal ° x vertical 178° (CR >= 10)
response time:	5 ms
color:	black, black w/ texture

SCANNING FREQUENCY

scanning frequency:	horizontal: Hz vertical: 50~76 Hz
---------------------	--------------------------------------

RESOLUTION

max resolution:	2560 x 1080 @ 60 Hz
recommended resolution:	2560 x 1080 @ 60 Hz
color resolution:	16.7 million

POWER

power source:	110~240 VAC
power consumption:	ON: <95 W STANDBY: <0.5 W

OTHER FEATURES

user control:	
plug and play:	NA
speakers:	yes - 3 watts x 2
web cam:	no
headphone out:	NA
wall mount:	yes - 100 x 100 mm
height adjustable:	NA
tilt:	-3° ~ 21°

SIGNAL INPUT

analog D-sub 15 pin:	1 x VGA
DVI-D 24-pin:	1 x DVI-D
HDMI:	0 x HDMI
HDMI w/MHL:	1 x HDMI w/MHL
USB 2.0:	0 x USB 2.0
USB 3.0:	0 x USB 3.0
display port (in):	1 x DP (in)
display port (out):	0 x DP (out)
support MHL:	NA

REGULATIONS

Energy Star, CE, FCC, RoHS Compliant, cTUVus

SOFTWARE

i-Menu / e_Saver / Screen+

IN THE BOX

VGA Cable, HDMI Cable, Power Cord, User Manual, Warranty Card, Driver, AOC Software, Audio Cable

LOADING QUANTITY

20' container loading w/ pallet:312
40' STD container loading w/ 728
pallet:

DIMENSIONS

product with stand (WxHxD):
714mm x 388mm x 233mm
28.1" x 15.3" x 9.2"

packaging (WxHxD):
383mm x 524mm x 186mm
32.9" x 20.63" x 7.32"

weight (NET):	7.16 kg 15.78 lbs
weight (GROSS)	10.4 kg 22.92 lbs
warranty:	3 years
UPC code:	685417705887