



Hi-Speed 13-Port Desktop USB Hub

13 Ports, USB 2.0, AC/Bus Power Hub with Multiple Transaction Translator and 2.4 A Fast Charge Capable

Part No.: **162463**

Powerful USB performance in a multiport hub.

The Manhattan Hi-Speed USB Desktop Hub easily expands USB access for desktop and notebook computers to connect more peripherals and mobile devices. With 13 extra high-speed, backward-compatible ports and a high-capacity 4-amp power adapter, the Manhattan Hi-Speed USB Desktop Hub can manage almost any digital enthusiast's growing collection of USB-enabled devices. It's ideal for recharging MP3 players, digital cameras and other mobile accessories and connecting keyboards, mice, webcams, flash drives, card readers and more. Fast charging capabilities for iPhone, iPad, Galaxy Tab, Galaxy Smartphones and more, from four specified ports, with button when data transmission is suspended. The compact and durable plastic case features the 3.5mm 5VDC power jack and built-in USB Data Transfer/Power cable on the side panel and Data Transfer/ Fast Charge control button on the top to help better organize connections, minimize cable clutter and allow easy access control. Plug and play with hot-swap capabilities, Windows and Mac compatibility and data transfer speeds up to 480 Mbps help the Manhattan Hi-Speed USB Desktop Hub consolidate numerous, less-capable hubs into a single USB solution.

Features:

- Provides 13 Hi-Speed USB 2.0 ports for additional peripherals
- Replaces less-capable hubs with compact multiport design and high-capacity 4-amp power adapter
- Fast charge a mobile device, up to 2.4 A, with control button
- Versatile bus or AC powered with overcurrent protection, integrated secondary USB cable for additional bus power
- Plug and play; hot-swappable
- Compatible with all USB-equipped computers
- Windows and Mac compatible
- Three-Year Warranty

Specifications:

Standards and Certifications

- USB 2.0, USB 1.1, USB 1.0

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- FCC
- CE

Ports

- Transfer speeds: 1.5 / 12 / 480 Mbps
- 2 upstream ports, Standard-A
- 13 downstream ports, Standard-A
- 5VDC port
- Up to 500 mA power, all ports
- Up to 2.4 A power, 1 port (with data transfer turned off), capable in ports 5-8
- Multiple Transaction Translator (MTT) capable in ports 1-4, 9

Physical

- Dimensions: 121 x 71 X 25 mm (4.8 x 2.8 x 1 in.)
- Weight: 147 g (5.2 oz.)
- Integrated USB cable, Standard-A, 100 cm (39 in.)
- Includes secondary integrated USB cable, Standard-A
- Data Transfer / Charge button; On/Off
- Housing: ABS plastic
- LED power indicator

Power Adapter

- cUL, FCC
- Input: 100 - 240 V, 50/60 Hz; 0.68 A, maximum
- Output: 5 V / 4 A
- Cable: 1.8 m (6 ft.)

System Requirements

- USB-enabled PC or Mac system
- Windows XP/Vista/Windows 7/8/10 or Mac OS 9 or above
- Available USB port

Package Contents

- Hi-Speed USB Desktop Hub
- Power adapter
- Instructions



