


10-Port USB Charging Station with Adjustable Storage, 12V 8A (96W) USB Charger Output

MODEL NUMBER: **U280-010-ST**



Charges up to 10 electronic devices, including tablets, cell phones and laptops, at the same time via USB connection. Neatly organizes the devices within its adjustable storage brackets while charging.

Description

Whether you're at home or in the office, Tripp Lite's U280-010-ST 10-Port USB Charging Station provides plenty of ports and power to keep all your devices at 100% capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. You can charge up to ten tablets, cell phones, laptops and other devices at the same time. It doesn't require a computer, so you can take it anywhere AC power is available.

To charge your USB devices, simply plug the included external dual-voltage (100V–240V) power supply into any NEMA 5-15R outlet, and connect your devices to the available USB ports. The charger protects against overheating, overcurrent and overcharging—in fact, it stops charging as soon as your devices' batteries are at full capacity. A front LED indicates the unit is turned on and receiving AC power.

The U280-010-ST delivers up to 5V, 2.4A to each port (5V/1.92A when fully loaded), which is perfect for charging even battery-intensive devices like the Apple® iPad®. Plus, adjustable brackets on top of the charger allow it to also act as storage, providing space to neatly organize devices while they charge. You can adjust the brackets to accommodate the number and size of the devices being charged.

Features

Charges Up to 10 Devices at the Same Time Ideal for charging tablets, cell phones, laptops and other devices at home or work. Connect devices to unit's USB ports for proficient charging. Charges anywhere AC power is available—no computer required.

Provides Plenty of Juice for Charging Delivers up to 5V, 2.4A per port, enough for charging battery-intensive devices like the Apple iPad®. Protects against overheating, overcurrent and overcharging* When fully loaded the output per port becomes 5V/1.92A.

Also Functions as Efficient Storage Includes 14 adjustable brackets that neatly organize devices while they charge. Brackets are adjustable to accommodate number and size of devices being charged.

Easy to Use Included external dual-voltage (100–240V) power supply plugs into any NEMA 5-15R outlet. Front LED indicates when unit is turned on and receiving AC power.

Highlights

- Up to 5V, 2.4A per port for charging battery-intensive devices
- External dual-voltage power supply with NEMA 5-15P plug
- Protects against overheating, overcurrent and overcharging
- Includes 14 adjustable storage brackets for organizing devices
- Charges anywhere AC power is available—no computer required

System Requirements

- For international use, the P058-006 (Europe) or P060-006 (UK) power cords can be purchased separately

Package Includes

- 10-Port USB Charging Station
- External Power Supply with C6 Inlet (Input: 100–240V, 50/60 Hz, 2A; Max Output: 12V, 8A, 3 ft.)
- C5 to 5-15P Power Cord
- (14) Storage brackets
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332190352
Product Type	Charging Station
Charging Form Factor	Charging Hub
AC Adapter	100-240V, 50/60Hz, 3A; Output: 12V, 8A, 3-ft.
Device Compatibility	Phone; Tablet; Amazon Kindle
Technology	USB
INPUT	
External Power Supply Plug(s)	NEMA 5-15P North America
OUTPUT	
Output Capacity	96W
Overload Protection	Yes
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V, 50/60Hz, 3.0A MAX
External Power Supply Output Specs (V / A)	12V/8A
External Power Supply Cord Length (m.)	1
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	CCC; CE; FCC; GS; PSE; RoHS; TUV; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power)
CHARGING	
Charging Ports / Amps	(10) 2.4A
Number of Charging Ports	10
Total Charging Amps	19.2A
Charging Method	USB
Total Charging Watts	96
Charging Ports Detail	USB-A: Up to 5V/2.4A
Charging Port Type	(10) USB A (FEMALE)
Charging Method Detail	USB-A: 5V/Max 2.4A Apple Fast Charge

PHYSICAL	
Color	Black
Material of Construction	Polycarbonate
Shipping Dimensions (hwd / cm)	7.90 x 26.90 x 15.60
Shipping Dimensions (hwd / in.)	3.11 x 10.59 x 6.14
Shipping Weight (kg)	1.23
Shipping Weight (lbs.)	2.71
Unit Dimensions (hwd / cm)	2,5 x 23,8 x 13,4
Unit Dimensions (hwd / in.)	1 x 9.4 x 4.7
Unit Packaging Type	Box
Unit Weight (kg)	0.26
Unit Weight (lbs.)	0.57
ENVIRONMENTAL	
Operating Temperature Range	41 to 95 F (5 to 35 C)
Storage Temperature Range	-4 to 122 F (-20 to 50 C)
Relative Humidity	20% to 80% RH, Non-Condensing
Power Consumption (Watts)	34
CONNECTIONS	
Ports	10
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	(10) USB A (FEMALE)
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
SPECIAL FEATURES	
Overcurrent Protection	Yes
Oversupply Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Certifications	EN 55022: 2010/AC: 2011, EN 55024: 2010, FCC Class B, RoHS, REACH
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	2-year limited warranty
--	-------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>