



19" Double Section Wallmount Cabinet

9U, Double Section, Assembled, Black

Part No.: **711845**

Intellinet Double-Section wallmount cabinets offer you a flexible solution for your network installations. The tempered-glass door, easily removable side panels and cold-rolled galvanized steel are just some of the top quality workmanship and materials that are standard. These cabinets ship completely assembled for a quick and easy installation.

Features:

- Ideal for 19" rackmount applications
- Maximum static load of 30 kg
- Tempered-glass door can be opened more than 180°
- Rear door for easy access to back of cabinet
- Cold-rolled, galvanized SPCC steel with up to 1.2 mm thickness
- Reversible Front door
- Antistatic powder coating on all panels
- Easily removable side panels
- Ships assembled
- Three-Year Warranty

Specifications:

General

- 19"
- Height: 9U
- Color: Black RAL9005
- Complies with: ANSI/EIA RS-310-D; IEC60297-2; DIN41494, Part 1; DIN41494, Part 7

Dimensions

- 500 (h) x 600 (w) x 550 (d) mm
- 19.7 (h) x 23.6 (w) x 21.7 (d) in.

Package Contents

- Double section wall mount
- Installation hardware



