



19" Wallmount Cabinet

15U, Flatpack, Black

Part No.: **711937**

Intellinet wallmount cabinets offer you a flexible and comprehensive solution for your network installations. Top quality materials and workmanship include cold-rolled, galvanized steel frame, antistatic powder coating and a tempered-glass door; while the flat-pack (unassembled) shipping* saves you space and money.

*Completely assembled versions are available in certain countries.

Features:

- Ideal for 19" rackmount applications
- Maximum static load of 60 kg
- Tempered-glass door can be opened more than 180°
- Cold-rolled, galvanized SPCC steel with up to 1.2 mm thickness
- Antistatic powder coating on all panels
- Reversible Front door
- Easily removable side panels
- Ships flatpacked
- Three-Year Warranty

Specifications:

General

- 19"
- Height: 15U
- Color: Black RAL9005
- Complies with: ANSI/EIA RS-310-D; IEC60297-2; DIN41494, Part 1; DIN41494, Part 7

Dimensions

- 770 (h) x 570 (w) x 450 (d) mm
- 30.3 (h) x 22.4 (w) x 17.7 (d) in.

Package Contents

- 2 depth-adjustable mounting rails
- Installation hardware



