

Acer recommends Windows 8.



Aspire Switch 10

SW5-012P

A 2-in-1 as versatile as you are

- A spectacular view
- Smooth versatility
- Dynamic productivity

ETOUCH

MORE BRILLIANT



P/N: NT.L6LED.003
EAN: 4713147217977
Model: SW5-012P-12F7



Acer recommends Windows 8.

SPECIFICATIONS

Aspire Switch 10
SW5-012P



Product views	1 HD webcam 2 10.1" touch display with 1280 x 800 HD resolution 3 Dual speakers 4 Keyboard hooks	5 Keyboard connector 6 Microphone 7 MicroSD™ card slot 8 Micro USB port 9 Micro HDMI™ port	10 DC-in jack for AC adapter 11 Multi-gesture touchpad 12 FineTip keyboard 13 Headphone/speaker jack 14 Power button	15 Volume button 16 Home button 17 USB 2.0 port (on keyboard)			
Operating system¹ Windows 8.1 Professional 32-bit							
CPU and chipset¹ Intel® Atom™ processor Z3735F							
Memory^{1, 2, 3} Single-channel DDR3L SDRAM support: 2 GB of onboard DDR3L system memory							
Display⁴ 10.1" display with IPS (In-Plane Switching) technology, HD 1280 x 800 resolution, high-brightness LED-backlit TFT LCD with integrated multi-touch, supporting 10-finger touch							
16:10 aspect ratio		Wide viewing angle		Super-slim design			
Graphics¹ Intel® HD Graphics with 3D graphics hardware acceleration							
Audio Two built-in stereo speakers		Built-in digital microphone					
Storage⁶ Card reader • microSD™ Card • 64 GB eMMC							
Webcam¹ Video conferencing: Acer Crystal Eye HD webcam with 1920 x 1080 resolution and 1080p Full HD audio/video recording							
Wireless and networking^{1, 6, 7} WLAN • 802.11b/g/n wireless LAN		WPAN • Bluetooth® 4.0					
Privacy control¹ Trusted Platform Module (TPM) solution							
Dimensions and weight⁸ Dimensions		Weight 0.585 kg (1.29 lbs.) with 2-cell battery pack 1.17 kg (2.58 lbs.) with 2-cell battery pack, pad and dock 1.2 kg (2.65 lbs.) with 2-cell battery pack, pad and dock with hard drive					
Power adapter and battery Power adapter 2-pin 18 W AC adapter		Battery • 22 Wh 5910 mAh 3.8 V 2-cell Li-polymer battery pack • Battery life up to 8 hours					
Input and control Keyboard: 83-/84-/87-key, 95% full-size Acer FineTip keyboard with international language support Touchpad: Multi-gesture touchpad, supporting two-finger scroll and pinch. Swipes access charms, application commands, Microsoft Precision Touchpad Certification Control Keys: Volume up and down keys, Windows key							
Sensors Accelerometer (G-sensor) E-compass Gyroscope Ambient light sensor							
Windows Store Apps⁹ Content • Amazon® Kindle • CANAL TOUCH • eReadingNow • Hulu • Hulu Plus • iQIYI • iStoryTime Library • LeTV In-House • Acer Docs • Acer Media • Acer Photo • Acer Portal							
Content • LOVEFILM® web link • Spotify In-House • Acer Remote Files • Acer Video Player • Accessory Store • Identity Card • Live Updater • Quick Access • Recovery Management							
Windows Desktop Apps⁹ Lifestyle • Agoda web link • Booking.com web link • Hao123 web link • Yandex web link • Yandex.Disk Desktop							
Options and accessories 2-pin 18 W AC adapter Micro USB 2.0 to USB 2.0 cable							
Warranty One-year International Travelers Warranty (ITW)							
<ol style="list-style-type: none"> 1. Specifications vary depending on model. 2. Shared system memory may be allocated to support graphics, depending on system memory size and other factors. Actual system memory available to the operating system will be reduced by any memory used by the graphics solution and resources required by the operating environment. 3. Memory speed may vary, depending on the CPU, chipset or memory fitted. 4. All brands and product names mentioned herein include trademarks of their respective companies and are used solely to describe or identify the products. 5. 1 GB is 1 billion bytes, 1 TB is 1000 GB. Actual formatted capacity is less and may vary depending on preloaded materials and operating environment. Acer Recovery Management uses a portion of the stated hard disk capacity as dedicated backup space. 							
<ol style="list-style-type: none"> 6. Actual throughput may vary depending on network conditions and environmental factors such as network traffic or overhead, building construction and access point settings. 7. Subject to availability. 8. Weight may vary depending on product configuration, vendor components, manufacturing variability, and selected options. 9. Bundled software may vary depending on hardware configuration, OS and regional availability. 							

In a continuing effort to improve the quality of our products, information in this document is subject to change without notice. Images shown are only representations of some of the configurations available for this model. Availability may vary depending on region.

As a phenomenon known to thin-film transistors (TFTs), liquid crystal displays (LCDs) commonly exhibit a small number of discoloration dots, as so-called "non-conforming pixels." This phenomenon is a limitation of TFT LCD technology, not a product defect, and as such is not covered by Acer's warranty.

© 2014. All rights reserved.

Microsoft and Windows are registered trademarks of Microsoft Corporation. Intel, Intel Core, Core Inside, Pentium, Pentium Inside and Celeron are trademarks of Intel Corporation in the U.S. and other countries.

About Acer

Established in 1976, Acer is a *hardware + software + services* company dedicated to the research, design, marketing, sale and support of innovative products that enhance people's lives. Acer's product offering includes PCs, displays, projectors, servers, tablets and smartphones — tools our customers need to explore beyond limits and experience more. Acer employs 7,400 people and ranks No. 4 for total PCs globally (IDC 2013). Revenues for 2013 reached US\$12.02 billion. Please visit www.acer.com for more information.

acer
explore beyond limits™