

THE LENOVO® THINKCENTRE® M32 THIN CLIENT

EXCELLENT MANAGEABILITY, POWERFUL PERFORMANCE
AND ROCK-SOLID RELIABILITY



EXPANDING THE THINK BRAND
WITH THE LATEST PREMIUM
LENOVO® THIN CLIENT



FAN-LESS CABLE-LESS DESIGN

Lower power consumption
and zero noise



VARIETY OF I/O SUPPORT

6 USB, 4 Serial, 2 PS/2,
1 Parallel Port



CHOOSE YOUR OS

Windows Embedded Standard 7
or Lenovo® Terminal Operating
System (customized Linux)



LENOVO THIN CLIENT MANAGER (LTM)

Browser-based LTM allows
you to remotely manage
your Thin Clients

The Lenovo® ThinkCentre® M32 delivers outstanding performance and manageability. The Thin Client uses an Intel® Ultra-Low Voltage Celeron® processor for enhanced performance, together with preloaded Lenovo® Thin Client Manager, the latest web-based management platform for virtual desktop deployments. Finally, the Thin Client offers more I/O options for better productivity and, with its fan-less and cable-less design, saves on power consumption and optimizes space management.

THINKCENTRE® M32

THE LENOVO® THINKCENTRE® M32 THIN CLIENT

OUTSTANDING FEATURES

- Intel® Ultra-low voltage Celeron® platform—balancing cost, performance, and low power consumption
- Windows Embedded Standard 7 or Customized LeTOS Linux OS flexibility
- Dual Display Support to connect two monitors using either a VGA port or a DisplayPort—save on the cost of buying an additional graphic card
- Minimize noise and extend lifecycle with fan-less design
- Connect to various devices easily with a variety of input / output ports

SIMPLIFIED RELIABILITY AND MANAGEMENT

- Clutter-free with cable-less design
- Citrix® Receiver, VMWare® View and Microsoft Remote FX compatibility for better manageability

LENOVO® THIN CLIENT MANAGER (LTM)

- Web-based application—gives administrators freedom to access the console from any terminal
- Manage Thin Clients individually or by groups
- Delivered as a virtual appliance for easy installation on Hyper-V, XenServer™, or VMWare®
- User friendly—intuitive layout, context menus with greater variety and utility, and detailed menus make it easy to quickly access different options
- Licensed with the Thin Client product at no extra cost and three years of free software



SOFTWARE

PRELOADED APPLICATIONS

Lenovo® Terminal Operating System (LeTOS)

- rDesktop
- xfreerdp
- Citrix / XenApp View
- VMWare® View
- Mozilla Firefox®
- NX Client

Windows Embedded Standard 7 (WES 7)

- RDP Client
- Citrix Client
- VMWare® Client
- Internet Explorer
- .NET Framework
- Microsoft Silverlight
- Ultra VNC
- Adobe Reader

Lenovo® Thin Client Manager (LTM)

Powerful browser-based Lenovo® Thin Client Manager (LTM) application allows you to manage your Thin Client devices individually or in groups from anywhere on your network.

- Install new software, updates, patches, etc.
- Create / manage user profile settings
- Manage terminal settings
- Capture / restore images (cloning)
- Manage inventory
- A complete network management solution for your Thin Client assets

SPECIFICATIONS

PROCESSOR

Intel® Celeron® processor 807 (1.5 GHz)

OPERATING SYSTEM

Windows Embedded Standard version 7 (WES 7)
 Lenovo® Terminal Operating System
 (LeTOS – a custom Linux build)

PORTS AND SLOTS

- (4) Front USB 2.0
- (2) Rear USB 2.0
- (2) PS/2
- (1) VGA out
- (1) DP out

GRAPHICS

Intel® Integrated graphics

ETHERNET

RealTek® RTL8111F Gigabit Ethernet

MEMORY

1 SO-DIMM
 Up to 4GB, 1600 MHz, DDR3

STORAGE

WES 7
 8GB Solid State Media

DIMENSIONS (W x D x H)

220 mm x 55 mm x 170 mm
 (8.66" x 2.16" x 6.69")

WEIGHT

1.48 kg (3.26 lbs)

PHYSICAL SECURITY

Kensington lock

CHIPSET

Intel® NM70

PSU

65 W adapter

ACCESSORIES FOR THINKCENTRE® M32 THIN CLIENT



ThinkVision® Monitor



DisplayPort to Dual-DisplayPort Monitor Cable



Kensington Microsaver security cable lock from Lenovo®



Lenovo® Ultraslim Wireless Keyboard and Mouse Combo

LENOVO® SERVICES

Lenovo® offers a comprehensive portfolio of award-winning services to support and protect your ThinkCentre® investment. Succeed with substance and let Lenovo®'s service support you all the way.

Priority Technical Support¹

Makes your priority, our priority. 24x7 priority call routing to advanced-level technicians, electronic incident tracking, and escalation management services.

Warranty Upgrades – Onsite and Next Business Day

Maximizes PC uptime and productivity by providing convenient, fast repair service at your place of business.

Warranty Extensions (1-to-5 Years Total Duration)

This fixed-term, fixed-cost service helps accurately budget for PC expenses, protect your valuable investment, and potentially lower the cost of ownership over time.

Asset Tagging

Systems come equipped with a professional, flexible asset tag based on your exact specifications. PCs are easily identifiable and trackable right out of the box.

¹ Not available in all regions

©2013 Lenovo. All rights reserved.

Availability: Offers, prices, specifications and availability may change without notice. Lenovo is not responsible for photographic or typographic errors. **Warranty:** For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC, 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. **Trademarks:** Lenovo, the Lenovo logo, Rescue and Recovery, ThinkStation, ThinkVantage and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Core, Core Inside, Xeon and Xeon Inside are registered trademarks of Intel Corporation in the U.S. and other countries. Other company, product and service names may be trademarks or service marks of others. Visit Lenovo.com/safecomputing periodically for the latest information on safe and effective computing.