

2-Post Server Rack with Casters - 42U

StarTech ID: 2POSTRACK42



Store your server, network and telecommunications equipment in this sturdy 42U rack. With a 2-post design, the TAA compliant rack saves floor space and its dual-post, open-depth design makes it broadly compatible with longer equipment.

Maximum portability

The 2-post rack features four swiveling casters, so you can easily move it around in your server room, office or studio. It's easy to reposition or relocate the rack in order to connect your rack-mounted equipment to other devices throughout your workspace.

High durability

The durable dual-post server rack is made of heavy-gauge steel, instead of aluminum, to ensure a stable installation platform. The rack supports a static loading capacity of up to 1200 lb. (544 kg), and it's compliant with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494), to provide a stable platform that eliminates the need for concrete mounting kits.

Wide compatibility

You can easily mount your ANSI/EIA RS-310-D compliant network equipment to the rack without using additional hardware. It features square mounting holes on the frame and a universal design that's compatible with most rack equipment.

The 2POSTRACK42 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Use in your server room or any location where telecommunication and networking equipment needs to be housed
- Create a portable video editing and production rack that you can move around your studio to interface with different equipment

Features

- Superior durability and stability with full-steel construction
- Maximum portability with four swiveling casters for easy transportation
- Widely compatible with most rack-mountable equipment with square mounting holes and a 2-post open frame design
- 42U of mounting space
- TAA compliant
- Mount standard networking equipment using standard cage nuts and screws
- Easy assembly at the point of installation for rapid deployment

Technical Specifications

Warranty	2 Years
Casters	Included
Fan(s)	No
Frame Type	Open Frame
Front Door Type	Open
Industry Standards	DIN41491 Part I
Industry Standards	DIN41491 Part VII
Industry Standards	EIA RS310-D
Industry Standards	GB/T3047.2-92
Industry Standards	IEC297-2
Rack Type	2-Post
U Height	42U
Wallmountable	No
Weight Capacity	5295 oz [150000 g]
Shipping (Package) Weight	55.3 lb [25 kg]
Included in Package	2 - bottom supporting beams
Included in Package	2 - vertical rails
Included in Package	2 - horizontal rails
Included in Package	2 - angle support beams
Included in Package	2 - 2" heavy-duty casters
Included in Package	2 - 2" heavy-duty locking casters
Included in Package	30 - M6 screws
Included in Package	26 - M6 nuts
Included in Package	16 - M6 caster screws
Included in Package	32 - M6 cage nuts
Included in Package	32 - M6 rack screws with plastic washers
Included in Package	1 - Allen key 4mm
Included in Package	1 - quick install guide

Certifications, Reports and Compatibility

