



CADENCE

ZRS

ZRS-6KM

6.5 inch



TS PARAMETERS

FMS: 128.2 Hz	BL: 4.7 N/A
QMS: 2.98	SPL: 103 dB
QES: 0.96	VAS: 5.3
QTS: 0.72	RE: 3.2 Ohm
RES: 7 Ohm	RP: 10.4 Ohm
RMS: 2.3 kg/s	LP: 4.9 mH
CMS: 0.19 mm/N	CP: 516.6 μ F
MMS: 8.3 gr	LE: 0.3 mH
NREF: 1.13 %	

4 Ohm


150 Watts

SPECIFICATIONS

Application: High SPL Midrange Drivers
Basket Type: Stamped Steel
Dust Cap: Bullet Phase Plug
Surround Style: Laminated Cloth Accordion
Structure Weight: 50 oz.
1.25 inch CCAR High Power Voice Coil
Impedance: 4 Ohm
RMS / Peak Watts: 75 / 150
Frequency Response: 250Hz - 22KHz
SPL @ 1w/1m: 103dB

FEATURES

6.5 inch Two Way Component Speaker System
6.5 inch Kevlar Reinforced Pulp Paper Cone
25 oz. Magnet
14k Gold Plated Speaker Terminals
1 inch Titanium Dome Tweeters w/Neo Magnet
Ferro-Fluid Enhanced Voice Coil Cooling
Impedance Matching 12dB Two Way Crossover Network
Includes Tweeter Flush, Surface Mounts
Complete with Grills and Mounting Hardware



Cadence Acoustics

6519 Highway 9 North • Howell, NJ 07731
800.477.2328 • 732.370.5400 • fax: 732.370.5553 • www.cadencesound.com

