

## ThinkCentre M700z Platform Specifications

Processor	Intel® Celeron®, Intel Pentium®, or 6th Generation Intel Core™ i3 / i5 / i7 Processor																			
	Processor	Cores / Threads	Frequency Base/Max(GHz)	Cache	Memory Types	Integrated Graphics														
	Celeron G3900T	2 / 2	2.6 G	2 MB	DDR4-2133	HD 510														
	Pentium G4400T	2 / 2	2.9 G	3 MB	DDR4-2133	HD 510														
	Core i3-6100T	2 / 4	3.2 G	3 MB	DDR4-2133	HD 530														
	Core i5-6400T	4 / 4	2.2 G / 2.8 G	6 MB	DDR4-2133	HD 530														
	Core i5-6500T	4 / 4	2.5 G / 3.1 G	6 MB	DDR4-2133	HD 530														
	Core i5-6600T	4 / 4	2.7 G / 3.5 G	6 MB	DDR4-2133	HD 530														
	Core i7-6700T	4 / 8	2.8 G / 3.6 G	8 MB	DDR4-2133	HD 530														
Memory	32GB max, DDR4 2133, two 260-pin SO-DIMM sockets, dual-channel capable																			
Disk	<p>Some: SATA 6.0Gb/s, 2.5" Wide, 5400 rpm or 7200 rpm</p> <p>Some: Solid State Hybrid Drive (SSHD) / with 8GB MLC NAND flash memory, SATA 6.0Gb/s, 2.5" Wide, 5400 rpm</p>																			
Optical	<p>Some: Solid State Drive (SSD) / SATA 6.0Gb/s, 2.5" Wide</p> <p>Some: DVD, SATA 1.5Gb/s, 9.5mm high</p> <p>Some: DVD burner, SATA 1.5Gb/s, 9.5mm high</p>																			
Media reader	Optional 9-in-1 media card reader																			
Graphics	<p><b>Intel HD Graphics 510/530</b> in processor, uses main memory, DirectX® 12, external monitor support via DisplayPort™;</p> <p><i>Max resolution: 4096x2304 (DP)@60Hz</i></p>																			
Display	20" (508mm) <b>HD+ (1600x900) TFT color</b> , wide viewing angle 178° (Horizontal), LED backlight, 250 nits, 16:9 aspect ratio, 1000:1 contrast ratio, anti-glare																			
Light sensor	None																			
Multi-touch Camera	None																			
Controls	Optional 1.0-megapixel camera, fixed focus, supports 720p, with digital microphone, LED indicator, physical switch on/off																			
Chipset	<b>Intel H110 Chipset</b>																			
Rear ports	Four USB 2.0, ethernet (RJ-45), DisplayPort, optional serial (9-pin),																			
Side ports	Two USB 3.0 (one is Always On and fast charge), optional card reader, one headphone / microphone combo jack (3.5mm)																			
M.2 card slot	One M.2 Card slot (for WLAN)																			
Audio support	High Definition (HD) Audio, Realtek ALC233 / two internal stereo speakers (2W x 2), Dolby® Audio™ certified																			
WLAN <sup>13</sup>	<p>Some: 11ac wireless, M.2 Card, Qualcomm Atheros QCA9377 (dual band), Wi-Fi + Bluetooth 4.1 combo adapter, 1x1</p> <p>Some: 11ac wireless, M.2 Card, Qualcomm Atheros QCA6174 (dual band), Wi-Fi + Bluetooth 4.1 combo adapter, 2x2</p> <p>Some: 11ac wireless, M.2 Card, Intel Dual Band Wireless-AC 3165, Wi-Fi + Bluetooth 4.0 combo adapter, 1x1</p> <p>Some: 11ac wireless, M.2 Card, Intel Dual Band Wireless-AC 8260, Wi-Fi + Bluetooth 4.1 combo adapter, 2x2</p>																			
Bluetooth™ Ethernet	<p>Some: Bluetooth 4.0 or 4.1 wireless, integrated in Wi-Fi + Bluetooth combo adapter</p> <p>Gigabit ethernet, Realtek RTL8111G, Wake on LAN®</p>																			
Manageability Security chip	None																			
Security features	<ul style="list-style-type: none"> <li>Security slot (in rear for attachment of optional Kensington® MicroSaver® cable; Kensington lock also locks chassis)</li> <li>Smart USB protection, allows keyboard/ mouse only, blocks all storage devices</li> <li>Power-on, admin, hard disk password</li> <li>Boot sequence control</li> <li>Boot without keyboard and mouse</li> <li>Individual USB port disablement</li> <li>Optional Chassis intrusion switch</li> </ul>																			
Keyboard	Some: Preferred Pro USB Keyboard (USB connector), Lenovo logo																			
	Some: Lenovo Slim USB Keyboard (USB connector), black																			
	Some: Ultraslim Plus Wireless Keyboard (2.4GHz via USB receiver), black																			
	Some: Enhanced Optical USB Mouse, black, Lenovo logo																			
Mouse	Some: Ultraslim Plus Wireless Mouse (2.4GHz via USB receiver), black																			
	<ul style="list-style-type: none"> <li>Business black color</li> <li>Toolless stand</li> <li>Support VESA mount (100mm)</li> </ul>																			
	<table border="1"> <thead> <tr> <th></th><th>Dimensions (WxDxH)</th><th>Max weight (lb / kg)</th><th>Adjustments</th></tr> </thead> <tbody> <tr> <td>Without stand:</td><td>19.8 X 1.5 X 13.5 (inch); 503 X 38 X 344 (mm)</td><td>10.2 / 4.62</td><td>N/A</td></tr> <tr> <td>With Basic Monitor stand:</td><td>19.8 X 9.6 X 16.2 (inch); 503 X 245 X 412 (mm)</td><td>14.6 / 6.6</td><td>Tilt: 45° back, -5° forward</td></tr> <tr> <td>With Full Function Monitor stand:</td><td>19.8 X 9.6 X 15.7 (inch); 503 X 245 X 400 (mm)</td><td>14.9 / 6.77</td><td>Tilt: 45° back, -5° forward; Lift: 110mm; Swivel: +/-45°</td></tr> </tbody> </table>						Dimensions (WxDxH)	Max weight (lb / kg)	Adjustments	Without stand:	19.8 X 1.5 X 13.5 (inch); 503 X 38 X 344 (mm)	10.2 / 4.62	N/A	With Basic Monitor stand:	19.8 X 9.6 X 16.2 (inch); 503 X 245 X 412 (mm)	14.6 / 6.6	Tilt: 45° back, -5° forward	With Full Function Monitor stand:	19.8 X 9.6 X 15.7 (inch); 503 X 245 X 400 (mm)	14.9 / 6.77
	Dimensions (WxDxH)	Max weight (lb / kg)	Adjustments																	
Without stand:	19.8 X 1.5 X 13.5 (inch); 503 X 38 X 344 (mm)	10.2 / 4.62	N/A																	
With Basic Monitor stand:	19.8 X 9.6 X 16.2 (inch); 503 X 245 X 412 (mm)	14.6 / 6.6	Tilt: 45° back, -5° forward																	
With Full Function Monitor stand:	19.8 X 9.6 X 15.7 (inch); 503 X 245 X 400 (mm)	14.9 / 6.77	Tilt: 45° back, -5° forward; Lift: 110mm; Swivel: +/-45°																	
Power supply 120 watts adapter, autosensing, 89% PSU																				
Limited warranty <sup>3</sup>	Some: 1-year or 3-year, depot repair service																			
	Some: 1-year or 3-year, limited onsite service																			
	Some: 3-years, limited onsite service, OID (Onsite International Delivery) / For Lenovo service upgrade options, please go to S-TC sheet																			
Preload	<b>Preloaded operating system</b>																			
	Some: Windows® 7 Professional 64 preinstalled through downgrade rights in Windows 10 Pro 64-bit																			
	Some: Windows 7 Professional 64																			
	Some: Windows 10 Pro 64-bit																			
Environment	Some: Windows 10 Home 64-bit																			
	<b>Preloaded applications (only some listed)</b>																			
	<ul style="list-style-type: none"> <li>Desktop Power Manager</li> <li>Lenovo Solution Center</li> <li>Lenovo REACHit</li> <li>Lenovo SHAREit</li> <li>Lenovo Bluetooth Lock (for models with Wi-Fi/BT card)</li> <li>McAfee® LiveSafe™ (30-day trial)</li> <li>Microsoft Office preloaded; purchase a product key to activate</li> <li>PowerDVD Create (DVD±RW)</li> <li>Lenovo ThinkVantage Tools</li> <li>Only for Window 10</li> <li>Lenovo Companion</li> <li>Cyberlink PowerDVD (DVD, DVD±RW)</li> <li>Lenovo QuickOptimizer</li> <li>Only for Window 7</li> <li>Rescue and Recovery</li> <li>Password Manager</li> <li>ThinkVantage System Update</li> <li>Lenovo Message Center Plus</li> <li>Adobe® Reader®</li> </ul>																			
MIL-SPEC test	EPEAT™ Gold rating; ENERGY STAR® 6.1; TCO Certified; ErP Lot 3; GREENGUARD® certified; RoHS-compliant																			
	MIL-STD-810G military certification (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock)																			
Accessories	For compatible accessories, please go to TC-AQP sheet																			

<b>Model</b>		<b>10EY0006US</b>
Product		ThinkCentre M700z
Region		US
Machine Type		10EY
TopSeller		TopSeller
Processor		Core i3-6100T (2C, 3.2GHz, 3MB)
vPro		No
Graphics		Integrated Intel HD Graphics 530
Monitor Cable		None
Memory		8GBx1
Display		20.0" HD+ (1600x900) WVA Anti-glare
Multi-touch		None
Storage		256GB SSD
Optical		DVD±RW
Media Reader		9-in-1
WLAN + Bluetooth		Intel 3165 ac, 1x1 + BT4.0
Optional Rear Ports		None
Camera		720p
Chassis Intrusion Switch		None
Keyboard / Mouse		USB / USB
Stand		Monitor Stand
Power Supply		120W 89% Adapter
Operating System		Windows 10 DG Windows 7 Pro 64
Warranty		3-year, Onsite
Global		No
Ann Date (mm/yy)		12/15



