

# JTouch

## Interactive Displays



Touchscreen displays to captivate and collaborate with audiences of all types

# The JTouch Family

**InFocus**  
Collaboration That Works

Part#s: INF4030p, INF4032p, INF5701, INF6501wp, INF6501wAGp, INF6501cp, INF6501cAGp, INF7001ap, INF8002

K-12 Only Part#s: INF4030, INF4032, INF6501w, INF6501wAG, INF6501c, INF6501cAG, INF7001a

Enrich and engage audiences in huddle spaces, classrooms, boardrooms, and beyond with the JTouch family of bright, colorful LCD touchscreen displays.

Available with a digital whiteboard or LightCast Technology for wireless casting and web browsing, JTouch provides amazing versatility and convenience, so you can collaborate at a moment's notice.

## Brightness and Clarity

JTouch helps you get your message across and connect with your audience with incredible brightness, color, and clarity. Your images, text, and video will be seen from anywhere in the room, even in large spaces with high ambient light.

## Engage Your Audience with Touch


Whether you're in a classroom, a boardroom, or at a trade show, the interactivity of JTouch engages audiences and encourages participation. JTouch gets students involved, attracts customers, and provides a great medium for testing and presenting touch-enabled applications.

## Easy to Connect

JTouch provides multiple ways to display your content, including HDMI, VGA, and wireless via Lightcast Technology, available in select JTouch models. To enable touch, simply connect the JTouch to your computer via USB.



Choose from a variety of InFocus mobile carts so that you can move your JTouch from room to room- wherever it's needed most.



- 1080p display with accurate and responsive multi-touch
- Incredibly sharp 4K resolution now available on 80-inch model
- Interactive, bright, crisp content in any light
- Quickly connect and display your notebook via HDMI, VGA, and more
- Easily share your mobile device's screen on LightCast-enabled JTouch displays
- Built-in whiteboard and web browser (varies by model)
- Anti-glare models available

## Bring Your Display to Life with 4K

The 80-inch JTouch now features 4K resolution for an incredibly sharp, vivid picture. Boost the impact of your content and make every meeting or presentation more engaging, informative, and memorable with 4K.

- More pixels mean more detail and depth for amazingly life-like images
- Enhanced color rendering
- Presenters benefit from crisp, clear images up close
- Audiences enjoy vibrant, detailed images, even from the back of a conference room

## Draw or Write on a JTouch Whiteboard

Toss aside your stained dry erase board, and turn your display into a stand-alone, full-featured interactive whiteboard. The JTouch Whiteboard is available on all 40-inch and 65-inch models.

- Capture and save whiteboard notes electronically
- Comes with a complete collection of digital pens, highlighters, shapes, and lines in a spectrum of colors

## LightCast Technology

LightCast Technology invigorates your JTouch with wireless content sharing and collaboration tools, making meetings or lessons of all types more engaging and efficient.

Mirror the screen of your wireless device on the JTouch display in seconds—it's easy and fast for users inside your organization, as well as guests. Or, browse the web and access cloud-based content. The JTouch with LightCast is a powerful, all-in-one tool for collaboration and creativity.

### Available in:

- INF4032/INF4032p
- INF6501c/INF6501cp
- INF6501cAG/INF6501cAGp

### Cast Your Screen

Don't huddle around a tiny laptop or tablet with your team. Wirelessly cast your device's screen and share your content in comfort.

- Works with Android, Windows, Apple, and Chrome devices\*
- Cast using your device's native protocol - Miracast for Android or Windows, or AirPlay (Mirroring mode) for Apple\*
- Use InFocus LightCast Sender to cast using Chrome extension (works on Apple, Windows, or Chrome OS)

### Browse the Web

Access the world of online content and tools with LightCast's built-in web browser.

- Connect the JTouch to your network via WiFi or LAN
- Easily access cloud content using built-in bookmark settings
- Quickly access file sharing platforms, such as DropBox or Google Docs
- Email information directly from the whiteboard

## Capture Ideas As They Occur with DigiEasel

At 40-inches, DigiEasel is the most versatile and portable member of the JTouch family—ensuring that you capture the next big idea, whenever or wherever it strikes.

Available as a stand-alone touchscreen and whiteboard (INF4030), DigiEasel allows you to draw, write, or capture notes on a vivid touch display in portrait or landscape mode.

Upgrade to DigiEasel with LightCast (INF4032/INF4032p) to add wireless content sharing and web browsing to your 40-inch display—all at a great value.



JTouch Whiteboard with LightCast, model INF6501c/INF6501cp



JTouch Whiteboard with LightCast, model INF6501c/INF6501cp



DigiEasel, model INF4032/INF4032p

\*Check with your manufacturer for Miracast or AirPlay compatibility with the specific version of your device's OS.

# Specifications\*

	INF4030	INF4032	INF5701	INF6501w	INF6501c	INF7001a	INF8002		
Display	INF4030p	INF4032p		INF6501wp	INF6501cp	INF6501cAG			
Size	40" diagonal		57" diagonal	65" diagonal	70" diagonal	80" diagonal			
Resolution	Full HD 1920 x 1080			4K 3840 x 2160					
Anti-Glare Option Available	No		Yes - INF6501wAG/INF6501wAGp and INF6501cAG/INF6501cAGp		No	Yes, plus Gorilla Glass			
Whiteboard	Yes		No	Yes		No			
Wireless Display (Casting)	No	Yes	No	No	Yes	No			
Browser	No	Yes	No	No	Yes	No			
Mounting Orientation	Portrait or Landscape		Landscape						
Technology	LED Edge-Lit LCD								
Pixel Pitch	0.15 mm horizontal, 0.45 mm vertical	0.67 mm	0.63 mm			0.46 mm			
Response Time	8.5ms	9.5 ms	6.5 ms			6 ms			
Contrast Ratio	5000:1				4000:1				
Brightness	300 cd/m <sup>2</sup>	370 cd/m <sup>2</sup>	400 cd/m <sup>2</sup>	350 cd/m <sup>2</sup>	400 cd/m <sup>2</sup>				
Input Connections	HDMI x4, VGA, component, composite, 3.5mm audio in, RCA stereo audio in, RS232, USB-B for touch screen control USB-A x2 on panel, USB-A x2 on bottom for embedded software	HDMI x2, VGA, RS232, RCA stereo audio in, 3.5 mm stereo audio in, USB-B for touch screen control	HDMI x4, VGA, component, composite, USB hub (USB 3.0 x4), 3.5mm audio in, RCA stereo audio in, RS232, USB-B for touch screen control	HDMI x2, VGA, RS232, RCA stereo audio in, 3.5 mm stereo audio in, USB-B for touch screen control	HDMI x2, VGA, RS232, RCA stereo audio in, 3.5 mm stereo audio in, USB-B for touch screen control	Displayport 1.2, HDMI 2.0 x2, HDMI 1.4, VGA, component, 3.5mm audio in, RCA stereo audio in, RS232			
Output Connections	RCA audio out		RCA audio out, 3.5 mm stereo audio out	RCA audio out		RCA audio out, 3.5 mm stereo audio out			
Touch Screen	Edge to edge capacitive glass								
Touch Points	10	5	6	IR multi-touch system					
Speakers (Integrated)	10W x2	7W x2	10W x2	7W x2					
Mount	VESA standard 200 x 200 mm M6 screws	VESA standard 400 x 400 mm M6 screws				VESA 400 x 600 M6 screws			
Accessories Included	Power cord, VGA & USB cable, tray, stylus, and documentation	Power cord, VGA cable, USB cable, remote control, and documentation							
Product Weight	44 lbs / 20 kg	124 lbs / 56 kg	110.2 lbs / 50.1 kg	154 lbs / 70 kg	154 lbs / 70 kg				
Product Dimensions (H x W x D)	21.8 x 38.3 x 4.5 in. 533 x 974 x 113 mm	34.9 x 56.7 x 3.7 in. 856 x 1388 x 91 mm	36.4 x 60.2 x 3.3 in. 925 x 1529 x 84 mm	39 x 65.7 x 4 in. 991 x 1669 x 102 mm	46.3 x 74.8 x 4 in. 1176 x 1900 x 101 mm				
Shipping Weight	56.4 lbs / 25.6 kg	153 lbs / 69 kg	150 lbs / 68.2 kg	170 lbs / 77.1 kg	201 lbs / 91.2 kg				
Shipping Dims (H x W x D)	28.1 x 41.9 x 7.9 in. 715 x 1063 x 200 mm	42.5 x 63.5 x 10 in. 1080 x 1613 x 254 mm	40 x 68 x 9.5 in. 1016 x 1727 x 241 mm	49 x 73 x 10.5 in. 1245 x 1854 x 267 mm	53.5 in. x 83.5 x 10.5 in. 1359 x 2121 x 267 mm				

## LightCast Technology (available in INF6501c/INF6501cp, INF6501cAG/INF6501cAGp, and INF4032/INF4032p)

Wireless Display Protocol	Miracast, AirPlay, and InFocus LightCast Sender
Casting Device Compatibility	Chrome and specific versions of Android, Windows, and Apple operating systems; check with your manufacturer for details.
Connectivity	802.11 b/g/n (2 dipole antenna), RJ-45 (10Base-TX), USB Type-A
Wireless Range	Up to 300 ft/91 m
Data Rate	Wireless: Up to 150 Mbps LAN: 10/100
Wi-Fi Compliant	802.11 b/g/n with MIMO
Security	IEEE Standard 64/128 bit WEP/WPA/WPA2-PSK/WPA-Enterprise

## Additional Display Specifications

**Refresh Rate:** 120 Hz

**Viewing Angle:** 176°

**Computer Touch Compatibility (via USB):** PC, Mac, Chromebook

**Power:** AC 100 to 240V, 50/60 Hz

**Operating Conditions:** 32° to 104° F at 0 to 10K feet / 0° to 40° at 0 to 3,048 m

**Noise:** <40dBA at 77° F / 25° C

**Warranty:** INF4030: 1 Year INF6501c: 2 Year

INF4032: 1 Year

INF5701: 2 Year

INF6501w: 2 Year

INF6501wAG: 2 Year

INF6501cAG: 2 Year

INF7001a: 2 Year

INF8002: 1 Year

## Accessories

Wall Mount for 50-70 Inch Display (INF-WALLMNT2)

Mobile Carts for 57-70 Inch Display (INF-MOB CART, INF-MOB CART PRO-B, INF-MOB CART PRO-S)

Wall Mount for 80 Inch Display (INF-WALLMNT3)

Mobile Cart for 80 Inch Display (INF-MCART-PL)

Deluxe Mobile Cart with PTZ Mount

and Accessory Shelf (INA-MCARTDX)

Lift Assist Mount for 57-70 Inch Display (INA-MNTBB70)

Lift Assist Mount for 80 Inch Display (INA-MNTBB95)

Floor Support for Lift Assist Wall Mount (INA-SUPPORTBB)

Mobile Cart for List Assist Mount (INA-CARTBB)

VESA Interface Bracket (INA-VESABB)

DigiEasel Floor Stand (INA-STNDSM)

LightCast Key (INA-LCKEY1, INA-LCKEY2,

INA-LCKEY3 - selection is location dependent)

Touchscreen Stylus (INA-STYLUS)

Extended Warranties

40-Inch (EPWHW40JT1, EPWHW40JT2)

57-Inch (EPWHW57JT1)

65-Inch (EPWHW65JT1)

70-Inch (EPWHW70JT1)

80-Inch (EPWHW80JT1, EPWHW80JT2)

\* Product specifications, terms, and offerings are subject to change at any time without notice.