

4-Port HDMI Switch with Remote Control - 4K 60 Hz, UHD, 4:4:4, HDR, 3D

MODEL NUMBER: **B119-004-UHD**



Connects 4 HDMI audio/video sources to one 4K HDMI TV, monitor or projector, and allows you to switch between them.

Features

4-Port HDMI Switch with Remote Connects 4 Sources to One 4K HDMI Display An excellent addition to your home theater, the B119-004-UHD allows you to connect four separate HDMI audio/video sources to your 4K television, projector or monitor's HDMI input and switch between them. For instance, connect a cable box, Blu-ray player, Xbox and audio receiver to your 4K HDTV, and use the manual pushbutton or included remote control to switch manually from one input to another.

Transmits Crystal-Clear 4K Video with HDR and 4:4:4 Color This four-port HDMI switch supports Ultra HD 4K video resolutions at 60 Hz, as specified in HDMI 2.0, as well as 48-bit True Color and HDR video, providing a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This adapter supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor. DTS-HD, Dolby TrueHD and 7.1-channel surround sound ensure your ears receive the same treat as your eyes.

Ready to Use Right from the Package, So You Can Plug and Play Immediately The compact metal switch requires no extra software to download and install. Connect your devices to the HDMI ports with user-supplied HDMI cables (such as Tripp Lite's P569-Series), and plug the included external power supply into an AC power source. A red LED indicates the unit is receiving power, and green LEDs indicate connected HDMI inputs. When the currently used source is powered off, the unit automatically switches to the next powered-on source.

Highlights

- Switch between 4 source devices with included remote for ultimate convenience
- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for crystal-clear video
- Supports High Dynamic Range (HDR) for richer contrast and expanded color accuracy
- Delivers full, rich DTS-HD, Dolby TrueHD and 7.1-channel surround sound audio
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Switch between your cable box, Blu-ray player, video game console, Roku or other HDMI sources in your home theater
- Connect multiple desktop computers and laptops to one monitor to save desk space
- Monitor the premises with as many as 4 security cameras connected to a single display
- Create up to 4 different digital signage messages to appear at various times on a 4K HDMI display

System Requirements

- Up to 4 source devices with HDMI output
- Display device with HDMI input

Package Includes

- B119-004-UHD 4-Port HDMI

Switch

- Remote control
- External power supply (Input: 100–240V, 50/60 Hz, 0.3A; Output: 5V 1A)
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332191342
Technology	HDMI; IR
VIDEO	
Max Supported Video Resolution	4K @ 60Hz 4:4:4
Max Supported Color Depth	48-bit Deep Color
HDR Support	Yes
3D Video Supported	Yes
AUDIO	
Audio Specification	DTS-HD, Dolby TrueHD and 7.1 Channel Surround Sound
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 1-15P North America
Bus Powered	No
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.35A
External Power Supply Output Specs (V / A)	5V / 2A
External Power Supply Cord Length (ft.)	4
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	CE; ETL; UL
USER INTERFACE, ALERTS & CONTROLS	

LED Indicators	Red (Power), Green (1, 2, 3, 4)
PHYSICAL	
Color	Black
Material of Construction	Steel
Rackmountable	No
Shipping Dimensions (hwd / cm)	7.62 x 13.21 x 18.03
Shipping Dimensions (hwd / in.)	3.00 x 5.20 x 7.10
Shipping Weight (kg)	0.45
Shipping Weight (lbs.)	1.00
Unit Dimensions (hwd / in.)	0.8 x 4.8 x 2
Unit Packaging Type	Box
Unit Weight (kg)	0.15
Unit Weight (lbs.)	0.33
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 °F (0 to 40 °C)
Storage Temperature Range	14 to 176 °F (-10 to 80 °C)
BTUs	6 BTU/Hr
Power Consumption (Watts)	1.75
Operating Humidity Range	10% to 85 % RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
COMMUNICATIONS	
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
CONNECTIONS	
Ports	4
Side A - Connector 1	(4) HDMI (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
FEATURES & SPECIFICATIONS	
Port Selection	Pushbutton; Remote Selector
HDCP Specification	2.2
Driver Required	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

STANDARDS & COMPLIANCE

Certifications	CE, FCC, RoHS, REACH
----------------	----------------------

WARRANTY

Product Warranty Period (Worldwide)	3-year limited warranty
-------------------------------------	-------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>