

## Mini DisplayPort 1.2 to VGA Adapter Cable, Active, M/M, 3 ft. (0.91 m)

### MODEL NUMBER: P586-003-VGA-V2

Converts a Mini DisplayPort v1.2 video signal for display on a VGA monitor, projector or television.

#### Features

##### Send High-Quality Mini DisplayPort v1.2 Video Signals to a VGA Display

- Connects Mini DisplayPort (or Thunderbolt) computer to VGA-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Low-profile VGA connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
- Mini DisplayPort and HD15 male connectors
- No separate adapter required

##### Vibrant, Superior Video Quality

- Supports computer video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Converts Single-Mode and Dual-Mode (DP++) Mini DisplayPort output
- Perfect for use with graphics cards, such as AMD Eyefinity, that don't output DP++ signals

##### Superior Materials for Superior Performance

- Double shielding with foil and braid for maximum EMI/RFI protection
- Nickel-plated connectors with gold-plated contacts for excellent conductivity
- Integral strain relief for long life

## Specifications

| OVERVIEW                       |                       |
|--------------------------------|-----------------------|
| UPC Code                       | 037332191847          |
| Technology                     | VGA/SVGA; DisplayPort |
| VIDEO                          |                       |
| Max Supported Video Resolution | 1920 x 1200 (1080p)   |
| PHYSICAL                       |                       |
| Color                          | Black                 |
| Cable Outer Diameter (OD)      | 5.0 +/- 15mm          |
| Cable Jacket Rating            | VW-1                  |
| Wire Gauge (AWG)               | 32                    |

#### Highlights

- Active adapter cable for use with any Mini Displayport (or Thunderbolt) port
- Low-profile VGA connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
- Supports computer video resolution up to 1920 x 1200
- Supports HD video resolution up to 1920 x 1080 (1080p)
- No separate adapter required
- Nickel-plated connectors with gold-plated contacts

#### Package Includes

- P586-003-VGA-V2 Mini DisplayPort 1.2 to VGA Active Adapter Cable, 3 ft.

|   |                          |
|---|--------------------------|
| Cable Length (ft.)                      | 3                        |
| Cable Length (m)                        | 0.9                      |
| Cable Length (in.)                      | 36                       |
| Material of Construction                | ABS, PVC                 |
| Shipping Dimensions (hwd / cm)          | 17.78 x 22.86 x 1.27     |
| Shipping Dimensions (hwd / in.)         | 7.00 x 9.00 x 0.50       |
| Shipping Weight (kg)                    | 0.07                     |
| Shipping Weight (lbs.)                  | 0.15                     |
| <b>ENVIRONMENTAL</b>                    |                          |
| Operating Temperature Range             | 32 to 104 F (0 to 40 C)  |
| Storage Temperature Range               | 5 to 122 F (-15 to 50 C) |
| Operating Humidity Range                | 0 to 85%, Non-Condensing |
| Storage Humidity Range                  | 0 to 85%, Non-Condensing |
| <b>CONNECTIONS</b>                      |                          |
| Side A - Connector 1                    | MINI DISPLAYPORT (MALE)  |
| Side B - Connector 1                    | HD15 (MALE)              |
| Connector Plating                       | Nickel                   |
| Contact Plating                         | Gold                     |
| <b>FEATURES &amp; SPECIFICATIONS</b>    |                          |
| Displayport Specification               | 1.2                      |
| <b>STANDARDS &amp; COMPLIANCE</b>       |                          |
| Certifications                          | CE, FCC, RoHS, REACH     |
| <b>WARRANTY</b>                         |                          |
| Product Warranty Period (Worldwide)     | 3-year limited warranty  |
| Product Warranty Period (U.S. & Canada) | 3-year limited warranty  |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>