



FCS-4202 Version: 1

Zoom Dome Network camera, 2-Megapixel, 802.3af PoE, Day & Night, IR LEDs, 3x Optical Zoom, WDR, Outdoor

Key Features

- 2-Megapixel (1920 x 1080) high-definition resolution
 - Compression: H.264/MPEG-4/MJPEG
 - Built-in infrared LEDs for night viewing up to 20m
 - Features WDR (Wide Dynamic Range) to enhance visibility under extremely bright or dark environments
 - Free video surveillance and CMS (Central Management System) software with 64-channel license
 - Removable IR-cut filter for day and night surveillance
 - Supports 2 video streams simultaneously
 - Supports 3x optical zoom
 - Vandal-proof IK08-rated housing
-

Specifications

System Specifications

Standards & Protocols:

IEEE 802.3 10-BASE-T, Ethernet

IEEE 802.3u 100-BASE-TX, Fast Ethernet

TCP/IP, HTTP, SMTP, FTP, DDNS, UPnP, NTP, PPPoE, DNS, DHCP, RTSP, Samba

Image Sensor:

2-Megapixel 1/2.7" Progressive Scan CMOS

Connectors and Cabling:

1 x RJ-45 10/100 Mbps PoE port

1 x DC Power Jack

1 x Audio in

1 x Audio Out

1 x DI/DO

Modularity:

1 x MicroSD/SDHC card slot

Button:

Reset Button

**Indicator:**

Power, Link

Lens:

3X optical zoom lens, auto iris, auto focus

f = 3mm ~ 9mm, F1.8

Fov(D), 136° ~ 39°

IR Cut Filter:

Removable infrared-cut filter for day & night function

IR LED:

6 IR LEDs for illumination up to 20m

Shutter Time:

Indoor : 1/30 ~ 1/120 sec

Outdoor : 1/30 ~ 1/1,000,000 sec

Angle of View:

62°

Pan/Tilt/Zoom:

3X optical zoom , 4X digital zoom

Video Compression:

H.264 / MPEG4 / MJPEG

Resolution:

2M (1920x1080)

Video Format:

MPEG4

Audio Compression:

AMR / AAC /AEC

Power:

Power Consumption: 8W

Power Input: DC12V 1.5A / 802.3af PoE

Features

General:

Backup: MicroSDHC card slot for local storage

IPv6: IPv4/IPv6 network operation DNS: Easy Internet monitoring

Security:

Alarm and Notification: Alarm: Motion Detection; Notification: FTP, SMTP, Samba

Access Control: Multi-level user access with password protection

IP address filtering

HTTPS encrypted data transmission

Video:

Image Setting: - Adjustable image size, quality and bit rate

- Configurable brightness, sharpness, contrast, saturation, white balance and exposure

- AGC/AWB/AES

- Wide Dynamic Range (WDR)

- 3D Noise Reduction (3DNR)

- Flip & Mirror

- Time Stamp

Streaming: Up to 2 video streams

Audio:

2-way audio (line in/out)

Performance

Number of Clients:

16

Data Transfer Rate:

10/100Mbps

Storage Capacity:

SD/MicroSD memory card of up to 64GB

Frame Rate:

30 fps at 1920 x 1080; 30 fps at 1280 x 720; 30 fps at 640 x 480; 15 fps at 320 x 240

Minimum illumination:

Color: 1.0 lux at F2.0

Environment

Temperature (°C):

Operating: -5°C ~ 50°C

Humidity (Non-condensing):

Operating: 10% ~ 80%

Physical Specifications

Dimensions (W x D x H mm):

63 x 63 x 92 mm

Weight (g):

500 g

Enclosure:

IP66 Waterproof

Others

Approval and Compliance:

CE, RoHS, FCC, Onvif

Deployment:

Desktop/Ceiling Mount

Operation Systems:

Microsoft Windows 8/7/Vista/XP

Viewing Systems:

Browser: Internet Explorer 6.x or above, Firefox, Chrome, Safari


Cell phone: 3GPP player

Real Player: 10.5 or above

Quick Time 6.5 or above



Diagram



Order Information

FCS-4202

Package Contents

FCS-4202
Power Adapter
RJ-45 Female/Female Coupler
Quick Installation Guide
Resource CD (User Manual, Utility, 64-CH Monitoring Software)
Screw Kit

No liability or responsibility for any errors or omissions in the content.
Specifications are subject to change without notice.
All mentioned brand names are registered trademarks and property of their owners.
Copyright © Digital Data Communications GmbH, Germany. All Rights Reserved.