

HDMI over Cat5/Cat6 Active Extender, Box-Style Remote Repeater for Video and Audio, 1080p @ 60 Hz w/Intl. Power Supply

MODEL NUMBER: **B126-110-INT**



Description

The B126-110-INT HDMI over Cat5/Cat6 Active Remote Repeater works with Tripp Lite B126-Series transmitters and receivers to extend an HDMI signal to multiple projectors, monitors or televisions in a chain. It's ideal for digital signs, trade shows, presentations, classrooms, retail settings and other applications where the video source is located farther than conventional cables allow or that require multiple displays connected to one source.

The repeater uses HDMI cable (see Tripp Lite's P568-Series) to connect to the local monitor and Cat5e/6 cable to transmit to the receiver and/or other remote repeaters in the chain (for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series).

The B126-110-INT can extend a 1080i (60 Hz) signal up to 175 feet (53.3 m), a 1080p (60 Hz) signal up to 125 feet (38.1 m) and a 3D signal up to 100 feet (30.5 m). You can connect up to three B126-110-INT units in the chain for a total of four HDMI displays and full signal extension of 700 feet/213.4 meters (1080i), 500 feet/152.4 meters (1080p) or 400 feet/121.9 meters (3D).

In addition to high-definition video, the B126-110-INT delivers full, rich stereo and 7.1-channel surround sound (multi-channel or PCM) audio when used with a B126-Series transmitter. Built-in equalization control lets you fine-tune the image quality at each remote display. Supports 24-bit True Color (8 bits per channel) and HDCP compatibility. Mounts to a wall, rack or pole using the included hardware.

Features

Extends High-Definition Signals

- Extends a 1080i(60 Hz) signal up to 175 ft.(53.3 m), a 1080p(60 Hz) signal up to 125 ft.(38.1 m) and a 3D signal up to 100 ft.(30.5 m)
- Connect up to 3 remote repeaters to the chain for maximum signal range of 700 ft./213 m(1080i), 500 ft./152.4 m(1080p) and 400 ft./121.9 m(3D)
- Connects to next link in the chain with one Cat5e/6 cable(for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series)

Supports the Latest Video and Audio Resolutions

Highlights

- Extends 1080i (60 Hz) signal up to 175 ft. (53.3 m)
- Connect up to 3 units in a chain for maximum extension
- Supports high-definition video resolutions up to 1080p (60 Hz)
- Supports stereo and 7.1-channel surround sound audio
- Plug and play—no software or drivers to install

Package Includes

- B126-110-INT HDMI over Cat5/Cat6 Active Remote Repeater
- Screwdriver for adjusting equalization
- External power supply w/CEE 7/16 Schuko, BS1363 UK and AS2112 Australia plugs (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V, 2A)
- Mounting hardware
- Owner's manual

- Works with all operating systems and HDMI video sources
- Supports HD resolutions up to 1080p(60 Hz)
- Supports stereo and 7.1-channel surround sound(multi-channel or PCM) audio when paired with [B126-002](#) or [B126-004](#) transmitter unit
- Supports 24-bit True Color(8 bits per channel) and HDCP
- Built-in equalization control lets you adjust the image on the local monitor

Easy to Set Up and Use

- Plug-and-play engineering—no software or drivers to download and install
- Connects quickly to local monitor with HDMI cable, such as Tripp Lite's P568-Series
- Included mounting hardware lets you install the unit on a wall, rack or pole
- International power supply with CEE 7/16 Schuko, BS1363 UK and AS2112 Australia plugs

Specifications

OVERVIEW	
Cable Type	HDMI; UTP (Cat5, Cat5e, Cat6, Cat6a)
PHYSICAL	
Shipping Weight (lbs.)	1.50
Shipping Weight (kg)	0.68
Unit Dimensions (hwd / in.)	1.0" x 4.50" x 2.50"
Unit Dimensions (hwd / cm)	2.54 x 11.43 x 6.35
Included Mounting Accessories	Yes
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
CONNECTIONS	
Connector A	HARDWIRE
Connector B	HARDWIRE
Ports	1
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	1-year limited warranty
-------------------------------------	-------------------------

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>