

4-Port HDMI over Cat5/Cat6 Extender/Splitter, Box-Style Transmitter for Video/Audio, 1080p @ 60 Hz w/Intl. Power Supply

MODEL NUMBER: **B126-004-INT**



Description

The B126-004-INT 4-Port HDMI over Cat5/Cat6 Extender/Splitter works with Tripp Lite B126-Series remote receivers to split a single HDMI audio/video signal into five separate signals—one local and four remote. It's ideal for digital signs, trade shows, presentations, retail settings and other applications where the video source is located farther than conventional cables allow or that require multiple displays connected to one source.

The B126-004-INT uses HDMI cable(see Tripp Lite's P568-Series) to connect to the source and the local monitor and Cat5e/6 cable to transmit to the remote monitors(for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series).

When used with Tripp Lite's [B126-1A0](#) or [B126-1A0-WP-1](#) active remote receivers, the B126-004-INT can extend a 1080i(60 Hz) signal up to 200 feet(61 m), a 1080p signal(60 Hz) up to 150 feet(45.7 m) and a 3D signal up to 125 feet(38.1 m). With a [B126-1P0](#) or [B126-1P0-WP-1](#) passive remote receiver, it can extend a 1080i(60 Hz) signal up to 100 feet(30.5 m) and a 1080p(60 Hz) signal up to 50 feet(15.2 m).

By daisy-chaining up to three B126-004-INT units, one video source can transmit to as many as 13 monitors—one local and 12 remote. Add up to three [B126-110](#) remote repeaters to each channel to fully extend the signal range or add more displays.

Easy to set up with no software or drivers to install, the unit mounts to a wall, rack or pole using the included hardware.

Features

Extends High-Definition Signals

- Extends a 1080i(60 Hz) signal up to 175 ft.(53.3 m), a 1080p(60 Hz) signal up to 125 ft.(38.1 m) and a 3D signal up to 100 ft.(30.5 m) with each optional Tripp Lite [B126-110](#) remote repeater
- Extends a 1080i(60 Hz) signal up to 200 ft.(61 m), a 1080p(60 Hz) signal up to 150 ft.(45.7 m) and a 3D signal up to 125 ft.(38.1 m) with Tripp Lite [B126-1A0](#) or [B126-1A0-WP-1](#) active remote receiver
- Extends a 1080i(60 Hz) signal up to 100 ft.(30.5 m) and a 1080p(60 Hz) signal up to 50 ft.(15.2 m) with Tripp Lite [B126-1P0](#) or [B126-1P0-WP-1](#) passive

Highlights

- Perfect for digital signs, trade shows and classrooms
- Can daisy-chain up to 3 units to extend signal to 13 monitors
- Works with all operating systems and HDMI video sources
- Supports stereo and 7.1-channel surround sound audio
- Plug and play—no software or drivers to install

Package Includes

- B126-004-INT 4-Port HDMI over Cat5/Cat6 Extender/Splitter
- HDMI daisy-chain cable, 12 in. (30.5 cm)
- External power supply w/CEE 7/16 Schuko, BS1363 UK and AS2112 Australia plugs (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V, 2A)
- Mounting hardware
- Owner's manual

remote receiver

- Add up to 3 remote repeaters on each channel for maximum signal range
- Daisy-chain up to 3 units to extend the original signal to as many as 13 display monitors(1 local, 12 remote)
- Connects to next link in the chain with one Cat5e/6 cable(for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series)

Supports the Latest Video and Audio Resolutions

- Works with all operating systems and HDMI video sources
- Supports HD resolutions up to 1080p(60 Hz)
- Supports stereo and 7.1-channel surround sound(multi-channel or PCM) audio
- Supports 24-bit True Color(8 bits per channel) and HDCP

Easy to Set Up and Use

- Plug and play—no software or drivers to download and install
- Connects quickly to source and local monitor with HDMI cable, such as Tripp Lite's P568-Series
- LEDs indicate when the unit is receiving power and an HDMI signal from the source
- Included mounting hardware lets you install the unit on a wall, rack or pole
- Mount up to 3 units in 1U of rack space using a Tripp Lite [B132-004-RB](#) rack-mount bracket
- International power supply with CEE 7/16 Schuko, BS1363 UK and AS2112 Australia plugs

Specifications

OVERVIEW	
Cable Type	HDMI; UTP (Cat5, Cat5e, Cat6, Cat6a)
PHYSICAL	
Optional Mounting Accessory Notes	Up to three B126-004 local units can be mounted in 1U of rack space using a Tripp Lite B132-004-RB Extender/Splitter 19in rackmount bracket
Unit Dimensions (hwd / in.)	1.125 x 5 x 4
Unit Dimensions (hwd / cm)	2.86 x 12.7 x 10.16
Included Mounting Accessories	Yes
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
CONNECTIONS	
Connector A	(4) RJ45 (FEMALE)
Connector B	(2) HDMI (FEMALE)

Ports	4
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>