

Avision

A vision of your office

Avision | AD125 Sheetfed Scanner

Scan to
cloud servers



Compact & Reliable

600
DPI

A4

Duplex
scanning

Up to
50
pages

25 ppm
50 ipm
scanning speed

118" Long
page

Features:

- 9 pre-programmed "scan-to" destinations
- Professional bundled software applications include Avison Button Manager, Nuance PaperPort, AVScan X and Avison Capture Tool
- AD125 scans 25 ppm/ 50 ipm images per minute in duplex mode (200 dpi, color)
- AD125 scans 20 ppm/ 40 ipm images per minute in duplex mode (300 dpi, color)
- Compact ADF holds up to 50 pages
- Press and scan to cloud servers including Google Docs, Microsoft SharePoint, or FTP via Button Manager V2

A small and fast sheet-fed scanner ideal for front office document scanning

The Avison AD125 is a small, fast and color sheet-fed scanner designed for desktop use that scans double-sided documents at speeds up to 50 images per minute. With its high performance and small footprint, the Avison AD125 is an ideal choice for your front office document scanning needs.



Advanced imaging

Despite its compact size, the Avison AD125 is ready to scan full-color double-sided originals at a high speed of up to 25 ppm and 50 ipm in 200 dpi thanks to the advanced 50-sheet auto document feeder. Every AD125 model is equipped with a CCD sensor for high quality scans, and a 50-sheet capacity of the ADF for efficient batch scans.

Easy to scan with a push of a button

With Avison's newly developed software application-Button Manager V2, the scanner allows you to complete your scan with a push of the Scan button and send the scanned image to a specified destination including e-mail, printer, image editing software application, or even a cloud server such as Google Drive or Microsoft SharePoint.




What we have bundled

The Avison AD125 comes with TWAIN and ISIS drivers, and is bundled with a suite of powerful software applications that include Avison Button Manager V2, AVScan X, and Nuance PaperPort SE 14. With Button Manager V2, you can scan and send images to e-mail, printer, or other destinations with a simple press of the Scan button. The AVScan X and Nuance PaperPort are highly effective image processing and document management software that helps you streamline your task more efficiently.

Avision | AD125 Sheetfed Scanner

Avision's Button Manager V2

-Completes your scan with a single step



The Button Manager V2 main screen

Button Manager V2 makes it easy for you to scan and send your image to your favorite destinations with a press one button. Now the new version comes with an innovative feature to let you scan and automatically upload the scanned document to popular cloud repositories such as Google Docs, Microsoft SharePoint, or FTP. In addition, the iScan feature allows you to insert the scanned image or recognized text after optional OCR (Optical Character Recognition) process to your text editor such as Microsoft Word to get your job done easily and quickly.

AVScan X

-The Intelligent Document Management Tool



The AVScan X main screen

Document Imaging is the very first step of Document Management. However, poor quality images can cause serious problems to later indexing or storing processes. It may increase scanning labor costs and lowers the OCR accuracy. AVScan X ensures all documents are checked and polished at the time they are scanned such that the image quality is guaranteed before they are ready to use for other purposes.

AVScan X is an intelligent scanning and electronic filing solution. AVScan X possesses distinct features that convert and index scanned information into electronic documents for easy storage and fast retrieval.

Nuance PaperPort SE14

- The Professional Choice to Organize and Share Your Documents



The PaperPort SE14 main screen

PaperPort SE 14 is Nuance's most popular scanning and document management solution, carefully designed specifically for home office use. Part traditional file cabinet, part digital-document desktop, PaperPort SE 14 is the fastest and easiest way to scan, share, search and organize your documents. Additionally, PaperPort SE 14 now delivers anytime-anywhere access to your most important files however it's convenient for you – using a PC, Mac, iPhone, iPad, or Android device.



Avision
Button Manager V2

AVScan X



Avision AD125 Product Specifications

Paper Feeding:	ADF 50-page capacity
Scanning Technology:	Color Charged-Coupled Device (CCD)
Document Size:	Max. 216 x 356 mm (8.5 x 14 in.) Min. 50 x 63.5 mm (1.9 x 2.5 in.)
Scanning Speed:	25 PPM / 50 IPM (Color, A4, 200 dpi) 20 PPM / 40 IPM (Color, A4, 300 dpi)
Paper Thickness:	34~127 g/m ² (9~34 lb.)
Optical Resolution:	600 dpi
Output Resolution:	75, 100, 150, 200, 300, 400 and 600 dpi
Output Formats:	B/W, greyscale, 24-bit color
Bundled Software:	Avision Button Manager V2, Avision AVScan X, PaperPort SE 14
Interface/Drivers	USB 2.0 / TWAIN , ISIS
Power Supply:	Input: 100-240 VAC, 50/60 Hz Output: 24V, 2.0A
Power Consumption:	Operation: <14.3 W Ready: <9 W Sleep: <2.2 W Off: <0.34 W
Environmental Factors:	Operating temperature: 10°C to 35°C (50°F to 95°F) Operating humidity: 10% to 85%
Acoustical Noise:	Standby: <45 dB Operating: <55 dB
Dimensions (W x D x H):	Max. 308 x 446 x 329 mm , 12.1 x 17.6 x 13 in. Min . 308 x 172 x 271 mm , 12.1 x 6.8 x 10.7 in.
Weight:	2.6 kg (5.7 lb.)
Recommended Daily Scanning Volume:	4,000 sheets

Specifications subject to change without notice.

System Requirements

CPU:	Intel® Core 2 Duo or higher
Memory:	1GB (32bit Windows) 2GB (64bit Windows)
DVD-ROM:	DVD ROM Drive
USB:	USB2.0 Port (USB1.1 supported)
Windows® Operating System:	Windows® XP SP3, Vista, 7, 8.x, 10 (32 & 64 bit)

Contents

AD125 Scanner
Power Supply
Quick Guide
USB 2.0 Cable
CD-ROM includes:
-Scanner Driver (TWAIN/ ISIS Driver)
-Avision Button Manager V2
-Avision AVScan X
-Nuance PaperPort SE 14



Avision
www.avision.com