

Avision

MiCube Mobile Scanner

Personal Document Scanner




Built-in 128MB Memory	Battery Powered	Speed 8ppm 300dpi / Color	Support 32GB SD Card	PDF JPG Color / B&W
Include MicroSD Card	Max. 600 dpi	Support 8.5"X14" Paper Size	Long page 36" 300 dpi	Include OCR Software





Avision MiCube Product Specifications

Technology:	CIS (contact image sensor)
Memory card:	Support SD card
Built-in memory:	128MB
Interface:	USB 2.0 / 1.1
Scan resolution:	600/300 dpi
File format:	JPG : Color/BW PDF : Color/BW
Battery:	Li-ion battery (AP-120, 3.7V, 1700mA)
Battery life:	200 pages A4
Auto power off:	3 Minutes
Max. scan area:	8.5" X 14" (216 x 356 mm)
Long Page Mode:	36 inch (300 dpi)
ADF capacity:	8 pages
Speed (A4):	8PPM
Dimension:	295 mm x 81 mm x 41 mm (11.6 in x 3.2 in x 1.6 in)
Weight:	800 g (1.8 lbs)



control panel indication

1	Message LCM	Show image message
2	Ready LED	Show ready status or scan in progress
3	Scan	Press "Scan" to start a scan.
4	Color/BW	Press "Color/BW" to switch to Color or BW mode
5	JPEG/PDF	Press "JPEG/PDF" to switch to JPEG or PDF file
6	300/600 dpi	Press "300/600 dpi" to switch to 300 or 600 dpi.

what we have bundled


PaperPort SE14

- The Professional Choice to Organize and Share Your Documents



PaperPort SE 14 is Nuance's most popular scanning and document management solution, carefully designed specifically for home office use. Part traditional file cabinet, part digital-document desktop, PaperPort SE 14 is the fastest and easiest way to scan, share, search, and organize your documents. Additionally, PaperPort SE 14 now delivers anytime-anywhere access to your most important files however it's convenient for you – using a PC, Mac, iPhone, iPad, or Android device.

Slim and easy-to-use



Avision
www.avision.com

Avision Inc.

No. 20, Creation Rd. I
Hsinchu Science Park 30077, Taiwan,
R.O.C.

Tel: 886-3-5782388
Fax: 886-3-5777017
E-mail: sales@avision.com.tw