

LG MONITORS

28LH4530-P

28" LED HD TV

28"

* Class size: See below for details.

LED

Smart Energy Saving

Triple XD Engine

Flicker Safe



PANEL	
Screen Size	27.5"
Resolution	1366x768
Panel Type	ADS
Color Gamut (CIE1931)	68%
Color Bit	8bit (6bit+FRC)
Color Depth (Number of Colors)	16.7M
Pixel pitch (mm)	0.44475 x 0.44925
Brightness (Typ.)	200 cd/m2
Contrast Ratio (Original)	1000:1
Contrast Ratio (DFC)	5M:1
Response Time_Typ. (GTG)	8ms
Viewing Angle(CR≥10)	R/L 178 (Typ.), U/D178 (Typ.)
Surface Treatment(Glare/non Glare)	non Glare
INPUT/OUTPUT	
HDMI 2.0	Yes
D-Sub	Yes
TUNER INPUT	
Digital	ATSC
Analog	NTSC
SPEAKER	
Type	Internal
Input	5W x 2
FREQUENCY	
H-Frequency	30kHz-83kHz
V-Frequency	56Hz-75Hz
POWER	
Type (w/ Watt)	Adapter (32W)
Input	100-240V
Normal On (Typ.)	TBD
Power Save/Sleep Mode (Max)	1W
DC Off (Max)	0.4W
SPECIAL FEATURES	
HDCP	Yes
Remote Control	Yes
Key Lock	Yes
Caption	Yes
Flicker Safe	Yes
Eye Comfort Mode	Yes
Smart Energy Saving	Yes
Motion Eye Care	Yes
Auto / Manual Clock	Yes
On/ Off Time	Yes

Sleep Timer	Yes
Auto Off / Auto Sleep	Yes
Picture Mode	Yes
Triple XD engine	Yes
ARC-PC	16:9, 4:3
Wall Mount	100 x 100
DIMENSIONS/WEIGHT	
With Stand (WxHxD)	25.3" x 6.3" x 16.9"
Without Stand (WxHxD)	25.3" x 2.3" x 15.7"
Shipping Dimensions (WxHxD)	31.1" x 4.3" x 17.3"
With Stand Weight	23 lbs
Without Stand Weight	22 lbs
Shipping Weight	30 lbs
ACCESSORIES	
Power Cord	Yes
Remote Controller	Yes
STANDARD	
UL / cUL	Yes
FCC-B	Yes
EPA	Yes
LIMITED WARRANTY / UPC	
Limited Warranty	1 Year Parts and Labor
UPC	719192199767
Country of Origin	Mexico