

## Hospital-Grade Power Cord, NEMA 5-15P to C13 - Green Dot, 10A, 125V, 18 AWG, 8 ft. (2.43 m) Coiled Cord, Black

MODEL NUMBER: P006-C08-HG10



Coiled medical power cord connects your PC or other hospital equipment with a C14 inlet to a grounded hospital-grade AC outlet.

### Features

**Hospital-Grade Power Cable is a Safe Solution for Medical Facilities** This hospital-grade IEC power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible hospital equipment with a three-pin C14 inlet. It features a C13 end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source located outside patient-care vicinities.

**Coiled Power Cord Allows You Freedom of Movement** The NEMA 5-15P-HG hospital-grade plug is connected to a coiled power cord that fully extends to 8-ft. (2.43 m). The cord is designed to resist tangles and knots, and it takes up less space when not stretched to its full length. Best of all, the coiled cable gives you more freedom in placing the power strip where it's most needed at any given time.

**Designed and Tested to Strict Hospital-Grade Standards** The hospital-grade power cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

### Highlights

- Recommended for connecting devices to power outlets outside patient-care vicinities
- Coiled cord extends to 8-ft. (2.43 m) to allow flexibility in placing devices away from AC outlet
- Medical power cord replaces or upgrades power cord provided by manufacturer
- NEMA 5-15P-HG plug connects to AC power; C13 plug connects to device's C14 inlet

### Applications

- Connect devices like PCs, mobile carts, monitors and printers to a power outlet up to 8-ft. (2.43 m) away in a hospital environment outside patient-care vicinities
- Extend an existing power connection up to 8-ft. (2.43 m) to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P006-C08-HG10 Hospital-Grade Power Cord, NEMA 5-15P to C13, 8-ft. (2.43 m) Coiled, Black

## Specifications

### OVERVIEW

UPC Code	037332193322
Device Compatibility	Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America
<b>INPUT</b>	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	8
Cable Length (m)	2.4
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	17.78 x 25.15 x 1.27
Shipping Dimensions (hwd / in.)	7.00 x 9.90 x 0.50
Shipping Weight (kg)	0.27
Shipping Weight (lbs.)	0.60
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P-HG
Side B - Connector 1	IEC-320-C13
<b>SPECIAL FEATURES</b>	
High Voltage	No
Locking Plug	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	ANSI/UL 62 AND 817, CAN/CSA C22.2 NO. 21 AND 49, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<https://www.tripplite.com/products/product-certification-agencies>