

**LG MONITORS**

# 27UD68-P

## 27" Ultra HD IPS 4K Monitor

**27"**

\* Class size: See below for details.

**Ultra HD IPS 4K**
**sRGB over 99%**
**Freesync (at 60Hz)**
**Color Calibrated**
**Game Mode, Black Stabilizer**
**On-Screen Control**
**My Display Presets**
**HDMI x 2, Display Port**


| PANEL                          |                      |
|--------------------------------|----------------------|
| Screen Size                    | 27"                  |
| Panel Type                     | IPS                  |
| Color Gamut (CIE 1931)         | sRGB 99%             |
| Color Depth (Number of Colors) | 10bit(8bit + A-FRC)  |
| Pixel Pitch (mm)               | 0.1554mm x 0.1554mm  |
| Response Time                  | 5ms GTG              |
| Refresh Rate                   | 60 Hz                |
| Aspect Ratio                   | 16:9                 |
| Resolution                     | 3840x2160            |
| Brightness                     | 350 cd/m2            |
| Contrast Ratio                 | 5M:1                 |
| Viewing Angle                  | 178 / 178            |
| INPUT/OUTPUT                   |                      |
| HDMI 2.0                       | Yes                  |
| Display Port 1.2               | Yes                  |
| D-Sub                          | Yes                  |
| POWER                          |                      |
| Type                           | 40W Adapter          |
| Input                          | 100-240Vac, 50/60Hz  |
| Normal On (EPA 6.0)            | 29W                  |
| SPECIAL FEATURES               |                      |
| Picture Mode                   | Yes                  |
| Reader Mode                    | Yes                  |
| Original Ratio                 | Yes                  |
| PIP/PBP                        | Yes                  |
| Color weakness                 | Yes                  |
| Flicker safe                   | Yes                  |
| Automatic Standby              | Yes                  |
| Six Axis Control               | Yes                  |
| Smart Energy Saving            | Yes                  |
| Super Resolution+              | Yes                  |
| 4 screen split                 | Yes                  |
| On-Screen Control              | Yes                  |
| Others                         | Black Stabilizer     |
| DIMENSIONS/WEIGHT              |                      |
| Without Stand (WxHxD)          | 24.2" x 1.9" x 14.4" |
| With Stand (WxHxD)             | 24.2" x 7.3" x 17.9" |
| Shipping Dimensions (WxHxD)    | 27.3" x 17.3" x 5.5" |
| With Stand Weight              | 10.8 lbs             |
| Shipping Weight                | 14.1 lbs             |

| CABINET / ACCESSORIES  |                        |
|------------------------|------------------------|
| Power Cord             | Yes                    |
| HDMI                   | Yes                    |
| CD                     | Yes                    |
| ESG                    | Yes                    |
| Manual                 | Yes                    |
| Cable holder           | Yes                    |
| STANDARD               |                        |
| UL(cUL)                | Yes                    |
| TUV-TYPE               | Yes                    |
| FCC-B, CE              | Yes                    |
| EPA 6.0                | Yes                    |
| ErP                    | Yes                    |
| EPEAT                  | Yes (Gold)             |
| Windows                | Yes (win10)            |
| LIMITED WARRANTY / UPC |                        |
| Limited Warranty       | 1 Year Parts and Labor |
| UPC                    | 719192200609           |
| Country of Origin      | China                  |